






ZHENQIN




DS1026 SERIES

FEMALE HEADER PITCH 2.0mm TYPE




DS1026-12 SERIES
Side Entry
Right Angle



DS1026-13 SERIES
Side Entry
Right Angle



DS1026-14 SERIES
Side Entry
S.M.T



DS1027 & 1028 SERIES



MINI JUMPER PITCH DS1027 2.54mm & DS1028 PITCH 2.0mm

MATERIAL

- ◆ Insulator: Thermoplastic (UL 94V-0)
- ◆ Color: See ordering information
- ◆ Contact: Copper Alloy
- ◆ Contact Plated: See ordering information

SPECIFICATION

- ◆ Storage Temperature: -20-70°C
- ◆ Operating Temperature: 0-85°C
- ◆ Contact Resistance: 12m Ω max.



UNIT:mm

Ordering Information

Series No.	No. of Contacts	Housing Type	Terminal Material	Contact plating	Housing Color	Profile
DS1027 & DS1028	34	A	B	F1	B.	I
	1-9 pieces	A: Open B: Closed	P: Phosphor Bronze B: Brass	F1: Gold Flash (Please contact us for other plating thickness)	B: Black U: Blue E: Green R: Red	L: Long TYPE 1: 6.0mm 2: 6.47mm