

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0039000038**
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 18-24, 22+22 AWG, Reel

Documents:

Drawing (PDF)	Application Specification 55560001-AS-000 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Packaging Specification 55560001-PK-000 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	Test Summary 55560000-TS-000 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification 55560008-TS-000 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification PS-5556-001-001 (PDF)	Datasheet (PDF)
Product Specification PS-5556-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000039 (Loose)
Product Name	Mini-Fit
UPC	800753585010

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.182/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 22+22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	5556T
--------------------	-------

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Packaging Specification	55560001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, 55560008-TS-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	55560000-SD-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

5556 Series

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel
 Mount [44516](#)
Mini-Fit BMI Panel Mount
 Receptacle Housing
 [42474](#) , [43760](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for	11030044
Mini-Fit Jr. Terminals	
FineAdjust Applicator	2037026300
for Mini-Fit Double	
Crimp Applications	
Using Two 22 AWG	
Wires	

PremiumGrade Hand	<u>638190901</u>
Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 18-24 AWG	
FineAdjust	<u>639015600</u>
Applicator for 18-20 AWG and 18-24 AWG Wires with Insulation Diameter 1.90-2.30mm	
FineAdjust Applicator	<u>639023900</u>
for Insulation OD 1.40-1.70mm - 18-24 AWG	
FineAdjust Applicator	<u>639024800</u>
for Insulation OD 2.50-2.95mm	
Optimized for 18 AWG Only	
FineAdjust Applicator	<u>639024900</u>
for Insulation OD 2.30-2.60mm - 18-24 AWG	
FineAdjust Applicator	<u>639047800</u>
for Insulation OD 2.50-2.95mm, 18-24 AWG	
FineAdjust Applicator	<u>639048000</u>
for Insulation OD 1.65-2.05mm, 18-24 AWG	
T2 Terminator	<u>639115600</u>
for insulation OD 1.90-2.30mm - 18-24 AWG	
T2 Terminator	<u>639123900</u>
for insulation OD 1.40-1.70mm - 18-24 AWG	
T2 Terminator	<u>639124800</u>
for insulation OD 2.50-2.95mm	
optimized for 18 AWG only	
T2 Terminator	<u>639124900</u>
for insulation OD 2.30-2.60mm - 18-24 AWG	
T2 Terminator	<u>639147800</u>
for Mini-Fit Crimp Terminals, 18-24 AWG with Large Insulation ODs	
T2 Terminator	<u>639148000</u>
for Mini-Fit Crimp Terminals, 18-24 AWG with Smaller Insulation ODs	
Japan	
Description	Product #
Applicator for M211A	<u>570223000</u>
Bench Press, 18-24 AWG Wire	

S-1 Applicator 570223700
for Mini-Fit Plug
and Receptacle
Terminals, 18-24
AWG, UL1007 Wires
S-1 Applicator 570223710
for Mini-Fit Plug
and Receptacle
Terminals, 18-24
AWG, UL1015 Wires
Hand Extraction Tool 570316000

This document was generated on 06/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39-00-0038](#) [39-00-0038 \(Mouser Reel\)](#) [39-00-0038 \(Cut Strip\)](#)