CONSTANT VOLTAGE LED DRIVER 24VDC 50WATT

Electronics

POWERPAX: LED-DR-24V-2080-50

Features:

- Input Voltage 200-240Vac
- IP20 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 1 Year Warranty

Description:

The Range of 50 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-24V-2080-50
Output Voltage Rating	24Vdc
Output Current Range	2.08A
Rated Power	50 Watt
Dimensions	185 x 63 x 22mm
Input Voltage Range	200-240VAC
Input Voltage Frequency	50-60Hz
Inrush Current	<75A
Input power	<65W
Efficiency	≥85%
Power Consumption Without Load	<0.5W
Overload Protection	Ta, 0.94-1.06 times of input voltage, 1.5 times of rated power
Short Circuit Protection	Ta, 0.94-1.06 times of input voltage
Automatically Restart	Over load, short circuit
Working Temperature	-20°C to +45°C
Relative Humidity	45% ~ 85%
MTBF	30000hr
EMC emission	EN55015
EMC Immunity	EN61547
Safety Standards	EN61347-1, EN61347-2-13



General Note TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT Electronics plc


TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500

CONSTANT VOLTAGE LED DRIVER 24VDC 50WATT



POWERPAX: LED-DR-24V-2080-50

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX

TT Electronics IoT Solutions Ltd Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK t: +44 (0) 1429 852 500

ISS.3 10/06/2020 Page: 2