

# Rittal – The System.

Faster – better – everywhere.



## AX 1260.000

# Compact enclosure AX

State: 15/06/2022 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 1260.000 - Compact enclosure AX Basic enclosure AX, sheet steel

System perfection. The new compact enclosure AX (sheet steel) offers maximum data quality and consistency in engineering, and flexibility and safety in assembly and interior installation.

## Features

Model No.	AX 1260.000
Material	Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure with door(s) Gland plate(s) in enclosure base Mounting plate Perforated door strip Lock: 3 mm double-bit
Protection category NEMA	NEMA 1, 3R, 4, 12
Protection category to IEC 60 529	IP 66
Type rating to UL 50E	Type 1, 3R, 4, 12
IK Code	IK10
Dimensions	Width: 600 mm Height: 1,200 mm Depth: 300 mm
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness of mounting plate	2.5 mm

# Features

Mounting plate	Width: 545 mm Height: 1,175 mm
Number of doors	1
Interchangeable door hinge	Yes
Lock	Lock version: 3-point lock system Number locks: 1 Lock insert: 3 mm double-bit
Gland plate	Size: 7 Qty.: 1
Basic material	Sheet steel
Packs of	1 pc(s).
Weight/pack	50 kg
Copper weight (kg per piece)	0
Customs tariff number	94032080
EAN	4028177813274
ETIM 7.0	EC000261
ECLASS 8.0	27180101

# Approvals

Approvals	Bureau Veritas DNV-GL GOST Lloyds Register of Shipping UL + C-UL
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK