

Specification Sheet

Part Number: 110-80004



Tensions and provides clean, flush cuts for 50lb. to 250lb. cable ties, including wide strap ties.

Impact-resistant housing and durable components for extended service life.

Easy-to-adjust tension knob offers 33 different settings for precise, repeatable applications.

Advanced ergonomic design minimizes necessary hand force and “kickback” to reduce repetitive-motion injuries.

EVO 9HT High Tension Mechanical Hand Tool, Tension Range 27 lb to 116 lb, 1/pkg

Article Number 110-80004

Type EVO9HT

Color Red (RD) Black (BK)

Product Description HellermannTyton's EVO 9 manual cable tie application tool combines durability, precision and control with unparalleled comfort. Manufactured with high-performance materials and components, the EVO 9 cuts cable ties with up to 250-lb tensile strength. Its innovative, ergonomic design minimizes the stress on hands and wrists and “kickback” that occur with traditional tools, reducing the risk of repetitive-motion injuries. The HT model offers high tension while the SP model features a smaller grip.

| | |
|---------------------------------------|---|
| Short Description | EVO 9HT High Tension Mechanical Hand Tool, Tension Range 27 lb to 116 lb, 1/pkg |
| Global Part Name | EVO9HT-MET/PL-BK/RD |
| Technical Description | Tension Range 27 lb to 116 lb |
| Length L (Imperial) | 7.5 |
| Length L (Metric) | 191 |
| Width W (Imperial) | 1.3 |
| Width W (Metric) | 33 |
| Cable Ties | T120, T150, T250, T255, WS |
| Height H (Imperial) | 5.3 |
| Height H (Metric) | 135 |
| Tension Setting Tools | Adjustable |
| Cable Tie Width Max (Imperial) | 0.5 |
| Material | Metal (MET) Plastic (PL) |
| Material Shortcut | MET PL |

ROHS Compliant Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 8205599000