

## **TECHNICAL DATA SHEET**

Part#: 7148E

## Cutters - Medium Taper Relieved Head -★★★★+- Carbon Steel

The 7148E five star Lazer Line® medium tapered/relieved optimum flush cutter has a cutting capacity of .001" - .036" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action.

**Taper Relieved Head** 

\*\*\*\*

Lazer Flush

662847009228

8203.20.60.60

Carbon 10<sup>10</sup> ohms/sq

3

**EAR99** 

USA

27111511

- Precision Level
- Material
- Surface Resistivity
- Shape
- Type of Cut
- Group
- Cutting Capacity
- Blade Angle Blade Length

• Body Width

Body Height

**Cutting Tools** 50 - 18 AWG / .001 - .036" / .03 - .9 mm 14.25° .36" (9mm) 0.42" (10.5mm) .25" (6.25mm) 5.75" (143.75mm)

MADE IN

• Weight (OZ) • UPC

• OAL

- Schedule B
- ECCN
- UNSPSC Code
- Country of Origin









