

## **TECHNICAL DATA SHEET**

Part#: 7141E

Cutters - Medium Oval Head -★★★★- Carbon Steel

The 7141E five star Lazer Line® medium oval maximum flush cutter has a cutting capacity of .005" - .045" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

\*\*\*\* Precision Level Carbon

Material

10<sup>10</sup> ohms/sq Surface Resistivity Shape Round Head Optimum Flush

Type of Cut

**Cutting Tools** 

• Group Cutting Capacity

36 - 17 AWG / .005 - .045" / .13 - 1.13 mm

 Blade Angle 14.25°

.38" (9.5mm)

• Blade Length • Body Width

0.42" (10.5mm)

Body Height

.25" (6.25mm)

OAL

5.75" (143.75mm) 3

• Weight (OZ)

662847009150

Schedule B

UPC

8203.20.60.60

• ECCN

EAR99

• UNSPSC Code

27111511

Country of Origin

**USA** 









