

TECHNICAL DATA SHEET

Part#: 7242E

Cutters - Medium Oval Head -★★★★- Carbon Steel

The 7242E five star Lazer Line® medium oval optimum flush cutter has a cutting capacity of .001" - .042" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action.

**** Precision Level

Material

 Surface Resistivity 108 ohms/sq Shape Round Head

 Type of Cut Lazer Flush • Group **Cutting Tools**

 Cutting Capacity 50 - 18 AWG / .001 - .042" / .03 - 1.05 mm

Carbon

 Blade Angle 14.25° • Blade Length .38" (9.5mm) • Body Width 0.42" (10.5mm) .25" (6.25mm) Body Height

OAL 4.75" (118.75mm) 3

• Weight (OZ)

UPC 662847009518 Schedule B 8203.20.60.60 • ECCN EAR99 • UNSPSC Code 27111511

 Country of Origin **USA**









