

Datenblatt Art. 394.190

Data sheet | Fiche technique | Scheda tecnica | Fișa tehnică

LED Akku Handleuchte

Netzanschluss		Power supply	
Ladegerät			
Stromanschluss	100-240VAC~ 50Hz 12VDC	Charger Power supply	100-240VAC~ 50Hz 12VDC
Bemessungsspannung	3,7VDC	Rated voltage	3,7VDC
Arbeitsstrom	500mA	Working current	500mA
Batterie			
Bezeichnung	JNICR18650 2200mAh 3.7V	Battery Designation	JNICR18650 2200mAh 3.7V
Typ	Lithium Batterie	Type	Lithium Battery
Kapazität	2200mAh	Capacity	2200mAh
Gewicht	44g	Weight	44g
Funktionsmodule		Function modules	
Schalter			
LED Lampe			
160 LEDs 9,6W LED Lumen: 13,000~15,000MCD		160 LEDs 9,6W LED lumen 13,000~15,000MCD	
Weitere Produkteigenschaften		Further product attributes	
Material			
Gehäuse: ABS (Acrylnitril-Butadien-Styrol) PVC (Polyvinylchlorid)		Housing: ABS (Acrylonitrile-Butadiene-Styrene) PVC (Polyvinyl Chloride)	
Länge	53,3cm	Length	53,3cm
Lieferumfang		Scope of delivery	
1x LED Handleuchte inkl. 230V~ Netzteil, 12V Kfz-Ladegerät, Magnethalter		1x LED Handlamp incl. 230V~ mains adaptor, 12V in-vehicle charger, magnetic holder	
Im Blister verpackt		In Blister	
Umgebungsbedingungen		Environmental conditions	
Schutzart	IP20	Protection type	IP20
Konformität / Approbation		Conformity / Approval	
WEEE-pflichtig		Underlies WEEE	

