

## **TECHNICAL DATA SHEET**

Part#: 7210E

Cutters - Medium - Oval/Relieved Head -★★★★- Carbon Steel

The 7210E five star large Lazer Line® round relieved head Semi-flush cutter with a cutting capacity of .008" to .045" soft wire is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This overall length is 4.75". The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action.

\*\*\*\* Precision Level Carbon

Material

 Surface Resistivity 10<sup>8</sup> ohms/sq

Round Relieved Head Shape Type of Cut Optimum Flush • Group **Cutting Tools** 

32 - 16 AWG / .008 - .050" / .2 - 1.25 mm Cutting Capacity

 Blade Angle 14.25°

• Blade Length .46" (11.5mm) Body Width 0.42" (10.5mm) .25" (6.25mm) Body Height OAL 4.75" (118.75mm) 3

• Weight (OZ)

UPC 662847009365 Schedule B 8203.20.60.60 • ECCN EAR99 • UNSPSC Code 27111511 Country of Origin **USA** 









