

TECHNICAL DATA SHEET

Part#: 9240E

Cutters - Medium Oval Head -★★★★- Carbon Steel

The 9240E five star Lazer Line® medium oval semi-flush cutter has a cutting capacity of .018" - .040" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

**** Precision Level

 Material Carbon

10¹⁰ ohms/sq Surface Resistivity Shape Round Head Type of Cut Semi-Flush • Group **Cutting Tools**

 Cutting Capacity 32 - 18 AWG / .008 - .042" / .2 - 1.05 mm

14.25° Blade Angle

• Blade Length .31" (7.75mm) Body Width 0.42" (10.5mm) .25" (6.25mm) Body Height OAL 4.5" (112.5mm) 3

• Weight (OZ)

UPC 662847009822 Schedule B 8203.20.60.60 • ECCN EAR99 • UNSPSC Code 27111511 Country of Origin **USA**









