

TECHNICAL DATA SHEET

Part#: 7104E

Cutters - Angulated Head ★★★★- Carbon Steel - Blade Length.30" (7.5mm)

The 7104E five star Lazer Line® large angulated/tapered maximum flush cutter with a cutting capacity of .003" - .025" soft wire is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. This 6" tool has a 50° angled tip with a set-screw to prevent over-travel while prolonging the life of the tool.

**** Precision Level Carbon

Material

10¹⁰ ohms/sq Surface Resistivity Shape Angulated Head Type of Cut Optimum Flush

• Group **Cutting Tools**

 Cutting Capacity 40 - 22 AWG / .003 - .025" / .08 - .063 mm

50° • Blade Angle

• Blade Length .30" (7.5mm) • Body Width 0.42" (10.5mm) .25" (6.25mm) Body Height 6" (150mm) OAL

• Weight (OZ) 3.4

• UPC 662847009044 Schedule B 8203.20.60.60 • ECCN EAR99 • UNSPSC Code 27111511 Country of Origin **USA**









