

c SU'us **RoHS** Compliant



E222871

UL Approved Illuminated Pushbutton

## Specifications

Electrical Ratings	3A @ 125VAC, 65°C, 50K cycles				
	3A @ 250VAC, 65°C, 50K cycles				
Sealing Degree	IP67				
Electrical Life	50,000 cycles typical				
Mechanical Life	1,000,000 cycles typical momentary				
	500,000 cycles typical latching				
Contact Resistance	$\leq$ 50m $\Omega$ initial				

Actuation Force	200 ±50gF SPDT				
	250 ±50gF DPDT				
Actuation Travel	3.2 ± .25mm				
Dielectric Strength	2,000Vrms min between contacts				
Insulation Resistance	$\geq$ 1,000M $\Omega$ min @ 500VDC				
Operating Temperature	-20°C to 65°C				
Storage Temperature	-20°C to 65°C				


#### Materials

Actuator	Stainless Steel, Anodized Aluminum
LED Lens	Polycarbonate (PC)
Threaded Body	Stainless Steel, Anodized Aluminum
Terminal Support	Polybutylene Terephthalate (PBT)
Inner Switch Body	Polybutylene Terephthalate (PBT)
Contacts	Silver plated Copper Alloy
Terminals	Silver plated Copper Alloy
Hardware	One Hex Nut & One "O" Ring Supplied

## **Ordering Information**

1. Series	AHU	1	Ν	В	S	R	12
AHU 2. Number of Po 1 = SPDT 2 = DPDT	les						
3. Latching Option N = Momentar L = Latching							
B = Flush actu C = Flush actu	ator, non-illuminat ator, ring illuminat ator, dot illuminate	ed	ıminated				
5. Switch Finish S = Stainless B = Black Ano	Steel dized Aluminum						
6. LED Color Z = No LED R = Red Y = Yellow	G = Green B = Blue W = White						
7. LED Voltage Z = No LED 6 = 6V 12 = 12V 24 = 24V	110 = 110V 220 = 220V N = No internal r	esistor in series wit	h the LED				
	W	ww.citrelay.com	phone - 763	.535.2339	fax - 763.535.21	94	page 1






www.citrelay.com phone - 763.535.2339 fax - 763.535.2194


Dimensions shown in mm. Dimensions are shown for reference purposes only.

page 2



#### Schematics Single Pole






**Bottom View** 


↓ 2 5 C

**Double Pole** 




Panel Cut-Out

Panel Cut-Out



## **Optional Socket Housing**



Specifications and availability subject to change without notice.

-4.00 [.16] -3.70 [.15]

page 3



# AHU UL Approved Illuminated Pushbutton

#### **LED Characteristics**

LED Batingo		Color						
LED Ratings		R	Y	G	В	W	Units	
Reverse Voltage	V <sub>R</sub>	5	5	5	5	5	V	
Forward Current (peak)	I <sub>FS</sub>	120	120	160	160	160	mA	
Reverse Current V <sub>R</sub> = 5V	I <sub>R</sub>	10	10	10	10	10	μA	
Power Dissipation	PT	80	80	120	120	120	mW	
Forward Voltage (typ) I <sub>F</sub> = 20mA	V <sub>F</sub>	2.1	2.1	3.3	3.3	3.0	V	
Luminous Intensity, I <sub>F</sub> = 20mA	LI	120	120	170	100	700	mcd	

Dimensions shown in mm. Dimensions are shown for reference purposes only.