Energizer_® VISION HD Performance light with Digital Focus

PMZH21

The Energizer. VISION HD Performance light with Digital Focus features MAXVIZ technology that offers outstanding beam natural color and optimized contrast, giving users an expanded field of high-definition vision. Energizer. proprietary Digital Focus Technology enables users to have optimum control of their light for enhanced direct and peripheral vision. The exceptional user control with enhanced light output makes this light ideal for the home, vehicle or workplace. Experience Energizer. Vision HD Performance Light with Digital Focus for the ultimate lighting control in the palm of your hand.



Provides 400 Lumens of Light



Provides Run Time of 4 Hours



Sustains 1 Meter Drop Test



Illuminates objects up to 115m away



Water Resistant – works after splashing water on all sides

DESIGN BENEFITS

- ✓ Durable aircraft grade aluminum construction
- One press digital focusing allows consumers to adjust light beam between focus and area light
- √ 15-20 Year Design To Last based on typical consumer usage patterns
- ✓ Hold the switch for two seconds to activate strobe mode

LIGHT AND POWER SOURCE

- √ Features LED Technology
- ✓ Operates on 2 AA for maximum brightness runtime



CERTIFICATES AND COMPLIANCE

C ∈ RoHS

EMC, EN62471, FCC

Tested according to ANSI/PLATO FL 1 – 2016 Standards. Results based on: Energizer MAX Alk / E91

PERFORMANCE BENEFITS

- MAXVIZ Technology to deliver a wide, powerful beam and high-definition vision
- Up to 15X brighter than standard LED technology
- ✓ Extended run time

SPECIFICATIONS

Weight Excluding Batteries:

108 Grams / 3.81 Ounces

Dimensions:

159mm x 30mm / 22mm or 6.25" x 1.19" / 0.88"

NUMBER OF OPERATING MODES: 3

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
High	400	4	115
Low	50	21	35