


[PRODUCTS](#) ▾

[MARKETS](#) ▾

[RESOURCES](#)
[COMPANY](#) ▾

[DISTRIBUTORS](#) ▾

[CONTACT US](#)

[Home](#) / [Markets](#) / [Military](#) / [Aerospace](#) / [Pushbutton – 59-113](#)

Images are for representation purposes only.

## Pushbutton – 59-113

12MM MINIATURE SEALED PUSHBUTTON

SKU: 59-113 / Categories: [All Products](#), [Construction](#), [Industrial](#), [Military / Aerospace](#), [Offroad / Recreation](#), [Push Button](#)

<a href="#">Description</a>	<a href="#">Additional information</a>	<a href="#">Datasheet</a>
<a href="#">Downloads</a>	<a href="#">Stock Checker</a>	

### Additional information

<b>Switch Type</b>	<i>Pushbutton</i>
<b>Switch Operation</b>	<i>Momentary</i>
<b>Actuator Type</b>	<i>Round Button</i>
<b>Actuator / Cap Color</b>	<i>Green</i>
<b>Case Color</b>	<i>Black</i>
<b>Contact Configuration</b>	<i>SPST-NO-DB</i>
<b>Operating Force (Nom)</b>	<i>3N / 10.8ozf</i>
<b>Contact Material</b>	<i>Gold Plated</i>
<b>Contact Voltage AC Nom</b>	<i>125V</i>
<b>Contact Voltage DC Max</b>	<i>50V</i>
<b>Contact Current AC Max</b>	<i>400mA @ 32V AC</i>
<b>Contact Current DC Max</b>	<i>100mA</i>
<b>Illuminated</b>	<i>Non Illuminated</i>
<b>Illumination Color</b>	<i>Not Applicable</i>
<b>Illumination Voltage</b>	<i>Not Applicable</i>
<b>Switch Mounting</b>	<i>Threaded Bushing</i>
<b>Panel Cutout (H x W)</b>	<i>13.65 x 12.95</i>
<b>IP Rating</b>	<i>IP67</i>
<b>Legend</b>	<i>Not Applicable</i>
<b>Operating Temperature Range</b>	<i>-55°C to +125°C</i>
<b>Standards Met</b>	<i>Not Applicable</i>
<b>Mechanical Life</b>	<i>1000000</i>
<b>Electrical Life</b>	<i>500000</i>
<b>Product Series</b>	<i>59</i>

#### ITW Switches USA

195 E Algonquin Road  
Des Plaines, IL 60016  
P. 800-544-3354

#### ITW Switches UK

Edgington Way, Sidcup, Kent,  
DA14 5EF. United Kingdom  
P. + 44 (0) 208 308 8000

#### Terms of Use

[Privacy Policy/GDPR](#)  
[Modern Slavery Act](#)  
[Terms & Conditions \(North America\)](#)  
[Terms & Conditions \(EU\)](#)

