

CHERRY MC 2000



Models may vary from the image shown

Infra-red mouse with tilt-wheel technology

Single-handed control and efficient navigation. The CHERRY MC 2000 infra-red mouse with tilt-wheel offers top quality processing, precision and reliability. Unique in its class.

Key benefits

- 3-button mouse
- Tilt-wheel for horizontal/vertical scrolling
- GS certification
- Resolution 1,600 dpi
- Infra-red sensor
- Suitable for both right-handed and left-handed operation
- Symmetrical design
- Standard size

Technical Data:

Weight (product):

118 g

Total weight (with packaging):

156 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-15°C to 60°C

Operating Temperature:

0°C to 40°C



Current Consumption:

max. 50 mA

Interface:

- USB

Product approvals:

- CE 
- TÜV-Süd/GS 

System requirements:

- USB connection

Delivery Volume:

- CHERRY MC 2000
- Operating instructions in hard copy

Dimensions (product):

109 x 62 x 37 mm

Packaging dimensions:

130 x 100 x 43 mm

Reliability:

- Standard keys: >3 mill. operations

Mouse:

- Scanning: Infrared
- Resolution: 1600 dpi
- Number of Keys: 3
- Mouse wheel design: Tilt-Wheel
- Design: Symmetrical
- Connection: USB
- Housing colour: black
- Key colour: black

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 125

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

	Product name	Order number	EAN code
1	CHERRY MC 2000	JM-0600-2	4025112083334