

Wiha SoftFinish®.

The specialist for dry and general applications.



The right tool at a glance, thanks to the printed screw symbol on the handle end.

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum torque forces in dry and general working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.

Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.



Thermoplastic elastomer tolerates high loads and feels soft and pleasant to the touch.

Blade with hex bolster for wrenches to use on particularly tight screws.

Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

For slotted screws.



302 SoftFinish® slotted cabinet screwdriver. Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 5265, DIN ISO 2380.
Application: Especially for dry and general applications.

| Order-No. | ⌀ | → | ⊖ | ● | ← | + | ⊞ |
|-----------|-----|-----|-----|-----|-----|----|----|
| 00684 6 | 2.0 | 65 | 0.4 | 2.0 | 169 | 23 | 10 |
| 00685 3 | 2.5 | 75 | 0.4 | 2.5 | 179 | 23 | 10 |
| 00686 0 | 3.0 | 80 | 0.5 | 3.0 | 184 | 23 | 10 |
| 00687 7 | 3.0 | 100 | 0.5 | 3.0 | 204 | 23 | 10 |
| 00689 1 | 3.0 | 150 | 0.5 | 3.0 | 254 | 23 | 10 |
| 00690 7 | 3.0 | 200 | 0.5 | 3.0 | 304 | 23 | 10 |
| 32383 7 | 3.0 | 300 | 0.5 | 3.0 | 404 | 23 | 5 |
| 00691 4 | 3.5 | 100 | 0.6 | 3.5 | 204 | 23 | 10 |
| 26931 9 | 3.5 | 200 | 0.5 | 3.5 | 304 | 23 | 10 |
| 00692 1 | 4.0 | 100 | 0.8 | 4.0 | 211 | 30 | 10 |
| 00694 5 | 4.0 | 150 | 0.8 | 4.0 | 261 | 30 | 10 |
| 00695 2 | 4.0 | 200 | 0.8 | 4.0 | 311 | 30 | 10 |
| 00696 9 | 4.0 | 300 | 0.8 | 4.0 | 411 | 30 | 5 |
| 27753 6 | 4.5 | 80 | 0.8 | 4.5 | 191 | 30 | 10 |
| 00697 6 | 4.5 | 125 | 0.8 | 4.5 | 236 | 30 | 10 |
| 00698 3 | 5.5 | 125 | 1.0 | 5.5 | 236 | 30 | 10 |
| 00700 3 | 5.5 | 150 | 1.0 | 5.5 | 261 | 30 | 10 |
| 00701 0 | 5.5 | 200 | 1.0 | 5.5 | 311 | 30 | 10 |
| 00702 7 | 5.5 | 300 | 1.0 | 5.5 | 411 | 30 | 5 |
| 32384 4 | 6.0 | 300 | 1.0 | 6.0 | 418 | 36 | 5 |

• Additional dimension. Non-DIN size.



302 SoftFinish® slotted workshop screwdriver. Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 5265, DIN ISO 2380.
Application: Especially for dry and general applications.

| Order-No. | ⌀ | → | ⊖ | ● | ← | + | ⊞ |
|-----------|------|-----|-----|------|-----|----|----|
| 27754 3 | 6.0 | 100 | 1.0 | 5.5 | 218 | 36 | 10 |
| 27755 0 | 6.0 | 150 | 1.0 | 5.5 | 268 | 36 | 10 |
| 00704 1 | 6.5 | 100 | 1.2 | 6.0 | 218 | 36 | 10 |
| 00703 4 | 6.5 | 150 | 1.2 | 6.0 | 268 | 36 | 10 |
| 00706 5 | 6.5 | 200 | 1.2 | 6.0 | 318 | 36 | 5 |
| 00708 9 | 8.0 | 150 | 1.2 | 7.0 | 274 | 41 | 10 |
| 00707 2 | 8.0 | 175 | 1.2 | 7.0 | 299 | 41 | 5 |
| 00709 6 | 8.0 | 175 | 1.6 | 7.0 | 299 | 41 | 5 |
| 32399 8 | 8.0 | 300 | 1.2 | 7.0 | 424 | 41 | 5 |
| 00711 9 | 10.0 | 200 | 1.6 | 8.0 | 324 | 41 | 5 |
| 32400 1 | 10.0 | 300 | 1.6 | 8.0 | 424 | 41 | 5 |
| 00712 6 | 12.0 | 250 | 2.0 | 8.0 | 374 | 41 | 5 |
| 00713 3 | 14.0 | 250 | 2.5 | 11.0 | 374 | 41 | 5 |

• Additional dimension. Non-DIN size.

For slotted screws.



308 SoftFinish® slotted screwdriver. Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 5265, DIN ISO 2380.
Application: Especially for dry and general applications.

| Order-No. | ⌀ | → | ⊖ | ● | ← | + | ⊞ | |
|-----------|------|-----|-----|------|----|-----|----|----|
| 00731 7 | 3.5 | 75 | 0.6 | 4.0 | - | 186 | 30 | 10 |
| 00732 4 | 4.5 | 90 | 0.8 | 4.0 | - | 201 | 30 | 10 |
| 00733 1 | 5.5 | 100 | 1.0 | 5.0 | 8 | 213 | 36 | 10 |
| 00734 8 | 6.5 | 125 | 1.2 | 6.0 | 10 | 238 | 36 | 10 |
| 00735 5 | 7.0 | 125 | 1.1 | 6.0 | 10 | 238 | 36 | 10 |
| 00736 2 | 8.0 | 150 | 1.2 | 8.0 | 13 | 268 | 41 | 10 |
| 00737 9 | 9.0 | 150 | 1.4 | 8.0 | 13 | 268 | 41 | 10 |
| 00738 6 | 10.0 | 175 | 1.6 | 8.0 | 13 | 293 | 41 | 5 |
| 00739 3 | 12.0 | 200 | 2.0 | 10.0 | 16 | 318 | 41 | 5 |
| 00740 9 | 14.0 | 250 | 2.5 | 10.0 | 16 | 368 | 41 | 5 |

• Additional dimension. Non-DIN size.



530 SoftFinish® slotted screwdriver. Hex blade with hex bolster, solid steel cap.

| Order-No. | ⌀ | → | ⊖ | ● | ← | + | ⊞ | |
|-----------|------|-----|-----|------|----|-----|----|----|
| 03223 4 | 3.5 | 75 | 0.6 | 4.0 | - | 186 | 30 | 10 |
| 03224 1 | 4.5 | 90 | 0.8 | 4.0 | - | 201 | 30 | 10 |
| 03225 8 | 5.5 | 100 | 1.0 | 5.0 | 8 | 213 | 36 | 10 |
| 03226 5 | 6.5 | 125 | 1.2 | 6.0 | 10 | 238 | 36 | 10 |
| 03228 9 | 8.0 | 150 | 1.2 | 8.0 | 13 | 271 | 41 | 5 |
| 03230 2 | 10.0 | 175 | 1.6 | 8.0 | 13 | 296 | 41 | 5 |
| 03231 9 | 12.0 | 200 | 2.0 | 10.0 | 16 | 321 | 41 | 5 |
| 03232 6 | 14.0 | 250 | 2.5 | 10.0 | 16 | 371 | 41 | 5 |

• Additional dimension. Non-DIN size.



398 SoftFinish® slotted screw-holding screwdriver. Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Application: For setting and turning screws in difficult to access areas.

| Order-No. | ⌀ | → | ⊖ | ← | + | ⊞ |
|-----------|-----|-----|-----|-----|----|---|
| 32867 2 | 2.5 | 75 | 0.4 | 186 | 30 | 5 |
| 32868 9 | 3.0 | 100 | 0.5 | 211 | 30 | 5 |
| 32869 6 | 4.0 | 125 | 0.8 | 243 | 36 | 5 |
| 32870 2 | 5.0 | 150 | 1.0 | 268 | 36 | 5 |
| 32871 9 | 6.0 | 175 | 1.2 | 293 | 36 | 5 |



Wiha SoftFinish®.

The specialist for dry and general applications.

For Phillips screws.



311 SoftFinish® Phillips screwdriver.
Round blade.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.


| Order-No. | ⊕ | → | ● | ○ | ← | → | → |
|-----------|------|-----|------|-----|----|---|----|
| 00754 6 | PH0 | 60 | 3.0 | 164 | 23 | | 10 |
| 27756 7 | PH0 | 100 | 3.0 | 204 | 23 | | 10 |
| 00756 0 | PH1 | 80 | 4.5 | 191 | 30 | | 10 |
| 27757 4 | PH1 | 100 | 4.5 | 211 | 30 | | 10 |
| 00757 7 | PH1• | 200 | 4.5 | 311 | 30 | | 10 |
| 03738 3 | PH1• | 300 | 4.5 | 411 | 30 | | 5 |
| 00759 1 | PH2 | 100 | 6.0 | 218 | 36 | | 10 |
| 27758 1 | PH2 | 150 | 6.0 | 268 | 36 | | 10 |
| 00760 7 | PH2• | 200 | 6.0 | 318 | 36 | | 5 |
| 03739 0 | PH2• | 300 | 6.0 | 418 | 36 | | 5 |
| 00762 1 | PH3 | 150 | 8.0 | 274 | 41 | | 10 |
| 00763 8 | PH4 | 200 | 10.0 | 324 | 41 | | 5 |

• Additional dimension. Non-DIN size.



312 SoftFinish® Phillips screwdriver.
Hex blade with hex bolster.

| Order-No. | ⊕ | → | ● | ○ | ← | → | → |
|-----------|-----|-----|------|----|-----|----|----|
| 00764 5 | PH1 | 80 | 5.0 | 8 | 186 | 30 | 10 |
| 00765 2 | PH2 | 100 | 6.0 | 10 | 213 | 36 | 10 |
| 00766 9 | PH3 | 150 | 8.0 | 13 | 268 | 41 | 10 |
| 00767 6 | PH4 | 200 | 10.0 | 16 | 318 | 41 | 5 |



531 SoftFinish® Phillips screwdriver.
Hex blade with hex bolster, solid steel cap.

| Order-No. | ⊕ | → | ● | ○ | ← | → | → |
|-----------|-----|-----|-----|----|-----|----|----|
| 03237 1 | PH1 | 80 | 5.0 | 8 | 186 | 30 | 10 |
| 03238 8 | PH2 | 100 | 6.0 | 10 | 213 | 36 | 10 |
| 03239 5 | PH3 | 150 | 8.0 | 13 | 268 | 41 | 10 |



397 SoftFinish® Phillips screw-holding screwdriver.
Clamping sleeve holds the screw.
Blade: Chrome-vanadium steel, through hardened, black-finish.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Application: For setting and turning screws in difficult to access areas.


| Order-No. | ⊕ | → | → | → | → |
|-----------|-----|-----|-----|----|---|
| 32406 3 | PH0 | 100 | 211 | 30 | 5 |
| 32404 9 | PH1 | 125 | 236 | 36 | 5 |
| 32405 6 | PH2 | 175 | 286 | 36 | 5 |

For Pozidriv screws.



313 SoftFinish® Pozidriv screwdriver.
Round blade.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

| Order-No. | ⊕ | → | ● | → | → | → |
|-----------|-----|-----|-----|-----|----|----|
| 00768 3 | PZ0 | 60 | 3.0 | 164 | 23 | 10 |
| 00770 6 | PZ1 | 80 | 4.5 | 191 | 30 | 10 |
| 26454 3 | PZ1 | 300 | 4.5 | 411 | 30 | 5 |
| 00772 0 | PZ2 | 100 | 6.0 | 218 | 36 | 10 |
| 26455 0 | PZ2 | 300 | 6.0 | 418 | 36 | 5 |
| 00774 4 | PZ3 | 150 | 8.0 | 274 | 41 | 10 |



314 SoftFinish® Pozidriv screwdriver.
Hex blade with hex bolster.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.

| Order-No. | ⊕ | → | ● | ○ | ← | → | → |
|-----------|-----|-----|------|----|-----|----|----|
| 00776 8 | PZ1 | 80 | 5.0 | 8 | 186 | 30 | 10 |
| 00777 5 | PZ2 | 100 | 6.0 | 10 | 213 | 36 | 10 |
| 00778 2 | PZ3 | 150 | 8.0 | 13 | 268 | 41 | 10 |
| 00779 9 | PZ4 | 200 | 10.0 | 16 | 318 | 41 | 5 |



532 SoftFinish® Pozidriv screwdriver.
Hex blade with hex bolster, solid steel cap.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: ISO 8764.
Application: Especially for dry and general applications.


| Order-No. | ⊕ | → | ● | ○ | ← | → | → |
|-----------|-----|-----|-----|----|-----|----|----|
| 03245 6 | PZ1 | 80 | 5.0 | 8 | 186 | 30 | 10 |
| 03246 3 | PZ2 | 100 | 6.0 | 10 | 213 | 36 | 10 |
| 03247 0 | PZ3 | 150 | 8.0 | 13 | 271 | 41 | 10 |

Stubby-screwdriver.



302 SoftFinish® slotted screwdriver.
Short round blade.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.
Standards: DIN 5265, DIN ISO 2380, handle acc. to DIN 5268 - style K.
Application: For working in confined spaces.

| Order-No. | ⊕ | → | ⊖ | ● | → | → | → |
|-----------|-----|----|-----|-----|----|----|----|
| 26964 7 | 4.0 | 25 | 0.8 | 4.0 | 81 | 34 | 10 |
| 26965 4 | 5.5 | 25 | 1.0 | 5.5 | 81 | 34 | 10 |
| 26966 1 | 6.5 | 25 | 1.2 | 6.5 | 81 | 34 | 10 |
| 26967 8 | 8.0 | 25 | 1.2 | 8.0 | 81 | 34 | 10 |



311 SoftFinish® Phillips screwdriver.
Short round blade.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.
Standards: ISO 8764, handle acc. to DIN 5268 - style K.
Application: For working in confined spaces.

| Order-No. | ⊕ | → | ● | → | → | → |
|-----------|-----|----|-----|----|----|----|
| 26968 5 | PH1 | 25 | 4.5 | 81 | 34 | 10 |
| 26969 2 | PH2 | 25 | 6.0 | 81 | 34 | 10 |
| 26970 8 | PH3 | 25 | 8.0 | 81 | 34 | 10 |



313 SoftFinish® Pozidriv screwdriver.
Short round blade.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.
Standards: ISO 8764, handle acc. to DIN 5268 - style K.
Application: For working in confined spaces.

| Order-No. | ⊕ | → | ● | → | → | → |
|-----------|-----|----|-----|----|----|----|
| 26971 5 | PZ1 | 25 | 4.5 | 81 | 34 | 10 |
| 26972 2 | PZ2 | 25 | 6.0 | 81 | 34 | 10 |
| 26973 9 | PZ3 | 25 | 8.0 | 81 | 34 | 10 |

Screwdriver with mm scale.



NEW
3021 SoftFinish® slotted screwdriver.
Round blade with lasered millimetre scale from 30 to 110 mm.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 7437, DIN 5264, DIN ISO 2380.
Application: Especially for dry and general applications.
Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 30 to 110 mm.

| Order-No. | ⊕ | → | ⊖ | ● | → | → | → |
|-----------|-----|-----|-----|-----|-----|----|----|
| 35397 1 | 5.5 | 125 | 1.0 | 5.5 | 236 | 30 | 10 |



NEW
3111 SoftFinish® Phillips screwdriver.
Round blade with lasered millimetre scale from 20 to 90 mm.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 7437, DIN 5264, DIN ISO 2380.
Application: Especially for dry and general applications.
Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 20 to 90 mm.

| Order-No. | ⊕ | → | ● | → | → | → |
|-----------|-----|-----|-----|-----|----|----|
| 35398 8 | PH2 | 100 | 6.0 | 218 | 36 | 10 |



NEW
3131 SoftFinish® Pozidriv screwdriver.
Round blade with lasered millimetre scale from 20 to 90 mm.
Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.
Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
Standards: DIN 7437, DIN 5264, DIN ISO 2380.
Application: Especially for dry and general applications.
Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 20 to 90 mm.

| Order-No. | ⊕ | → | ● | → | → | → |
|-----------|-----|-----|-----|-----|----|----|
| 35399 5 | PZ2 | 100 | 6.0 | 218 | 36 | 10 |

Wiha SoftFinish®.

The specialist for dry and general applications.



For TORX® screws.



362 SoftFinish® TORX® screwdriver.
Round blade.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 26259 4 | T3 | 60 | 2.5 | 164 | 23 | 10 |
| 26260 0 | T4 | 60 | 2.5 | 164 | 23 | 10 |
| 01285 4 | T5 | 60 | 2.5 | 164 | 23 | 10 |
| 01286 1 | T6 | 60 | 3.5 | 164 | 23 | 10 |
| 01287 8 | T7 | 60 | 3.5 | 164 | 23 | 10 |
| 01288 5 | T8 | 60 | 3.5 | 164 | 23 | 10 |
| 01289 2 | T9 | 60 | 4.0 | 171 | 30 | 10 |
| 01290 8 | T10 | 80 | 4.0 | 191 | 30 | 10 |
| 01291 5 | T15 | 80 | 4.0 | 191 | 30 | 10 |
| 01292 2 | T20 | 100 | 4.0 | 218 | 36 | 10 |
| 01293 9 | T25 | 100 | 4.5 | 218 | 36 | 10 |
| 01294 6 | T27 | 115 | 5.5 | 233 | 36 | 10 |
| 01295 3 | T30 | 115 | 6.0 | 233 | 36 | 10 |
| 01296 0 | T40 | 130 | 7.0 | 254 | 41 | 10 |
| 01297 7 | T45 | 130 | 8.0 | 254 | 41 | 5 |



362BE SoftFinish® TORX® ball end screwdriver.
Hex blade.
 Blade: High-quality chrome-molybdenum steel, through-hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For all hard-to-reach TORX® screws.
 Extra: The TORX® ball end enables fastening and unfastening at an angle of up to 25°.
 With elongated TORX® profile behind ball end.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip | |
|-----------|-------|--------|-------|-----|-----|-----|----|
| 32250 2 | T9 | 60 | 7/64 | 2.8 | 164 | 23 | 10 |
| 32251 9 | T10 | 60 | 1/8 | 3.2 | 184 | 23 | 10 |
| 32252 6 | T15 | 80 | 9/64 | 3.6 | 191 | 30 | 10 |
| 32253 3 | T20 | 80 | 5/32 | 4.0 | 211 | 30 | 10 |
| 32254 0 | T25 | 100 | 3/16 | 4.8 | 218 | 36 | 10 |
| 32255 7 | T27 | 115 | 7/32 | 5.6 | 233 | 36 | 10 |
| 32256 4 | T30 | 115 | 1/4 | 6.4 | 233 | 36 | 10 |

For TORX® and TORX® tamper resistant screws.



362R SoftFinish® TORX® MagicSpring® screwdriver.
Retaining spring holds TORX® screws in place.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and tightening TORX® screws in difficult to access areas.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 27736 9 | T6 | 60 | 3.5 | 164 | 23 | 10 |
| 27737 6 | T7 | 60 | 3.5 | 164 | 23 | 10 |
| 27738 3 | T8 | 60 | 3.5 | 164 | 23 | 10 |
| 27739 0 | T9 | 60 | 4.0 | 171 | 30 | 10 |
| 27740 6 | T10 | 80 | 4.0 | 191 | 30 | 10 |
| 27741 3 | T15 | 80 | 4.0 | 191 | 30 | 10 |
| 27742 0 | T20 | 100 | 4.0 | 218 | 36 | 10 |
| 27743 7 | T25 | 100 | 4.5 | 218 | 36 | 10 |
| 27811 3 | T27 | 115 | 5.5 | 233 | 36 | 10 |
| 27744 4 | T30 | 115 | 6.0 | 233 | 36 | 10 |
| 27745 1 | T40 | 130 | 7.0 | 254 | 41 | 10 |



362TR SoftFinish® TORX® Tamper Resistant screwdriver.
With borehole in the blade tip.
For TORX® screws with locking pin.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 With borehole in the blade tip.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.


| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 03106 0 | T7H | 60 | 3.5 | 164 | 23 | 10 |
| 03107 7 | T8H | 60 | 3.5 | 164 | 23 | 10 |
| 03108 4 | T9H | 60 | 4.0 | 171 | 30 | 10 |
| 26456 7 | T9H | 300 | 4.0 | 411 | 30 | 5 |
| 01300 4 | T10H | 80 | 4.0 | 191 | 30 | 10 |
| 26457 4 | T10H | 300 | 4.0 | 411 | 30 | 5 |
| 01301 1 | T15H | 80 | 4.0 | 191 | 30 | 10 |
| 26458 1 | T15H | 300 | 4.0 | 411 | 30 | 5 |
| 01302 8 | T20H | 100 | 4.0 | 211 | 30 | 10 |
| 28005 5 | T20H | 300 | 4.0 | 411 | 30 | 5 |
| 01303 5 | T25H | 100 | 4.5 | 211 | 30 | 10 |
| 01304 2 | T27H | 115 | 5.5 | 233 | 36 | 10 |
| 01305 9 | T30H | 115 | 6.0 | 233 | 36 | 10 |
| 01306 6 | T40H | 130 | 7.0 | 254 | 41 | 10 |

For TORX PLUS® and Allen screws.



362IP SoftFinish® TORX PLUS® screwdriver.
Round blade.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 26091 0 | 6IP | 60 | 3.5 | 164 | 23 | 10 |
| 26093 4 | 7IP | 60 | 3.5 | 164 | 23 | 10 |
| 26095 8 | 8IP | 60 | 3.5 | 164 | 23 | 10 |
| 26097 2 | 9IP | 60 | 4.0 | 171 | 30 | 10 |
| 26099 6 | 10IP | 80 | 4.0 | 191 | 30 | 10 |
| 26101 6 | 15IP | 80 | 4.0 | 191 | 30 | 10 |
| 26103 0 | 20IP | 100 | 4.0 | 218 | 36 | 10 |
| 26105 4 | 25IP | 100 | 4.5 | 218 | 36 | 10 |
| 26107 8 | 27IP | 115 | 5.5 | 233 | 36 | 10 |
| 26109 2 | 30IP | 115 | 6.0 | 233 | 36 | 10 |
| 26111 5 | 40IP | 130 | 7.0 | 254 | 41 | 10 |



362RIP SoftFinish® TORX PLUS® MagicSpring® screwdriver.
Retaining spring holds TORX PLUS® screws in place.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and tightening TORX PLUS® screws in hard to reach areas.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 28760 3 | 6IP | 60 | 3.5 | 164 | 23 | 10 |
| 28761 0 | 7IP | 60 | 3.5 | 164 | 23 | 10 |
| 28762 7 | 8IP | 60 | 3.5 | 164 | 23 | 10 |
| 28763 4 | 9IP | 60 | 4.0 | 171 | 30 | 10 |
| 28764 1 | 10IP | 80 | 4.0 | 191 | 30 | 10 |
| 28765 8 | 15IP | 80 | 4.0 | 191 | 30 | 10 |
| 28766 5 | 20IP | 100 | 4.0 | 218 | 36 | 10 |
| 28767 2 | 25IP | 100 | 4.5 | 218 | 36 | 10 |
| 28768 9 | 27IP | 115 | 5.5 | 233 | 36 | 10 |
| 28769 6 | 30IP | 115 | 6.0 | 233 | 36 | 10 |
| 28770 2 | 40IP | 130 | 7.0 | 254 | 41 | 10 |



356 SoftFinish® hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 32264 9 | 1.5 | 60 | 164 | 23 | | 10 |
| 32265 6 | 2.0 | 60 | 164 | 23 | | 10 |
| 26190 0 | 2.5 | 75 | 179 | 23 | | 10 |
| 26191 7 | 3 | 75 | 179 | 23 | | 10 |
| 26192 4 | 4 | 75 | 186 | 30 | | 10 |
| 26193 1 | 5 | 75 | 186 | 30 | | 10 |
| 26194 8 | 6 | 100 | 218 | 36 | | 10 |
| 26195 5 | 8 | 100 | 218 | 36 | | 10 |

For hex socket screws.



367 SoftFinish® ball end hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For all screws that are difficult to access.
 Extra: The ball end enables the user to work at angles up to 25°.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 26303 4 | 1.5 | 75 | 179 | 23 | | 10 |
| 26304 1 | 2 | 100 | 204 | 23 | | 10 |
| 26305 8 | 2.5 | 100 | 204 | 23 | | 10 |
| 26328 7 | 3 | 100 | 204 | 23 | | 10 |
| 26329 4 | 4 | 100 | 211 | 30 | | 10 |
| 26330 0 | 5 | 100 | 211 | 30 | | 10 |
| 26331 7 | 6 | 125 | 243 | 36 | | 10 |
| 26332 4 | 8 | 150 | 268 | 36 | | 10 |
| 26333 1 | 10 | 150 | 271 | 41 | | 5 |
| 26307 2 | 12 | 150 | 271 | 41 | | 5 |



367R SoftFinish® MagicRing® ball end hex screwdriver.
Ring made of spring steel holds hex screws in place.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and turning screws in difficult to access areas.
 Extra: The ball end enables the user to work at angles up to 25°.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 26077 4 | 3 | 100 | 204 | 23 | | 10 |
| 26079 8 | 4 | 100 | 211 | 30 | | 10 |
| 26081 1 | 5 | 100 | 211 | 30 | | 10 |
| 26083 5 | 6 | 125 | 243 | 36 | | 10 |
| 26085 9 | 8 | 150 | 268 | 36 | | 10 |
| 26087 3 | 10 | 150 | 271 | 41 | | 5 |



357 SoftFinish® offset hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Ideal for high-torque applications, e.g. in workshops.

| Order-No. | Blade | Length | Width | Tip | Tip | Tip |
|-----------|-------|--------|-------|-----|-----|-----|
| 26230 3 | 3 | 35 | 20 | 139 | 23 | 10 |
| 26231 0 | 4 | 40 | 25 | 151 | 30 | 10 |
| 26232 7 | 5 | 45 | 28 | 156 | 30 | 10 |
| 26233 4 | 6 | 50 | 32 | 168 | 36 | 10 |
| 26234 1 | 8 | 60 | 36 | 178 | 36 | 10 |
| 26235 8 | 10 | 70 | 40 | 199 | 41 | 10 |



► See VDE tools, page 228 – 237

Wiha SoftFinish®.

The specialist for dry and general applications.

For hex nuts.



341 SoftFinish® hex nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: Especially for dry and general applications.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|-----|-----|-----|----|------|---|----|
| 01018 8 | 4 | 125 | 236 | 30 | 6.9 | | 10 |
| 01020 1 | 5 | 125 | 236 | 30 | 7.9 | | 10 |
| 01021 8 | 5.5 | 125 | 236 | 30 | 7.9 | | 10 |
| 01022 5 | 6 | 125 | 236 | 30 | 8.9 | | 10 |
| 01023 2 | 7 | 125 | 243 | 36 | 10.9 | | 10 |
| 01024 9 | 8 | 125 | 243 | 36 | 11.9 | | 10 |
| 01025 6 | 9 | 125 | 243 | 36 | 12.9 | | 10 |
| 01026 3 | 10 | 125 | 243 | 36 | 14.4 | | 10 |
| 01027 0 | 11 | 125 | 249 | 41 | 15.9 | | 5 |
| 01028 7 | 12 | 125 | 249 | 41 | 16.9 | | 5 |
| 01029 4 | 13 | 125 | 249 | 41 | 18.4 | | 5 |
| 01030 0 | 14 | 125 | 249 | 41 | 19.4 | | 5 |
| 01031 7 | 15 | 125 | 249 | 41 | 21.9 | | 5 |
| 01032 4 | 16 | 125 | 249 | 41 | 21.9 | | 5 |
| 01033 1 | 17 | 125 | 249 | 41 | 23.4 | | 5 |



347 SoftFinish® hex nut driver.
Round blade with hex bolster.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: Especially for dry and general applications.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|----|-----|----|-----|----|------|----|
| 01092 8 | 7 | 125 | 10 | 238 | 36 | 11.0 | 10 |
| 01093 5 | 8 | 125 | 10 | 238 | 36 | 12.0 | 10 |
| 01094 2 | 9 | 125 | 10 | 238 | 36 | 13.0 | 10 |
| 01095 9 | 10 | 125 | 10 | 238 | 36 | 14.5 | 10 |
| 01096 6 | 11 | 125 | 13 | 246 | 41 | 16.0 | 5 |
| 01097 3 | 12 | 125 | 13 | 246 | 41 | 17.0 | 5 |
| 01098 0 | 13 | 125 | 13 | 246 | 41 | 19.0 | 5 |

347 Zoll SoftFinish® hex nut driver. Inch sizes.

Round blade with hex bolster.
 Blade: Chrome-vanadium steel, through hardened, nickel-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

| Order-No. | Ø | → | ← | → | ← | mm | → | ← |
|-----------|------|-----|----|-----|----|-------|----|----|
| 02836 7 | 3/16 | 125 | 10 | 231 | 30 | 4.76 | 8 | 10 |
| 02837 4 | 1/4 | 125 | 10 | 238 | 36 | 6.35 | 10 | 10 |
| 02838 1 | 5/16 | 125 | 10 | 238 | 36 | 7.94 | 12 | 10 |
| 02839 8 | 3/8 | 125 | 10 | 238 | 36 | 9.53 | 14 | 10 |
| 02840 4 | 7/16 | 125 | 13 | 246 | 41 | 11.11 | 16 | 10 |
| 02841 1 | 1/2 | 125 | 13 | 246 | 41 | 12.70 | 19 | 10 |

For hex and triangular nuts.



343 SoftFinish® hex nut driver.
Short round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For working in confined spaces.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|-----|----|-----|----|----|---|----|
| 01076 8 | 5.5 | 65 | 176 | 30 | 8 | | 10 |
| 01077 5 | 6 | 65 | 176 | 30 | 9 | | 10 |
| 01078 2 | 7 | 65 | 183 | 36 | 11 | | 10 |
| 01079 9 | 8 | 65 | 183 | 36 | 12 | | 10 |
| 01081 2 | 10 | 65 | 183 | 36 | 14 | | 10 |



372 SoftFinish® hex nut driver.
Flexible shaft for hard to reach areas.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: E.g. for tightening and loosening adjustable hose clamps.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|-----|-----|-----|----|----|---|----|
| 01435 3 | 5 | 150 | 261 | 30 | 8 | | 10 |
| 01436 0 | 5.5 | 150 | 261 | 30 | 8 | | 10 |
| 01437 7 | 6 | 150 | 261 | 30 | 9 | | 10 |
| 01438 4 | 7 | 150 | 268 | 36 | 11 | | 10 |
| 01439 1 | 8 | 150 | 268 | 36 | 12 | | 10 |
| 01440 7 | 10 | 175 | 293 | 41 | 14 | | 10 |
| 01443 8 | 13 | 175 | 293 | 41 | 19 | | 5 |



344 SoftFinish® triangular nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 22416.
 Application: For triangular screws DIN 22424 and triangular nuts DIN 22425.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|-----|-----|-------|-----|----|----|----|
| 26212 9 | M4 | 125 | 6.8 | 236 | 30 | 11 | 10 |
| 26213 6 | M5 | 125 | 8.3 | 236 | 30 | 13 | 10 |
| 26216 7 | M6 | 125 | 10.05 | 236 | 30 | 16 | 10 |
| 26214 3 | M8 | 125 | 12.05 | 243 | 36 | 18 | 10 |
| 26217 4 | M10 | 125 | 15.05 | 243 | 36 | 22 | 10 |
| 26218 1 | M12 | 125 | 16.55 | 249 | 41 | 24 | 10 |

For slotted nuts. Sets with round blades.




305 SoftFinish® slotted nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: For nuts DIN 546.

| Order-No. | Ø | → | ← | → | ← | → | ← |
|-----------|------|-----|-----|------|-----|----|---|
| 32364 6 | M1.7 | 80 | 0.5 | 4.0 | 184 | 23 | 5 |
| 32363 9 | M2 | 80 | 1.0 | 4.5 | 184 | 23 | 5 |
| 32362 2 | M2.3 | 90 | 1.0 | 5.0 | 201 | 30 | 5 |
| 32361 5 | M2.6 | 90 | 1.2 | 5.5 | 201 | 30 | 5 |
| 32360 8 | M3 | 100 | 1.2 | 6.0 | 211 | 30 | 5 |
| 32358 5 | M3.5 | 100 | 1.4 | 7.0 | 218 | 36 | 5 |
| 32359 2 | M4 | 100 | 1.4 | 8.0 | 218 | 36 | 5 |
| 32357 8 | M5 | 125 | 2.0 | 10.0 | 243 | 36 | 5 |
| 32356 1 | M6 | 125 | 2.5 | 11.0 | 243 | 36 | 5 |
| 32355 4 | M8 | 150 | 3.0 | 14.0 | 274 | 41 | 5 |
| 32354 7 | M10 | 150 | 3.5 | 18.0 | 274 | 41 | 5 |



302 HK6 SO SoftFinish® slotted/ Phillips screwdriver set, 6 pcs.
Round blades.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

| Order-No. | Series | → | ← | | |
|-----------|------------|---------|---------|---------|---------|
| 07152 3 | 302 HK6 SO | | 1 | | |
| Ⓢ | 302 | 3.5x100 | 4.5x125 | 5.5x150 | 6.5x150 |
| ⊕ | 311 | PH1x80 | PH2x100 | | |



302 ZK6 SO SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs.
Round blades.

| Order-No. | Series | → | ← | | |
|-----------|------------|---------|---------|---------|---------|
| 07153 0 | 302 ZK6 SO | | 1 | | |
| Ⓢ | 302 | 3.5x100 | 4.5x125 | 5.5x150 | 6.5x150 |
| ⊕ | 313 | PZ1x80 | PZ2x100 | | |

Sets with round blades.



311 K6 SoftFinish® Phillips/ Pozidriv screwdriver set, 6 pcs.
Round blades.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

| Order-No. | Series | → | ← | |
|-----------|--------|--------|---------|---------|
| 26146 7 | 311 K6 | | 1 | |
| Ⓢ | 311 | PH1x80 | PH2x100 | PH3x150 |
| ⊕ | 313 | PZ1x80 | PZ2x100 | PZ3x150 |



302 HK6 01 SoftFinish® slotted/Phillips/ Pozidriv screwdriver set, 6 pcs.
Round blades.

| Order-No. | Series | → | ← | |
|-----------|------------|---------|---------|---------|
| 26113 9 | 302 HK6 01 | | 1 | |
| Ⓢ | 302 | 4.0x100 | 5.5x125 | 6.5x150 |
| ⊕ | 311 | PH1x80 | PH2x100 | |
| ⊕ | 313 | PZ2x100 | | |

Wiha SoftFinish®.

The specialist for dry and general applications.



► See VDE tools,
page 228 – 237

Sets with hex blades.



308 HK6 SoftFinish® slotted/ Phillips screwdriver set, 6 pcs. Hex blades with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

| Order-No. | Series | | | | | |
|-----------|---------|--------|---------|---------|---------|---|
| 21248 3 | 308 HK6 | | | | | 1 |
| ⓪ | 308 | 3.5x75 | 4.5x90 | 5.5x100 | 7.0x125 | |
| ⊕ | 312 | PH1x80 | PH2x100 | | | |



308 ZK6 SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs. Hex blades with hex bolster.

| Order-No. | Series | | | | | |
|-----------|---------|--------|---------|---------|---------|---|
| 21249 0 | 308 ZK6 | | | | | 1 |
| ⓪ | 308 | 3.5x75 | 4.5x90 | 5.5x100 | 7.0x125 | |
| ⊕ | 314 | PZ1x80 | PZ2x100 | | | |

Sets with steel caps. Nut driver set.



530 HK6 SoftFinish® slotted/ Phillips screwdriver set, 6 pcs. Hex blades with hex bolster, solid steel cap.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

| Order-No. | Series | | | | | |
|-----------|---------|--------|---------|---------|---------|---|
| 21250 6 | 530 HK6 | | | | | 1 |
| ⓪ | 530 | 3.5x75 | 4.5x90 | 5.5x100 | 6.5x125 | |
| ⊕ | 531 | PH1x80 | PH2x100 | | | |



530 ZK6 SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs. Hex blades with hex bolster, solid steel cap.

| Order-No. | Series | | | | | |
|-----------|---------|--------|---------|---------|---------|---|
| 21251 3 | 530 ZK6 | | | | | 1 |
| ⓪ | 530 | 3.5x75 | 4.5x90 | 5.5x100 | 6.5x125 | |
| ⊕ | 532 | PZ1x80 | PZ2x100 | | | |



341 K5 SoftFinish® hex nut driver set, 5 pcs. Round blades.

Blade: Chrome-vanadium steel, through hardened, chrome-plated. Deep drawn socket.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

| Order-No. | Series | | | | |
|-----------|--------|---------|--------|-------|---|
| 01034 8 | 341 K5 | | | | 1 |
| ⊙ | 341 | 5.5x125 | 7x125 | 8x125 | |
| | | 10x125 | 13x125 | | |

TORX® sets.



362 K6 S0 SoftFinish® TORX® screwdriver set, 6 pcs. Round blades.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

| Order-No. | Series | | | | | |
|-----------|-----------|---------|---------|---------|--|---|
| 07155 4 | 362 K6 S0 | | | | | 1 |
| ⊙ | 362 | T10x80 | T15x80 | T20x100 | | |
| | | T25x100 | T30x115 | T40x130 | | |



362 K7 SoftFinish® TORX® screwdriver set, 7 pcs. Round blades.

| Order-No. | Series | | | | | |
|-----------|--------|---------|---------|---------|--------|---|
| 01299 1 | 362 K7 | | | | | 1 |
| ⊙ | 362 | T8x60 | T9x60 | T10x80 | T15x80 | |
| | | T20x100 | T25x100 | T30x115 | | |



362BE K6 SoftFinish® TORX® ball end screwdriver set, 6 pcs. Hex blade.

Blade: High-quality chrome-molybdenum steel, through-hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For all hard-to-reach TORX® screws.

Extra: The TORX® ball end enables fastening and unfastening at an angle of up to 25°.

With elongated TORX® profile behind ball end.

| Order-No. | Series | | | | |
|-----------|----------|--------|---------|---------|---|
| 32249 6 | 362BE K6 | | | | 1 |
| ⊙ | 362BE | T9x60 | T10x60 | T15x80 | |
| | | T20x80 | T25x100 | T30x115 | |

Sets.



362R K6 S0 SoftFinish® TORX® MagicSpring® screwdriver set, 6 pcs. Retaining spring holds TORX® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and tightening TORX® screws in difficult to access areas.

| Order-No. | Series | | | | | |
|-----------|------------|---------|---------|---------|--|---|
| 27746 8 | 362R K6 S0 | | | | | 1 |
| ⊙ | 362R | T10x80 | T15x80 | T20x100 | | |
| | | T25x100 | T30x115 | T40x130 | | |



362 K6 01 SoftFinish® Pozidriv/ TORX® screwdriver set, 6 pcs. Round blades.

| Order-No. | Series | | | | | |
|-----------|-----------|--------|---------|---------|---------|---|
| 26114 6 | 362 K6 01 | | | | | 1 |
| ⊕ | 313 | PZ1x80 | PZ2x100 | | | |
| ⊙ | 362 | T10x80 | T15x80 | T20x100 | T25x100 | |



362TR K6 SoftFinish® TORX® Tamper Resistant screwdriver set, 6 pcs. For TORX® screws with locking pin.

| Order-No. | Series | | | | | |
|-----------|----------|----------|----------|----------|--|---|
| 24506 1 | 362TR K6 | | | | | 1 |
| ⊙ | 362TR | T10Hx80 | T15Hx80 | T20Hx100 | | |
| | | T25Hx100 | T30Hx115 | T40Hx130 | | |