

# Automobile Rocker Switch

**Q-10228**



**TYPE: R13-203L**  
**Rocker**




## SPECIFICATIONS

Rating: 25A 12V DC  
 Contact R: 50mΩ max  
 Insulation R: 500V DC 100MΩ min  
 Dielectric Strength: 1 Minute 1500V AC  
 Operating Temperature: -25°C ~ +85°C  
 Electrical Life: 10, 000 Cycles

Outline Drawing



Mounting



Circuitry

