

## RVUTT01 Connectivity Accessories - REVConnect Termination Tool



For more Information  
please call

1-800-Belden1

### General Description:

REVConnect Universal Termination Tool

### Usage (Overall)

**Suitable Applications:** To terminate REVConnect Jacks and Plugs

### Physical Characteristics (Connectivity)

#### Dimensions

**Dimensions:**

Height (mm)	Width (mm)	Length (mm)
150.114	117.348	34.290

#### Materials

**Materials:**

Description	Material	Color
Frame	Aluminum	
Handle grip	Plastic	Black
Blade Block	Steel	
Blades & Knives	Steel	
Press Head	Nickel plated zinc alloy diecast	

#### Color

**Color:** Blue

#### Weight

**Weight:** 0.295 kg

#### Packaging

**Packaging:** Individually packaged in a plastic clamshell, shipped in cardboard box (40/Box)

### Mechanical Characteristics (Connectivity)

**Termination Interface:**

Connection Durabilities	
Blades	20000
Handle	40000

**Storage Temperature Range:** -40°C To +60°C

**Installation Temperature Range:** -10°C To +50°C

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

**EU Directive 2011/65/EU (ROHS II):** Yes

#### Suitability

**Suitability - Indoor:** Yes - Indoor

### Notes (Overall)

#### Product Family

**Part Number List:**

Accessory	Part Number
Termination Tool	RVUTT01
Cable Preparation Tool	RVUCT01
Belt Clip	RVUTC01
Spare Blades	RVUTB01
Installation Tool Case	RVUTIK01

## RVUTT01 Connectivity Accessories - REVConnect Termination Tool

Carrying Tool Case	RVUTCC01
REVConnect Cores 50 Pack	RVUCOEW-B50

### Physical Properties (Overall)

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
RVUTT01	1 EA	0.789 LB		Q	REVConn Univ Term Tool

**Notes:**

Q = STANDARD PACKAGES CANNOT BE BROKEN.

Revision Number: 0    Revision Date: 09-12-2016

© 2020 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.