

**6M Double open-end spanner, Metric**

DIN 3110/ISO 1085.

**Finish:** Nickel and chrome-plated, fine-polished.

Sizes 41-46 mm and 46-50 mm nickel and chrome-plated.

**Material:** VANADIUM-EXTRA. Angle 15°.

Model with extremely flat heads.



Product code	EAN 731415+			L mm	a mm	b1 mm	b2 mm	
6M-4-5	1832018	10	4x5	100	3.1	13.5	15.5	14
6M-4.5-5.5	1832025	10	4.5x5.5	100	3.1	13.5	15.5	15
6M-5-5.5	1832032	10	5x5.5	100	3.1	13.5	15.5	15
6M-5.5-7	1832049	10	5.5x7	122	3.4	16.5	18.5	20
6M-6-7	1832056	10	6x7	122	3.4	16.5	18.5	21
6M-7-8	1832063	10	7x8	130	3.4	17.5	20.5	21
6M-8-9	1832070	10	8x9	140	3.7	21.0	22.5	31
6M-8-10	1832087	10	8x10	145	3.7	21.0	24.5	34
6M-10-11	1832094	10	10x11	157	4.0	24.0	28.0	46
6M-10-12	1832100	10	10x12	157	4.0	24.0	28.0	46
6M-10-13	1832117	10	10x13	172	4.5	26.0	31.5	67
6M-12-13	1832131	10	12x13	172	4.5	28.5	31.5	59
6M-12-14	1832148	10	12x14	172	4.5	28.5	32.0	67
6M-13-14	1832155	10	13x14	180	4.5	31.0	32.0	65
6M-13-15	1832162	10	13x15	190	4.8	31.0	35.0	87
6M-13-16	1832179	10	13x16	190	5.0	33.5	36.5	95
6M-13-17	1832186	10	13x17	205	5.5	32.5	39.0	100
6M-14-15	1832193	10	14x15	190	4.8	32.5	35.0	83
6M-14-17	1832209	10	14x17	205	5.5	32.5	39.0	110
6M-16-17	1832216	10	16x17	205	5.5	36.5	39.0	125
6M-16-18	1832223	10	16x18	205	5.8	36.5	41.0	112
6M-17-19	1832230	10	17x19	222	5.8	40.5	43.0	152
6M-18-19	1832247	10	18x19	222	5.8	41.0	43.0	159
6M-18-21	1832254	10	18x21	236	6.3	41.0	46.5	193
6M-19-22	1832261	10	19x22	236	6.3	45.0	51.5	195
6M-19-24	1832278	10	19x24	250	6.8	45.0	51.5	240
6M-20-22	1832285	10	20x22	236	6.3	45.0	48.5	198
6M-21-23	1832292	10	21x23	245	6.8	46.5	50.5	230
6M-21-24	1838072	10	21x24	250	7.4	47.5	54.0	250
6M-22-24	1832308	10	22x24	266	7.4	48.5	53.0	270
6M-24-26	1832315	10	24x26	266	7.4	53.0	56.0	280
6M-24-27	1832322	10	24x27	275	8.0	55.0	58.0	360
6M-24-30	1832339	5	24x30	280	8.0	53.0	64.0	360
6M-25-28	1832353	5	25x28	280	8.0	55.0	59.0	340
6M-27-30	1832360	5	27x30	300	8.6	58.0	61.5	430
6M-27-32	1832377	5	27x32	300	8.6	58.0	65.0	420
6M-30-32	1832384	5	30x32	300	8.6	64.0	68.5	440
6M-30-34	1838089	5	30x34	330	9.5	64.0	73.0	600
6M-30-36	1832407	5	30x36	330	10.0	64.0	73.0	700
6M-32-36	1832414	5	32x36	345	10.0	68.5	74.5	740
6M-34-36	1832421	1	34x36	345	10.0	69.0	72.0	725
6M-36-41	1832438	1	36x41	395	11.8	77.5	85.5	1020
6M-38-42	1832445	1	38x42	395	11.8	75.0	83.0	1030
6M-41-46	1832452	1	41x46	400	13.3	85.0	94.0	1120
6M-46-50	1832469	1	46x50	446	14.2	94.0	100.5	1610

**6M/6Z-Set Double open-end spanner, Metric or Inch**

DIN 3110/ISO 1085.

**Finish:** Nickel and chrome-plated, fine-polished.**Material:** VANADIUM-EXTRA.

Angle 15°. Model with extremely flat heads. In plastic clip.

**6M/S8** in attractive sales cardboard box. **6M/SH6** and **6M/SH12** on detachable spanner rack, with locking device.

Product code	EAN 731415+				L mm / inch	
6M/8T	1832476	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	735	
6M/10T	1832490	1	10	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32	1570	
6M/12T	1832506	1	12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	2070	
6Z/8T	1832704	1	8	1/4x5/16 5/16x11/32 3/8x7/16 1/2x9/16 19/32x11/16 5/8x3/4 13/16x7/8 15/16x1	1005	
6M/SH 6	3013262	1	6	8x9 10x11 12x13 14x15 16x17 18x19	553	
6M/SH1	3013439	1	12	6x7 8x9 10x11 12x13 13x17 14x15 16x17 18x19 19x22 20x22 21x23 24x27	1704	

**6Z Double open-end spanner, Inch**

DIN 3110/ISO 1085.

**Finish:** Nickel and chrome-plated, fine-polished.**Material:** VANADIUM-EXTRA.

Angle 15°. Model with extremely flat heads.



Product code	EAN 731415+			L mm	a mm	b1 mm	b2 mm	
6Z-1/4-5/16	1832520	5	1/4x5/16	130	3.4	17.0	20.0	21
6Z-5/16-11/32	1832537	5	5/16x11/32	140	3.7	21.0	24.5	33
6Z-3/8-7/16	1832544	5	3/8x7/16	157	4.0	24.0	28.0	46
6Z-7/16-1/2	1832551	5	7/16x1/2	172	4.3	27.5	31.5	66
6Z-1/2-9/16	1832568	5	1/2x9/16	180	4.5	30.0	34.0	82
6Z-9/16-5/8	1832575	5	9/16x5/8	190	5.0	31.0	35.0	88
6Z-19/32-11/16	1832582	5	19/32x11/16	205	5.3	34.0	39.0	113
6Z-5/8-3/4	1832605	5	5/8x3/4	205	5.8	39.0	43.0	156
6Z-11/16-3/4	1832612	5	11/16x3/4	222	5.8	39.0	43.0	147
6Z-3/4-7/8	1832629	5	3/4x7/8	236	6.3	42.0	48.0	190
6Z-25/32-13/16	1832636	5	25/32x13/16	236	6.3	45.5	50.0	230
6Z-13/16-7/8	1832643	5	13/16x7/8	245	6.8	45.0	50.0	235
6Z-7/8-15/16	1832650	5	7/8x15/16	266	7.4	51.5	55.0	305
6Z-15/16-1	1832667	5	15/16x1	266	7.4	52.0	55.0	280
6Z-1-1/8	1832674	1	1x1/8	280	8.0	54.0	59.0	340
6Z-1-1/16-1-1/4	1832681	1	1 1/16x1 1/4	300	8.6	58.0	65.0	430
6Z-1-1/4-1-3/8	1832698	1	1 1/4x1 3/8	345	10.0	67.0	72.0	720