



SPECIFICATION

1. Rated Voltage 5 VDC
2. Operating Voltage 4~8 VDC
3. Max. Rated Current 40mA/5VDC
4. Min. Sound Pressure Level 88dB/10cm
5. Resonant Frequency 2300±300Hz
6. Response Time 100ms
7. Case Material PPS/Black
8. Operating Temperature -20~+70°C
9. Store Temperature -30~+80°C
10. Weight 2g

				KEPO NINGBO KEPO ELECTRONIC CO.,LTD http://www.chinaacoustic.com	
No.	DESCRIPTION	MENDER	DATE	Magnetic Buzzer QUARTZ-1 SMA-1392-2956	
TOLERANCES UNLESS NOTED OTHERWISE X * .XX * .XXX * 90° FORMED +2° ANGLES -1°		APPROVALS	DATE	UNIT	DWG NO.
FIRST ANGLE PROJECTION		DRAWN 梅海江	08.05.22	mm	OEM2956
APPROVED		CHECKED		SCALE	SHEET
				NOT TO SCALE	VER 1.0