

MNX ABS 150/100 HG



Sample photo

Order symbol: ABS 150/100 HG
Product nbr: 6081315
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022950
EI. number:
 Finland: 3420555
 Electric No. 8212023288
 Denmark:
 Electric No. Italy: 7361100
 Electric No. Sweden: 2535757

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	180	130	100	MIN 10 DIN-15 Mounting rail
inch:	7.1	5.1	3.9	MIN 15 DIN-15 Mounting rail

Materials:		
Material:	ABS	FP A 150/180 Front plate (Aluminium)
Base colour:	RAL 7035 -light grey	HFP 180 Front plate hinge series
Cover screws material:	Polyamide	FP 22046 Wall fastening lug (4 pcs)
Cover colour:	RAL 7035 -light grey	
Cover screws colour:	Grey	
Gasket material:	TPE	

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
Flammability Rating: UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6

Accessories:	
MIV 150	Mounting plate (Galvanized steel)

Certificates:
SGS Fimko
Gost R

