

FMA8005AS-M



80X80X16

0.60~1.028 M³/MIN

MATERIAL

Fame	Plastic PBT 94V0
Impeller	Plastic PBT 94V0
Lead Wire	AWG26"+ " Red "-" Black Standard JL 1007
Option	Signal output
Bearing	Sleeve Bearing

Dimensions in mm



Model	FMA8005AS-M
Rated Voltage DCV	5
Operating Voltage DCV	5.0-6.5
Rated Input W	1.25
Rated Current A	0.18
Operating Temperature °C	-10~70
Storage Temperature °C	-40~70
Speed RPM	2100
Max, Air Flow M ³ /Min(CFM)	0.60(21.2)
Max, Air Pressure mmH2O	1.88
Noise DB	29
Bearing	○
Weight (g)	APPROX.76

○: Sleevebearing