

2020



PROFESSIONAL QUALITY BITS



TIP PROFILES

-  Slotted
-  Phillips
-  Torx®
-  Security Torx®
-  Hex/Ball End/MagicRing
-  Security Hex
-  Nut Driver
-  Pozidriv®
-  Square
-  Tri-Wing
-  Spanner
-  Torq Set
-  TorxPlus®
-  Security TorxPlus®
-  Xeno Phillips
-  Security Pentalobe 5Point

COMPLETE BITS PROGRAM



Terminator Impact Insert & Power Bits

DESCRIPTION	Page
 Terminator Impact Bits	4-10

Cutting Tools

DESCRIPTION	Page
 Counter Sink	30
 Drill Bit	30




Standard Contractor Bits

DESCRIPTION	Page
 Torx® Insert/Power Bits	11-13
 Phillips Insert/Power Bits	19-20
 Hex Metric & Inch Insert/Power Bits	21-22
 Square Insert/Power Bits	26
 Slotted Insert/Power Bits	26-27
 Pozidriv® Insert/Power Bits	28
 Nut Setters	49

Insert & Power Bit Sets

DESCRIPTION	Page
 Security Bits Collector	37
 26inOne Ultra Drivers	32-34
 Insert Bit Selectors	36
 XSelector/XLSelectors	38
 Stubby Bit Holder Sets	35
 Pop-Up Bit Holder Sets	35
 Ratchet Bit Sets	36,41
 Power Bit Belt Packs	39

Specialty Bits

DESCRIPTION	Page
 Xeno Phillips Terminal Block	30
 Torx® Align Bits	18
 Security Torx® Insert/Power Bits	14-15
 TorxPlus® Insert/Power Bits	16-17
 Ball End Torx®	17
 Security Pentalobe	17
 Security Hex Triple Square Insert Bits	23
 XZN Insert	30
 Tri-Wing Insert/Power Bits	29
 Torq Set Insert/Power Bits	29
 Spanner	30

Power Blades & Sets

DESCRIPTION	Page
 Power Blades 15,20,25,28,31,48 Slotted/Phillips/Security Torx® & Hex TriWing/Square/Spanner/Pozidriv®	31,48
 Power Blade Sets	31,48

ESD 1/4" Quick Release Bit Holder Blade Set



DESCRIPTION Page

1/4" Quick Release 41

TorqueControl Insert & Micro Bit Sets



DESCRIPTION Page

TorqueControl Bit Sets 39

ESD Safe Micro Bit Handles/Bits & Sets

DESCRIPTION Page



Micro Bits 42-47



ESD Safe Micro Bit Sets 45-47

Bit Holders

DESCRIPTION Page



ESD Safe Bit Holders 41



SoftFinish®
Cushion Grip 40



MicroFinish
Non-Slip Grip 40



T-handle 40



SoftGrip Stubby Bit Holder 40



Flexible Shaft Bit Holder 40



Drive-Loc VI Bit Holder 40

Bit Holders

DESCRIPTION Page



Micro Bit Power Tool Adapter 44



ClicFix Quick Release
Insert Bits 41




CentroFix Quick Release
All 1/4" Drive Tools 41




Protturn Quick Release
1/4" Drive 40



Stainless Steel Bit Holder 41



Magnetic Bit Holders &
Retaining Ring Bit Holder 41



"SlimFix" Impact Bit Holder
Quick Release 40

Bit Sockets

DESCRIPTION Page



Torx® 1/4" Drive 50



Torx® 3/8" Drive 50



Torx® 3/8" - 5/16" Bits 50




Security Torx® 3/8" 50



Slotted Bit Sockets 1/2" Drive 50



Phillips Bit Socket 1/2" Drive 50




Hex Bit Sockets 1/4" Drive 51



Hex Bit Sockets 3/8" Drive 51




Ball End Hex Sockets 51




Socket Adapters 51



Impact Bit Holding Sockets 52



6" Bit Sockets 1/4" & 3/8" Drive 52



Socket Sets 53-54

Wiha Terminator Impact Bits

Up To 30X Performance Over Standard Screwdriver Bits



Dual material
impact absorbing
torsion zone

Special energy absorbing dual
material design

Tough impact absorbing torsional zone

Up to 30 times performance over
standard bits

Precision heat treated & premium
CVM tool steel

No special bit holder required

Standard 1/4" drive

Ready For Sudden Impact!



76886 Terminator Impact Bit Buddy Set, 34 Pc. Impact Bit Set Includes:

29mm Insert Bits

⊕ Phillips: #2, 3 ⊖ Square: #2, 3

⊗ TORX®: T20, T25, T30

⬢ Hex Metric: 4.0, 5.0, 6.0mm

⬢ Hex Inch: 5/32, 3/16, 7/32, 1/4"

49mm Insert Bits

⊕ Phillips: #2, 3 ⊖ Square: #2, 3

⊗ TORX®: T20, T25, T30

⬢ Hex Metric: 4.0, 5.0, 6.0mm

⬢ Hex Inch: 5/32, 3/16, 7/32, 1/4"

2 Magnetic Bit Holders 1/4" x 59mm

2 SlimFix Locking Bit Holders

2 Belt Clips For Bit Buddy Cases

⚖ lbs. 1.56

Wiha Accessory Bag



91473 General Purpose Zipper Bag

Heavy duty nylon. Keeps Wiha tools &
accessories organized.

Item	
No.	Size
91473	9.75" x 7.25"



765 Phillips Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	No.	Size	mm	pkg.
⊕	76501	1	29	10
⊕	76502	2	29	10
⊕	76503	3	29	10

768 Phillips Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	No.	Size	mm	pkg.
⊕	76801	1	29	2
⊕	76802	2	29	2
⊕	76803	3	29	2



765 Pozidriv® Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	No.	Size	mm	pkg.
⊕	76506	1	29	10
⊕	76507	2	29	10
⊕	76508	3	29	10

768 Pozidriv® Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	No.	Size	mm	pkg.
⊕	76806	1	29	2
⊕	76807	2	29	2
⊕	76808	3	29	2



765 Square Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	No.	Size	mm	pkg.
⊖	76538	1	29	10
⊖	76539	2	29	10
⊖	76540	3	29	10

768 Square Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	No.	Size	mm	pkg.
⊖	76838	1	29	2
⊖	76839	2	29	2
⊖	76840	3	29	2




765 TORX® Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	No.	Size	mm	pkg.
⊗	76510	T10	29	10
⊗	76511	T15	29	10
⊗	76512	T20	29	10
⊗	76513	T25	29	10
⊗	76514	T27	29	10
⊗	76516	T30	29	10
⊗	76517	T40	29	10

768 TORX® Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	No.	Size	mm	pkg.
⊗	76810	T10	29	2
⊗	76811	T15	29	2
⊗	76812	T20	29	2
⊗	76813	T25	29	2
⊗	76814	T27	29	2
⊗	76816	T30	29	2
⊗	76817	T40	29	2

1/4" Drive Insert & Power Bits




765 Hex Inch Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item				
No.	Inch	mm	pkg.	
76530	1/8	29	10	
76531	9/64	29	10	
76532	5/32	29	10	
76533	3/16	29	10	
76534	7/32	29	10	
76535	1/4	29	10	

768 Hex Inch Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item				
No.	Inch	mm	pkg.	
76830	1/8	29	2	
76831	9/64	29	2	
76832	5/32	29	2	
76833	3/16	29	2	
76834	7/32	29	2	
76835	1/4	29	2	


765 Hex Metric Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item				
No.	mm	mm	pkg.	
76523	3.0	29	10	
76524	4.0	29	10	
76525	5.0	29	10	
76526	6.0	29	10	

768 Hex Metric Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item				
No.	mm	mm	pkg.	
76823	3.0	29	2	
76824	4.0	29	2	
76825	5.0	29	2	
76826	6.0	29	2	


76897 28 Pc. Terminator Impact Insert Bit Set With SlimFix 1/4" Locking Bit Holder

Item No.	Set includes the following bits:
76897	Phillips: #1, 2 (2), 3
	Sq: #1, 2, 3 & Pozidriv®: #1, 2, 3
lbs. .47	Hex Metric: 3.0, 4.0, 5.0, 6.0mm
	Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Torx®: T10, T15, T20, T25(2), T30, T40

Wiha Insert Terminator Impact Bit Sets

76876 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76876 Set includes the following bits:

-  Hex In: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
-  Hex Metric: 3.0, 4.0, 5.0, 6.0mm


76877 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76877 Set includes the following bits:

-  Torx®: T10, T15, T20 (2), T25 (2), T27, T30 (2), T40


76881 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76881 Set includes the following bits:

-  Phillips: #1, 2, 3
-  Square: #1, 2, 3
-  Torx®: T20, T25, T30, T40

In Metal Box


76899 34 Pc. Terminator Impact Insert Bit Set With 3K Bit Holder Handle & SlimFix 1/4" Locking Bit Holder

Item No. Set includes the following bits:

76899	2 Phillips: #1, 2, 3
	Square: #1, 2 (2), 3
lbs.	Pozidriv®: #1, 2, 3
1.12	Torx®: T10, T15, T20 (2), T25 (2), T30 (2), T40
	Hex Metric: 3.0, 4.0, 5.0, 6.0mm
	Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



Includes magnetic bit holder

76890 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76890 Set includes the following bits:

-  3 Phillips: #2
-  Square: #2
-  Torx®: T15, T20, T25


76891 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76891 Set includes the following bits:

-  Phillips: #2, 3
-  Square: #2, 3
-  Torx®: T20, T25, T30


76893 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76893 Set includes the following bits:

-  Hex Inch: 5/32, 3/16, 7/32, 1/4"
-  Hex Metric: 4, 5, 6mm


76895 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm

76895 Set includes the following bits:

-  Torx®: T10, T15, T20, T25, T27, T30, T40

Includes magnetic bit holder

Wiha Power Terminator Impact Bits & Power Terminator Impact Bit Sets



765 Phillips Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76543	1	49	10
76544	2	49	10
76545	3	49	10

768 Phillips Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76843	1	49	2
76844	2	49	2
76845	3	49	2



765 Pozidriv® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76548	1	49	10
76549	2	49	10
76550	3	49	10

768 Pozidriv® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76848	1	49	2
76849	2	49	2
76850	3	49	2



765 Square Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
76578	1	49	10
76579	2	49	10
76580	3	49	10

768 Square Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
76878	1	49	2
76879	2	49	2
76880	3	49	2



765 TORX® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
76553	T10	49	10
76554	T15	49	10
76555	T20	49	10
76556	T25	49	10
76557	T27	49	10
76558	T30	49	10
76559	T40	49	10

768 TORX® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
76853	T10	49	2
76854	T15	49	2
76855	T20	49	2
76856	T25	49	2
76857	T27	49	2
76858	T30	49	2
76859	T40	49	2



765 Hex Inch Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	Hex	—	—
No.	Inch	mm	pkg.
76570	1/8	49	10
76571	9/64	49	10
76572	5/32	49	10
76573	3/16	49	10
76574	7/32	49	10
76575	1/4	49	10

768 Hex Inch Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	Hex	—	—
No.	Inch	mm	pkg.
76870	1/8	49	2
76871	9/64	49	2
76872	5/32	49	2
76873	3/16	49	2
76874	7/32	49	2
76875	1/4	49	2



765 Hex Metric Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	Hex	—	—
No.	mm	mm	pkg.
76563	3.0	49	10
76564	4.0	49	10
76565	5.0	49	10
76566	6.0	49	10

768 Hex Metric Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	Hex	—	—
No.	mm	mm	pkg.
76863	3.0	49	2
76864	4.0	49	2
76865	5.0	49	2
76866	6.0	49	2



76892 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76892 Set includes the following bits:

- +
- +
- +
- +
- +
- +
- +



76896 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76896 Set includes the following bits:

- +
- +
- +
- +
- +
- +
- +



76894 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76894 Set includes the following bits:

- +
- +
- +
- +
- +
- +
- +



Case Pack of 10
Bit Boxes Includes
Counter Top
Display



766 Phillips Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	Size	mm	pkg.
76601	1	29	25
76602	2	29	25
76603	3	29	25



766 Pozidriv® Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	Size	mm	pkg.
76606	1	29	25
76607	2	29	25
76608	3	29	25



766 Square Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	Size	mm	pkg.
76638	1	29	25
76639	2	29	25
76640	3	29	25



766 TORX® Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	Size	mm	pkg.
76610	T10	29	25
76611	T15	29	25
76612	T20	29	25
76613	T25	29	25
76614	T27	29	25
76616	T30	29	25
76617	T40	29	25



766 Hex Inch Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	Inch	mm	pkg.
76630	1/8	29	25
76631	9/64	29	25
76632	5/32	29	25
76633	3/16	29	25
76634	7/32	29	25
76635	1/4	29	25

766 Hex Metric Terminator Impact Bits,
1/4" Insert - 25 Bit Box Pack

Item			
No.	mm	mm	pkg.
76623	3.0	29	25
76624	4.0	29	25
76625	5.0	29	25
76626	6.0	29	25



766 Phillips Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	Size	mm	pkg.
76641	1	49	15
76642	2	49	15
76643	2	49	15



766 Square Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	Size	mm	pkg.
76644	1	49	15
76645	2	49	15
76646	3	49	15



766 Pozidriv® Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	Size	mm	pkg.
76647	1	49	15
76648	2	49	15
76649	3	49	15



766 TORX® Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	Size	mm	pkg.
76650	T10	49	15
76651	T15	49	15
76652	T20	49	15
76653	T25	49	15
76654	T27	49	15
76655	T30	49	15
76656	T40	49	15



766 Hex Inch Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	Inch	mm	pkg.
76670	1/8	49	15
76671	9/64	49	15
76672	5/32	49	15
76673	3/16	49	15
76674	7/32	49	15
76675	1/4	49	15

766 Hex Metric Terminator Impact Bits,
1/4" Power - 15 Bit Box Pack

Item			
No.	mm	mm	pkg.
76663	3.0	49	15
76664	4.0	49	15
76665	5.0	49	15
76666	6.0	49	15



Wiha Terminator Impact Bits 100 Bit Packs



735 Phillips Terminator Impact Bits, 1/4" Insert - 100 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
73501	1	29	100
73502	2	29	100
73503	3	29	100



735 Square Terminator Impact Bits, 1/4" Insert - 100 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
73522	1	29	100
73523	2	29	100
73524	3	29	100



735 TORX® Terminator Impact Bits, 1/4" Insert - 100 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
73507	T15	29	100
73508	T20	29	100
73509	T25	29	100
73510	T27	29	100
73511	T30	29	100



735 Pozidriv® Terminator Impact Bits, 1/4" Insert - 100 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
73504	1	29	100
73505	2	29	100
73506	3	29	100



735 Hex Inch Terminator Impact Bits, 1/4" Insert - 100 Bit Pack

Item	⬡	—	—
No.	Inch	mm	pkg.
73516	1/8	29	100
73517	9/64	29	100
73518	5/32	29	100
73519	3/16	29	100
73520	7/32	29	100
73521	1/4	29	100



735 Hex Metric Terminator Impact Bits, 1/4" Insert - 25 Bit Box Pack

Item	⬡	—	—
No.	mm	mm	pkg.
73512	3.0	29	100
73513	4.0	29	100
73514	5.0	29	100
73515	6.0	29	100



735 Phillips Terminator Impact Bits, 1/4" Power - 100 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
73525	1	49	100
73526	2	49	100
73527	3	49	100



735 Square Terminator Impact Bits, 1/4" Power - 100 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
73546	1	49	100
73547	2	49	100
73548	3	49	100



735 TORX® Terminator Impact Bits, 1/4" Power - 100 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
73531	T15	49	100
73532	T20	49	100
73533	T25	49	100
73534	T27	49	100
73535	T30	49	100



735 Pozidriv® Terminator Impact Bits, 1/4" Power - 100 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
73528	1	49	100
73529	2	49	100
73530	3	49	100



735 Hex Inch Terminator Impact Bits, 1/4" Power - 100 Bit Pack

Item	⬡	—	—
No.	Inch	mm	pkg.
73540	1/8	49	100
73541	9/64	49	100
73542	5/32	49	100
73543	3/16	49	100
73544	7/32	49	100
73545	1/4	49	100



735 Hex Metric Terminator Impact Bits, 1/4" Power - 100 Bit Box Pack

Item	⬡	—	—
No.	mm	mm	pkg.
73536	3.0	49	100
73537	4.0	49	100
73538	5.0	49	100
73539	6.0	49	100

Wiha Terminator Impact Bits 250 Bit Packs



765 Phillips Terminator Impact Bits, 1/4" Insert - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76581	1	29	250
76582	2	29	250
76500	3	29	250



765 Square Terminator Impact Bits, 1/4" Insert - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76583	1	29	250
76584	2	29	250
76537	3	29	250



765 TORX® Terminator Impact Bits, 1/4" Insert - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76585	T15	29	250
76586	T20	29	250
76587	T25	29	250
76588	T27	29	250
76589	T30	29	250



765 Pozidriv® Terminator Impact Bits, 1/4" Insert - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76504	1	29	250
76505	2	29	250
76509	3	29	250



765 Hex Inch Terminator Impact Bits, 1/4" Insert - 250 Bit Pack

Item			
No.	Inch	mm	pkg.
76521	1/8	29	250
76522	9/64	29	250
76527	5/32	29	250
76528	3/16	29	250
76529	7/32	29	250
76536	1/4	29	250

765 Hex Metric Terminator Impact Bits, 1/4" Insert - 250 Bit Box Pack

Item			
No.	mm	mm	pkg.
76515	3.0	29	250
76518	4.0	29	250
76519	5.0	29	250
76520	6.0	29	250



765 Phillips Terminator Impact Bits, 1/4" Power - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76590	1	49	250
76591	2	49	250
76541	3	49	250



765 Square Terminator Impact Bits, 1/4" Power - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76592	1	49	250
76593	2	49	250
76599	3	49	250



765 TORX® Terminator Impact Bits, 1/4" Power - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76594	T15	49	250
76595	T20	49	250
76596	T25	49	250
76597	T27	49	250
76598	T30	49	250



765 Pozidriv® Terminator Impact Bits, 1/4" Power - 250 Bit Pack

Item			
No.	Size	mm	pkg.
76542	1	49	250
76546	2	49	250
76547	3	49	250



765 Hex Inch Terminator Impact Bits, 1/4" Power - 250 Bit Pack

Item			
No.	Inch	mm	pkg.
76562	1/8	49	250
76567	9/64	49	250
76568	5/32	49	250
76569	3/16	49	250
76576	7/32	49	250
76577	1/4	49	250

765 Hex Metric Terminator Impact Bits, 1/4" Power - 250 Bit Box Pack

Item			
No.	mm	mm	pkg.
76551	3.0	49	250
76552	4.0	49	250
76560	5.0	49	250
76561	6.0	49	250

Impact Bits

Longest life impact bit available, 30X performance increase over standard bits.

Available in 1"/29mm Insert or 2"/49mm Power bits.

Precision tuned torsion zones are individually matched to bit profile reducing stress on the tip when used in an impact driver.

German formulated MoV tool steel combined with precision hardening & heat treating.

Hardest working tip selection in 15ct or 25ct bit box, 100ct or 250ct bulk packs.

Contractor Bits

Available in 1"/25mm Insert or 2"/50mm Power bits.

Suitable for all machine and manual screw driving applications.

German formulated CRV tool steel combined with precision hardening and heat treating.

Widest selection of bit offering in 15ct or 30ct bit box, 100ct or 250ct bulk packs.



250 Count Bulk Packs
Includes Bit Bowl

Wiha Terminator Impact Bits 250-piece Bit Bowls



768 Phillips Terminator Impact Bits, 1/4" Insert - 250-piece Bit Bowl

Item	+	—	—
No.	Size	mm	pkg.
76841	2	29	250



768 Phillips Terminator Impact Bits, 1/4" Power - 250-piece Bit Bowl

Item	+	—	—
No.	Size	mm	pkg.
76851	2	49	250




768 Square Terminator Impact Bits, 1/4" Insert - 250-piece Bit Bowl

Item	□	—	—
No.	Size	mm	pkg.
76847	2	29	250



768 Square Terminator Impact Bits, 1/4" Power - 250-piece Bit Bowl

Item	□	—	—
No.	Size	mm	pkg.
76861	2	49	250



768 TORX® Terminator Impact Bits, 1/4" Insert - 250-piece Bit Bowl

Item	✱	—	—
No.	Size	mm	pkg.
76842	T25	29	250



768 TORX® Terminator Impact Bits, 1/4" Power - 250-piece Bit Bowl

Item	✱	—	—
No.	Size	mm	pkg.
76852	T25	49	250



768 Hex Inch Terminator Impact Bits, 1/4" Insert - 250-piece Bit Bowl

Item	⬡	—	—
No.	Inch	mm	pkg.
76846	5/32	29	250



768 Hex Inch Terminator Impact Bits, 1/4" Power - 250-piece Bit Bowl

Item	⬡	—	—
No.	Inch	mm	pkg.
76860	3/16	49	250

Wiha Contractor Bits 250-piece Bit Bowls



723 Phillips Insert Bits, 1/4"

Item	+	—	—
No.	Size	mm	pkg.
72304	2	25	250



723 Square Insert Bits, 1/4"

Item	□	—	—
No.	Size	mm	pkg.
72347	2	25	250



723 TORX® Bits, 1/4"

Item	✱	—	—
No.	Size	mm	pkg.
72343	T25	25	250



723 Hex Inch Insert Bits, 1/4"

Item	⬡	—	—
No.	Inch	mm	pkg.
72328	5/32	25	250



723 Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	+	—	—
No.	Size	mm	pkg.
72351	2	50	250



723 Square Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	□	—	—
No.	Size	mm	pkg.
72391	2	50	250



723 TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	✱	—	—
No.	Size	mm	pkg.
72378	T25	50	250



723 Hex Inch Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	⬡	—	—
No.	Inch	mm	pkg.
72354	3/16	50	250

TORX® Bits


The ideal multi-purpose bits for all around quality and performance

Made by Wiha - Production Quality

Suitable for all applications for both manual and machine
Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life

Impact resistant modified CVM, tool steel, hardened



Wiha TORX® Insert Bit



10 bit pack

715 TORX® Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71523	T3	25	10	.12
71524	T4	25	10	.12
71505	T5	25	10	.12
71506	T6	25	10	.12
71507	T7	25	10	.12
71508	T8	25	10	.12
71509	T9	25	10	.12
71510	T10	25	10	.12
71515	T15	25	10	.12
71520	T20	25	10	.12
71525	T25	25	10	.12
71527	T27	25	10	.13
71530	T30	25	10	.14
71540	T40	25	10	.15


30 Piece Contractor Grade Bits

725 TORX® Insert Bit Packs, 30 Pcs., 1/4"

Item No.	Size	mm	lbs.
72572	T7	25	.36
72573	T8	25	.36
72574	T9	25	.36
72575	T10	25	.36
72576	T15	25	.36
72577	T20	25	.36
72578	T25	25	.36
72579	T27	25	.36
72580	T30	25	.36
72581	T40	25	.36

Wiha TORX® Bit Packs

2 bit pack



715 TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71548	T3	25	.03
71549	T4	25	.03
71550	T5	25	.03
71551	T6	25	.03
71552	T7	25	.03
71553	T8	25	.03
71554	T9	25	.03
71555	T10	25	.03
71556	T15	25	.03
71557	T20	25	.03
71558	T25	25	.03
71559	T27	25	.04
71560	T30	25	.04
71561	T40	25	.04

2 bit pack



777 TORX® Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item No.	Size	mm
77701	T6+T7	30
77702	T8+T9	30
77703	T10+T15	30
77704	T20+T25	30
77705	T27+T30	30

Wiha TORX® Bit Packs



71571 TORX® Insert Bit Packs, 1" CVM S2

modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71571 Set includes the following bits:

Torx®:

T15, T20, T25, T27,
wt. .08 T30, T40 x 1" (25mm)



71570 TORX® Insert Bit Packs, 1" CVM S2

modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc bit pack.

71570 Set includes the following bits:

Torx®:

T5, T6, T7, T8, T9,
wt. .07 T10 x 1" (25mm)

Wiha TORX® 5/16" Bits



5/16"

10 bit pack

725 TORX® Bits, 5/16"

Item No.	Size	mm	pkg.	lbs.
72525	T25	35	10	.27
72527	T27	35	10	.27
72530	T30	35	10	.27
72540	T40	35	10	.28
72545	T45	35	10	.31
72550	T50	35	10	.32
72555	T55	35	10	.52
72570	T60	35	10	.52

2 bit pack



5/16" Insert Bits



725 TORX® Insert Bit Packs, 5/16"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
72551	T50	35	.32
72569	T60	35	.52

Wiha TORX® Power Bits



10 bit pack

745 TORX® Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
	74511	T6	50	10	.18
	74512	T7	50	10	.18
	74513	T8	50	10	.18
	74517	T9	50	10	.19
	74519	T10	50	10	.20
	74521	T15	50	10	.20
	74523	T20	50	10	.20
	74529	T25	50	10	.20
	74531	T27	50	10	.20
	74533	T30	50	10	.20
	74535	T40	50	10	.25



2 bit pack

745 TORX® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
	74525	T1	50	.05
	74527	T2	50	.05
	74530	T3	50	.05
	74540	T4	50	.05
	74559	T5	50	.05
	74501	T6	50	.05
	74502	T7	50	.05
	74503	T8	50	.05
	74504	T9	50	.05
	74506	T10	50	.05
	74508	T15	50	.05
	74510	T20	50	.05
	74514	T25	50	.06
	74515	T27	50	.06
	74516	T30	50	.06
	74518	T40	50	.08



10 bit pack

745 TORX® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
	74536	T6	70	10	.02
	74538	T7	70	10	.02
	74542	T8	70	10	.02
	74544	T9	70	10	.02
	74546	T10	70	10	.02
	74548	T15	70	10	.02
	74551	T20	70	10	.03
	74553	T25	70	10	.03
	74556	T27	70	10	.04
	74558	T30	70	10	.04
	74561	T40	70	10	.04



2 bit pack

739 TORX® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
	73936	T6	70	1	.02
	73937	T7	70	1	.02
	73938	T8	70	1	.02
	73939	T9	70	1	.02
	73940	T10	70	1	.02
	73941	T15	70	1	.02
	73942	T20	70	1	.03
	73943	T25	70	1	.03
	73944	T27	70	1	.04
	73945	T30	70	1	.04
	73946	T40	70	1	.04



745 TORX® Power Bits 1/4" Hex Drive, Length 3.5"/90mm


Item	No.	Size	mm	pkg.	lbs.
	74563	T6	90	1	.03
	74565	T7	90	1	.03
	74567	T8	90	1	.03
	74569	T9	90	1	.03
	74571	T10	90	1	.03
	74573	T15	90	1	.03
	74575	T20	90	1	.04
	74577	T25	90	1	.04
	74579	T27	90	1	.04
	74581	T30	90	1	.04
	74583	T40	90	1	.04



745 TORX® Power Bits 1/4" Hex Drive, Length 6.0"/150mm

Item	No.	Size	mm	pkg.	lbs.
	74580	T6	150	1	.04
	74582	T7	150	1	.04
	74584	T8	150	1	.04
	74585	T9	150	1	.04
	74586	T10	150	1	.04
	74587	T15	150	1	.04
	74588	T20	150	1	.04
	74589	T25	150	1	.04
	74590	T27	150	1	.04
	74591	T30	150	1	.04


Wiha TORX® Double End Bits



10 bit pack

744 TORX® Double End Bits 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	pkg.	lbs.
	74413	T7	T7	65	10	.32
	74415	T8	T8	65	10	.32



744 TORX® Double End Bit Pack 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	lbs.
	74461	T7	T7	65	.05
	74462	T8	T8	65	.05

NOTES:

Wiha Insert Bit Blister Pack



72595 10 Pack TORX® Insert Bit Pack
CVM S2 modified tool steel.

TORX®: lbs.
T7, T8, T9, T10, T15 .16
T20, T25, T27, T30, T40

Wiha Insert Bit & Socket Set



72590 11 Piece TORX® Insert Bit Pack & Socket Set CVM S2 modified tool steel.
1/4" to 3/8" Drive Socket

1/4" Bits: T10, T15, T20, T25, T27, T30
5/16" to 3/8" Drive Socket lbs.
5/16" Bits: T40, T45, T50 .36

Wiha TORX® Insert Bit & Power Bit Sets



79445 XSelector Bit Set With TORX® Bits
Set Includes 1/4" Magnetic Bit Holder
& the following 10 bits:

lbs. **TORX®:** T7, T8, T9, T10, T15,
.29 T20, T25, T27, T30, T40



71195 PokitPak - TORX® Insert Bits In Molded Case - Includes 6 - 1/4" Insert Bits & Magnetic Bit Holder lbs. .16

TORX®:
T8, T10, T15, T20, T25, T30

Wiha TORX® Insert Bit Sets



Bit holder stainless steel, magnetic

38044 TORX® Pop-Up Bit Screwdriver Set
Wiha Cushion Grip handle, multi-component.
Compact storage for 12 bits in the handle.

Set includes the following 1/4" bits:
lbs. **TORX®:** T5, T6, T7, T8, T9, T10,
.42 T15, T20, T25, T27, T30, T40



38045 TORX® SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:
lbs. **TORX®:** T8, T10, T15,
.20 T20, T25, T30



79242 Bit-Selector With TORX® Bits
Includes Universal Magnetic 1/4" Bit Holder
& The Following 10 Insert Bits:

lbs. **TORX®:** T5, T6, T7, T8, T9,
.32 T10, T15, T20, T25, T30



74985 Power Bit Belt Pack With TORX® Bits
Includes the following 10 bits: lbs. .28

TORX®: T6, T7, T8, T9,
T10, T15, T20, T25, T27, T30

79245 Bit-Selector With TORX® Bits
Includes Auto Lock Magnetic 1/4" Bit Holder
& The Following 10 Insert Bits:

lbs. **TORX®:** T7, T8, T9, T10,
.34 T15, T20, T25, T27, T30, T40

Wiha Security TORX® Insert Bits and Power Bits

Security Torx®

Made by Wiha -
Production
Quality



Security
TORX®



Impact resistant modified
CVM tool steel, hardened

Highly resistant
to wear and
tear for a
long tool life

Suitable for all applications
for both manual and machine
Hardness HRC 59-61

10 bit pack



5/16"

725 Security TORX® Bits, 5/16"

Item					
No.	Size	mm	pkg.	lbs.	
72514	T25s	35	10	.26	
72515	T27s	35	10	.27	
72516	T30s	35	10	.28	
72542	T40s	35	10	.28	
72547	T45s	35	10	.32	
72558	T60s	35	10	.65	



2 bit pack



725 Security TORX® Bits, 5/16" 2 Bit Pk.

Item				
No.	Size	mm	lbs.	
72559	T25s	35	.26	
72560	T27s	35	.27	
72561	T30s	35	.28	
72562	T40s	35	.28	
72563	T45s	35	.29	
72564	T50s	35	.30	
72567	T55s	35	.32	
72568	T60s	35	.35	

5 bit packs



Made in Taiwan

745 Protturn Security TORX® Power Bits 1/4" Hex Drive, Length 3.0"/75mm

Item				
No.	Size	mm	pkg.	lbs.
74566	T10s	75	5	.01
74568	T15s	75	5	.01
74570	T20s	75	5	.01
74572	T25s	75	5	.02
74574	T27s	75	5	.02
74576	T30s	75	5	.03



10 bit
pack

705 Security TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item					
No.	Size	mm	pkg.	lbs.	
70507	T7s	50	10	.18	
70508	T8s	50	10	.18	
70509	T9s	50	10	.18	
70510	T10s	50	10	.19	
70515	T15s	50	10	.19	
70520	T20s	50	10	.21	
70525	T25s	50	10	.23	
70527	T27s	50	10	.23	
70530	T30s	50	10	.23	
70540	T40s	50	10	.23	
70545	T45s	50	10	.33	
70550	T50s	50	10	.37	

2 bit
pack



705 Security TORX® Power Bit Packs, 2"

Item				
No.	Size	mm	lbs.	
70556	T7s	50	.07	
70557	T8s	50	.07	
70558	T9s	50	.07	
70559	T10s	50	.07	
70560	T15s	50	.07	
70561	T20s	50	.07	
70562	T25s	50	.07	
70563	T27s	50	.07	
70564	T30s	50	.07	
70565	T40s	50	.07	
70566	T45s	50	.08	
70567	T50s	50	.08	

2 bit
pack



701 Security TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item				
No.	Size	mm	lbs.	
70150	T7s	25	.03	
70151	T8s	25	.03	
70152	T9s	25	.03	
70153	T10s	25	.03	
70154	T15s	25	.03	
70155	T20s	25	.03	
70156	T25s	25	.03	
70157	T27s	25	.03	
70158	T30s	25	.03	
70159	T40s	25	.03	

Wiha Security TORX® Insert Bit & Power Bit Sets



79247 Bit-Selector With Security TORX® Bits, Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:  lbs. .32

Security TORX®:

T7s, T8s, T9s, T10s, T15s,
T20s, T25s, T27s, T30s, T40s



70190 Bit-Selector With Security TORX® Bits, Includes The Following 7 Insert Bits:

Security TORX®:

	 lbs.
T7s, T8s, T9s,	
T10s, T15s, T20s, T25s	.21



79447 XSelector Bit Set With Security TORX® Bits, Includes 1/4" Magnetic Bit Holder & The Following Bits:  lbs. .27

Security TORX®: T7s, T8s,
T9s, T10s, T15s, T20s, T25s,
T27s, T30s, T40s



74987 Power Bit Belt Pack With Security TORX® Bits, Includes the following 10 bits:

	 lbs.
T7s, T8s, T9s,	
T10s, T15s, T20s,	
T25s, T27s, T30s, T40s	.29

Bit holder stainless steel, magnetic



38046 Security TORX® Pop-Up Bit Screwdriver Set Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle.  lbs. .42

Includes The Following 1/4" Bits:

TORX®: T5, T6

Security TORX®: T7s, T8s, T9s, T10s,
T15s, T20s, T25s, T27s, T30s, T40s

Bit holder stainless steel, magnetic

75mm Bits



38042 Security TORX® Pop-Up Bit Screwdriver Set Wiha Cushion Grip handle, multi-component. Compact storage for 6 bits in the handle.  lbs. .44

Includes The Following 75mm 1/4" Bits:

Security TORX®:

T10s, T15s, T20s, T25s, T27s, T30s



38047 Security TORX® SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Includes The Following 1/4" Bits:  lbs. .20

Security TORX®: T8s, T10s,
T15s, T20s, T25s, T30s

Wiha Security TORX® Power Blades & Holder



760 Security TORX® Power Blades S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	 Size	 lbs.	 pkg.
76008	T8s	.02	1
76009	T9s	.02	1
76010	T10s	.02	1
76015	T15s	.02	1
76020	T20s	.02	1
76025	T25s	.03	1
76027	T27s	.03	1
76030	T30s	.04	1
76040	T40s	.04	1



76092 9 Piece Security TORX® Blade Set

Item No.	 lbs.	Set includes:
76092	.30	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s



76000 CentroFix Cushion Grip Blade Holder Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item No.	 mm	 mm	 Inch	 mm	 Inch	 lbs.
76000	6.0	149	5.9	34.6	1.36	.26

Wiha TORXPlus® Insert Bits and Power Bits

TORXPlus®

Made by Wiha -
Production Quality

Highly resistant
to wear and
tear for a
long tool life

Impact resistant modified
chrome-vanadium-molybde-
num, tool steel, hardened

Suitable for all applications
for both manual and
machine Hardness
HRC 59-61



TORXPlus®



Security Pentalobe



10 bit
pack

716 TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
71603	IP3	25	10	.12
71604	IP4	25	10	.12
71605	IP5	25	10	.12
71606	IP6	25	10	.12
71607	IP7	25	10	.12
71608	IP8	25	10	.12
71609	IP9	25	10	.12
71610	IP10	25	10	.12
71615	IP15	25	10	.12
71620	IP20	25	10	.12
71625	IP25	25	10	.12
71627	IP27	25	10	.13
71630	IP30	25	10	.13
71640	IP40	25	10	.15



2 bit
pack



716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
71631	IP3	25	.03
71632	IP4	25	.03
71633	IP5	25	.03
71634	IP6	25	.03
71635	IP7	25	.03
71636	IP8	25	.03
71637	IP9	25	.03
71638	IP10	25	.03
71639	IP15	25	.03
71641	IP20	25	.03
71642	IP25	25	.03
71643	IP27	25	.03
71644	IP30	25	.03
71645	IP40	25	.04



10 bit pack

746 TORXPlus® Power Bits, 1/4" Hex, 2" OAL


Item No.	Size	mm	pkg.	lbs.
74601	IP5	50	10	.18
74602	IP6	50	10	.18
74603	IP7	50	10	.18
74604	IP8	50	10	.18
74608	IP9	50	10	.18
74612	IP10	50	10	.20
74616	IP15	50	10	.20
74620	IP20	50	10	.20
74624	IP25	50	10	.20
74628	IP27	50	10	.25
74632	IP30	50	10	.25
74636	IP40	50	10	.25



74982 Power Bit Belt Pack With TORXPlus® Bits Includes The Following 10 Bits:

Item No.	Size	mm	lbs.
74982	IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30		.28

2 bit
pack



746 TORXPlus® Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74611	IP1	50	.05
74613	IP2	50	.05
74614	IP3	50	.05
74617	IP4	50	.05
74659	IP5	50	.05
74660	IP6	50	.05
74661	IP7	50	.05
74662	IP8	50	.05
74663	IP9	50	.05
74664	IP10	50	.05
74665	IP15	50	.05
74666	IP20	50	.06
74667	IP25	50	.06
74668	IP27	50	.06
74669	IP30	50	.06
74670	IP40	50	.06

Wiha TORXPlus® Insert Bit Selectors



71690 Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

Item No.	Size	mm	lbs.
71690	IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40		.31

71692 Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

Item No.	Size	mm	lbs.
71692	IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20		.31

Wiha Security Pentalobe 5 Point Insert Bit



716 Security Pentalobe 5 Point Insert
Bits, 1/4" Hex, 1" OAL

Item				
No.	Size	mm	pkg.	lbs.
71648	PLS8	25	1	.11
71650	PLS10	25	1	.11
71652	PLS15	25	1	.11
71654	PLS20	25	1	.12
71656	PLS25	25	1	.13
71657	PLS27	25	1	.13
71658	PLS30	25	1	.14
71660	PLS40	35	1	.14


Wiha Insert Security Pentalobe 5 Point XSelector



79450 XSelector Bit Set With Security
Pentalobe 5 Point Bits Includes Magnetic
Bit Holder & The Following 7 Bits:

	Security Pentalobe: PLS8,
lbs.	PLS10, PLS15, PLS20,
.24	PLS25, PLS27, PLS30

Wiha Ball End TORX® Bits




745 Ball End TORX® Bits.
1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74524	T9	50	10	.18
74526	T10	50	10	.18
74528	T15	50	10	.18
74532	T20	50	10	.18
74534	T25	50	10	.18
74537	T27	50	10	.18
74539	T30	50	10	.18
74541	T40	50	10	.18

745 Ball End **TORX®** Power Bit Packs, 1"

Item			
No.	Size	mm	lbs.
74520	T10	50	.05
74522	T15	50	.05
74543	T20	50	.05
74545	T25	50	.06
74547	T27	50	.06
74549	T30	50	.08
74550	T40	50	.08

Wiha TORX® MagicSpring Screw Holding Power Bits



745 TORX® MagicSpring Screw Holding
Power Bits, 1/4" Hex Drive,
Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74552	T10	50	2	.05
74554	T15	50	2	.05
74555	T20	50	2	.05
74557	T25	50	2	.05
74564	T40	50	2	.05

NOTES:

Torx® Profiles



Torx®



**Ball End
Torx®**



**Security
Torx®**



TorxPlus®



Security

Pentalobe 5 Point

Wiha TORX® Align Insert Bits and Power Bits

Torx® Align Tapered For Snug Fit In Screw

Highly resistant
to wear and
tear for a
long tool life



Impact resistant modified
chrome-vanadium-
molybdenum, tool steel,
hardened

**Made by Wiha -
Production Quality**

Suitable for all applications
for both manual and machine
Hardness HRC 59-61



10 bit
pack

715 TORX® Align Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71536	T6	25	10	.12
71537	T7	25	10	.12
71538	T8	25	10	.12
71541	T10	25	10	.12
71542	T15	25	10	.12
71543	T20	25	10	.12
71544	T25	25	10	.13
71545	T27	25	10	.13
71546	T30	25	10	.14
71547	T40	25	10	.15

(Also Known As Torx Wedge Fit)

2 bit
pack



733 TORX® Align Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
73310	T6	25	.03
73311	T7	25	.03
73312	T8	25	.03
73313	T9	25	.03
73314	T10	25	.03
73315	T15	25	.03
73316	T20	25	.03
73317	T25	25	.03
73318	T27	25	.03
73319	T30	25	.03




10 bit
pack

747 TORX® Align Bits 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.
74711	T6	50	10	.18
74714	T7	50	10	.18
74717	T8	50	10	.18
74721	T9	50	10	.18
74724	T10	50	10	.18
74728	T15	50	10	.20
74732	T20	50	10	.22
74736	T25	50	10	.22
74739	T27	50	10	.22
74742	T30	50	10	.22

(Also Known As Torx Wedge Fit)

2 bit
pack



747 TORX® Align Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74760	T6	50	.05
74761	T7	50	.05
74762	T8	50	.05
74763	T9	50	.05
74764	T10	50	.05
74765	T15	50	.05
74766	T20	50	.06
74767	T25	50	.06
74768	T27	50	.06

Wiha TORX® Align Coated Insert Bits PokitPak



79283 PokitPak - TORX® Align Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits

TORX® Align:

T10, T15, T20, T25, T30, T40

lbs. .12



74981 Power Bit Belt Pack With TORX® Align Bits

Set includes the following 10 bits:

TORX® Align: T6, T7, T8, T9,
T10, T15, T20, T25, T27, T30

lbs. .28



Wiha Phillips Insert Bits



711 Phillips Insert Bits, 1/4" - 10 Bit Packs

Item				
No.	Size	mm	pkg.	lbs.
71100	0	25	10	.10
71101	1	25	10	.11
71102	2	25	10	.11
71103	3	25	10	.11

725 Phillips Insert Contractor Grade, 1/4"

No.	Size	mm	pkg.	lbs.
72519	0	25	30 pc	.85
72521	1	25	30 pc	.85
72522	2	25	30 pc	.85
72523	3	25	30 pc	.85

Phillips Bits

The ideal multi-purpose bits for all around quality & performance

Made by Wiha -
Production Quality

Suitable for all applications for both manual and machine
Hardness
HRC 59-61



Impact resistant
modified CVM, tool
steel, hardened

Highly resistant
to wear and
tear for a long
tool life



Phillips

High grade CVM steel, hardened torsion zone to prevent uneven torque distribution DIN 3126 ISO 1173 with anti-camout ribs

Wiha Phillips Insert Bit Packs

2 bit
pack



711 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel

Item			
No.	Size	mm	lbs.
71149	0	25	.03
71151	1	25	.03
71152	2	25	.03
71153	3	25	.04

2 bit
pack




777 Phillips Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77707	#1 + #2	30
77708	#0 + #3	30

Wiha Phillips 5/16" Insert Bits

2 bit
pack



721 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. 5/16" Hex Drive.

Item			
No.	Size	mm	lbs.
72102	2	32	.05
72103	3	32	.06
72104	4	32	.07



71056 Slotted/Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. Extra hard with natural finish, exact fit machined tips. 6pc. bit pk.

71056 Set includes the following bits:


① Slotted:

4.5, 5.5, 6.5 x 1" (25mm)

⊕ Phillips: lbs.

1, 2, 3 x 1" (25mm) .08

10 bit pack



71132 Phillips Drywall Stop Bit

High grade Chrome-vanadium steel, through hardened. Ideal bit for drywall constructors. Blue ring prevents the screw from being recessed too deeply into the plasterboard.

Item				
No.	Size	mm	lbs.	Pkg.
71132	2	25	.20	10

Wiha Phillips Power Bits



741 Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
74102	0	50	10	.23	
74103	1	50	10	.24	
74112	2	50	10	.25	
74124	3	50	10	.26	



741 Phillips Power Bit Packs, 2"

CVM S2 modified tool steel.


Item	No.	Size	mm	lbs.
74157	00	50	.06	
74158	0	50	.06	
74164	1	50	.06	
74165	2	50	.06	
74166	3	50	.06	



74150 Phillips Power Bit Packs, 2" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74150 Set includes the following bits:

Phillips Sizes:
wt. .09 1, 2, 3 x 2" (50mm)



741 Phillips Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
74167	00	70	10	.29	
74168	0	70	10	.29	
74106	1	70	10	.29	
74115	2	70	10	.37	
74127	3	70	10	.41	



739 Phillips Power Bits. 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack

Item	No.	Size	mm	pkg.	lbs.
73912	00	70	1	.29	
73913	0	70	1	.29	
73914	1	70	1	.29	
73915	2	70	1	.37	
73916	3	70	1	.41	



741 Phillips Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item	No.	Size	mm	pkg.	lbs.
74104	00	90	1	.32	
74107	0	90	1	.32	
74109	1	90	1	.34	
74118	2	90	1	.47	
74130	3	90	1	.53	



741 Phillips Power Bits 1/4" Hex Drive, Length 4.33"/110mm

Item	No.	Size	mm	pkg.	lbs.
74111	1	110	1	.40	
74121	2	110	1	.56	
74131	3	110	1	.65	



741 Phillips Power Bits 1/4" Hex Drive, Length 127mm/5"

Item	No.	Size	mm	pkg.	lbs.
74113	1	127	1	.04	
74123	2	127	1	.06	
74133	3	127	1	.07	



741 Phillips Power Bits 1/4" Hex Drive, Length 150mm/5.9"

Item	No.	Size	mm	pkg.	lbs.
74116	1	150	1	.05	
74126	2	150	1	.07	
74136	3	150	1	.09	

Wiha PokitPak Bit Set



71198 PokitPak - Slotted & Phillips Insert Bits In Molded Case -

Set Includes 6 - 1/4" Insert Bits & Magnetic Bit Holder

.16 Slotted: 4.5, 6.0mm

Phillips: 0, 1, 2, 3

Wiha Phillips Power Blades & Power Blade Holder



760 Phillips Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item	No.	Size	lbs.	pkg.
76041	0	.01	1	
76042	1	.02	1	
76043	2	.03	1	
76044	3	.04	1	



76094 4 Piece Phillips Blade Set

Item	No.	lbs.	Set includes:
76094	.17	3 x 90mm	Phillips: #0, 1, 2,



76000 CentroFix Cushion Grip Blade Holder

Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item	No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26	

Hex Bits



The ideal multi-purpose bits for all around quality & performance

Made by Wiha -
Production Quality

Impact resistant
modified CVM,
tool steel, hardened

Suitable for all applications
for both manual and machine
Hardness HRC 59-61

Highly resistant
to wear and tear
for a long tool life



Wiha Hex Inch & Metric Insert Bits



10 bit
pack

713 Hex Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71329	.050	25	10	.12
71326	1/16	25	10	.12
71328	5/64	25	10	.12
71330	3/32	25	10	.12
71333	7/64	25	10	.12
71336	1/8	25	10	.12
71339	9/64	25	10	.12
71342	5/32	25	10	.12
71345	3/16	25	10	.13
71348	7/32	25	10	.13
71351	1/4	25	10	.13
71353	5/16	25	10	.20
71356	3/8	25	10	.25

725 Hex Inch Insert Contractor Grade, 1/4"

Item No.	Size	mm	pkg.	lbs.
72502	1/16	25	30 pc	.85
72503	5/64	25	30 pc	.85
72504	3/32	25	30 pc	.85
72506	7/64	25	30 pc	.85
72507	1/8	25	30 pc	.85
72508	9/64	25	30 pc	.85
72509	5/32	25	30 pc	.85
72511	3/16	25	30 pc	.85
72512	7/32	25	30 pc	.85
72513	1/4	25	30 pc	.85



71396 Hex Inch Insert Bit Packs, 1"

6 pc. bit pack.

71396 Set includes the following bits:

Hex Inch:

	1/16, 3/32, 1/8, 5/32
wt. .13	3/16, 1/4" x 1" (25mm)



713 Hex Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71303	1.5	25	10	.12
71306	2.0	25	10	.12
71308	2.5	25	10	.12
71309	3.0	25	10	.12
71312	4.0	25	10	.12
71315	5.0	25	10	.14
71318	6.0	25	10	.14
71321	8.0	25	10	.20
71324	10.0	25	10	.27

725 Hex Metric Insert Contractor Grade, 1/4"

Item No.	Size	mm	pkg.	lbs.
72582	2.0	25	30 pc	.85
72583	2.5	25	30 pc	.85
72584	3.0	25	30 pc	.85
72585	4.0	25	30 pc	.85
72586	5.0	25	30 pc	.85
72587	6.0	25	30 pc	.85



71397 Hex Metric Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71397 Set includes the following bits:

Hex Metric:	wt. .21	2.0, 2.5, 3.0, 4.0, 5.0, 6.0
-------------	---------	------------------------------

Hex Metric Long Insert Bit On 5/16"



72388 Hex Metric Bit On 5/16" Stock

Item No.	mm	mm	pkg.	lbs.
72388	12.0	75	10	.14

Hex Inch & Metric Insert Bits

2 bit
pack



713 Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Inch	mm	lbs.
71359	.050	25	.03
71360	1/16	25	.03
71361	5/64	25	.03
71362	3/32	25	.03
71363	7/64	25	.03
71364	1/8	25	.03
71365	9/64	25	.03
71366	5/32	25	.04
71367	3/16	25	.04
71368	7/32	25	.04
71369	1/4	25	.04
71373	5/16	25	.05
71387	3/8	25	.06

733 Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	mm	mm	lbs.
73302	2.0	25	.03
73303	2.5	25	.03
73304	3.0	25	.03
73305	4.0	25	.03
73306	5.0	25	.03
73307	6.0	25	.04
73308	8.0	25	.05
73309	10.0	25	.06

2 bit
pack



777 Hex Inch Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item No.	Inch	mm
77723	3/32 + 7/64"	30
77724	1/8 + 9/64"	30
77725	5/32 + 3/16"	30
77726	7/32 + 1/4"	30

777 Hex Metric Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item No.	Metric	mm
77719	2.0 + 2.5mm	30
77720	3.0 + 4.0mm	30
77721	5.0 + 6.0mm	30

Wiha Hex Inch & Metric Power Bits



743 Hex Inch Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Inch	mm	pkg.	lbs.
74311	3/32	50	10	.30
74312	7/64	50	10	.30
74313	1/8	50	10	.30
74314	9/64	50	10	.30
74315	5/32	50	10	.30
74316	3/16	50	10	.30
74317	7/32	50	10	.30
74318	1/4	50	10	.30



743 Hex Inch Power Bit Packs, 2"

Item No.	Inch	mm	lbs.
74381	3/32	50	.07
74382	7/64	50	.07
74383	1/8	50	.07
74384	9/64	50	.07
74385	5/32	50	.07
74386	3/16	50	.07
74387	7/32	50	.07
74388	1/4	50	.07




743 Hex Metric Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	mm	mm	pkg.	lbs.
74325	2.5	50	10	.25
74330	3.0	50	10	.25
74340	4.0	50	10	.25
74350	5.0	50	10	.25
74360	6.0	50	10	.25
74380	8.0	50	10	.38



743 Hex Metric Power Bit Packs, 2"

Item No.	mm	mm	lbs.
74361	2.5	50	.07
74362	3.0	50	.07
74363	4.0	50	.07
74364	5.0	50	.07
74365	6.0	50	.07
74366	8.0	50	.09



743 Hex Inch Power Bits 1/4" Hex Drive, Length 2.75"/70mm

Item No.	Inch	mm	pkg.	lbs.
74343	7/64	70	10	.36
74344	1/8	70	10	.36
74345	9/64	70	10	.36
74346	5/32	70	10	.36
74348	7/32	70	10	.36
74349	1/4	70	10	.36



739 Hex Inch Power Bits 1/4" Hex Drive, Length 2.75"/70mm

Item No.	Inch	mm	pkg.	lbs.
73920	7/64	70	1	.36
73921	1/8	70	1	.36
73922	9/64	70	1	.36
73923	5/32	70	1	.36
73925	7/32	70	1	.36
73926	1/4	70	1	.36



743 Hex Metric Power Bits 1/4" Hex Drive, Length 2.75"/70mm

Item No.	mm	mm	pkg.	lbs.
74351	2.0	70	10	.36
74352	2.5	70	10	.36
74353	3.0	70	10	.36
74354	4.0	70	10	.36
74355	5.0	70	10	.36
74356	6.0	70	10	.36
74357	8.0	70	10	.36



739 Hex Metric Power Bits 1/4" Hex Drive, Length 2.75"/70mm

Item No.	mm	mm	pkg.	lbs.
73928	2.0	70	1	.36
73929	2.5	70	1	.36
73930	3.0	70	1	.36
73931	4.0	70	1	.36
73932	5.0	70	1	.36
73933	6.0	70	1	.36
73934	8.0	70	1	.36



743 Hex Metric Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item No.	mm	mm	pkg.	lbs.
74332	2.0	90	1	.40
74333	2.5	90	1	.40
74334	3.0	90	1	.40
74335	4.0	90	1	.40
74336	5.0	90	1	.40
74337	6.0	90	1	.40

Wiha Ball End Hex Inch Insert Bits




717 Ball End Hex Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71701	3/32	25	10	.12
71702	7/64	25	10	.12
71703	1/8	25	10	.12
71704	9/64	25	10	.12
71705	5/32	25	10	.12
71706	3/16	25	10	.13
71707	7/32	25	10	.14
71708	1/4	25	10	.15



717 Ball End Hex Inch Insert Bit Packs, 1"

Item No.	Inch	mm	lbs.
71711	3/32	25	.03
71712	7/64	25	.03
71713	1/8	25	.03
71714	9/64	25	.03
71715	5/32	25	.04
71716	3/16	25	.04
71717	7/32	25	.04
71718	1/4	25	.04



717 Ball End Hex Metric Insert Bits 1/4" Hex Drive, Length 1.5"/38mm

Item No.	mm	mm	pkg.
71719	1.5	38	2
71720	2.0	38	2
71721	2.5	38	2
71722	3.0	38	2
71723	4.0	38	2
71724	5.0	38	2
71725	6.0	38	2

Wiha Security Hex Insert Bits



10 bit pack

719 Security Hex Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71930	5/64	25	10	.12
71932	3/32	25	10	.12
71934	7/64	25	10	.12
71936	1/8	25	10	.12
71938	9/64	25	10	.12
71940	5/32	25	10	.12
71955	3/16	25	10	.13
71956	7/32	25	10	.14
71960	1/4	25	10	.15



10 bit pack

719 Security Hex Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71939	2.0	25	10	.12
71941	2.5	25	10	.12
71942	3.0	25	10	.12
71943	4.0	25	10	.12
71944	5.0	25	10	.15
71945	6.0	25	10	.15
71946	8.0	25	10	.20




2 bit pack

719 Security Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Inch	mm	lbs.
71970	5/64	25	.03
71971	3/32	25	.03
71972	7/64	25	.03
71973	1/8	25	.03
71974	9/64	25	.03
71975	5/32	25	.03
71976	3/16	25	.04
71977	7/32	25	.04
71978	1/4	25	.04



2 bit pack

719 Security Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	mm	mm	lbs.
71979	2.0	25	.03
71980	2.5	25	.03
71981	3.0	25	.03
71982	4.0	25	.03
71983	5.0	25	.04
71984	6.0	25	.04
71985	8.0	25	.05

1/4" Ball End MagicRing Bits

Screw Holding Hex Bits



717 MagicRing Metric Power Ball End Bits

Item No.	mm	mm	pkg.	lbs.
71730	3.0	50	1	.02
71740	4.0	50	1	.02
71750	5.0	50	1	.03
71760	6.0	50	1	.03

Screw Holding Hex Bits



717 MagicRing Inch Power Ball End Bits

Item No.	Inch	mm	pkg.	lbs.
71726	1/8	50	1	.02
71728	9/64	50	1	.02
71732	5/32	50	1	.02
71734	3/16	50	1	.03
71736	7/32	50	1	.03
71738	1/4	50	1	.03

Screw Holding Hex Bits



Screw Holding

MagicRing Insert & Power Bits

Screw Holding Hex Bits



713 MagicRing Metric Insert Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
71304	3.0	25	1	.01
71307	4.0	25	1	.01
71310	5.0	25	1	.01
71311	6.0	25	1	.01



743 MagicRing Metric Power Bits, 1/4"

Item No.	mm	mm	pkg.	lbs.
74301	3.0	50	1	.02
74305	4.0	50	1	.02
74307	5.0	50	1	.03
74319	6.0	50	1	.03



713 MagicRing Inch Insert Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
71343	1/8	25	1	.01
71346	9/64	25	1	.01
71349	5/32	25	1	.01
71352	3/16	25	1	.01
71354	7/32	25	1	.01



743 MagicRing Inch Power Bits, 1/4"

Item No.	Inch	mm	pkg.	lbs.
74369	1/8	50	1	.02
74371	9/64	50	1	.02
74373	5/32	50	1	.02
74375	3/16	50	1	.03
74379	1/4	50	1	.03

Wiha Hex Inch & Metric Bit Sets



79246 Bit-Selector With Hex Inch Bits
Set Includes Magnetic 1/4" Bit Holder
& The Following 10 Bits: lbs. .32

Hex Inch: 1/16, 5/64, 3/32, 7/64,
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

79256 Bit-Selector With Hex Metric Bits
Set Includes Magnetic 1/4" Bit Holder
& The Following 8 Bits: lbs. .30

Hex Metric: 1.5, 2.0, 2.5, 3.0,
4.0, 5.0, 6.0, 8.0mm



38058 Hex Inch SoftFinish® CushionGrip
Stubby Bit Holder with Wiha cushion grip
handle and CVM tool steel shaft. lbs. .22
Includes the following 1/4" bits:

Hex Inch: 3/32, 7/64, 1/8,
9/64, 5/32, 3/16"



38057 Hex Metric SoftFinish® CushionGrip
Stubby Bit Holder with Wiha cushion grip
handle and CVM tool steel shaft. lbs. .21

Includes The Following 1/4" Bits:
Hex Metric: 2.0, 2.5, 3.0,
4.0, 5.0, 6.0mm



79446 XSelector Bit Set With Hex Inch Bits
Set Includes Magnetic Bit Holder
& The Following 10 Bits: lbs. .27

Hex Inch: 1/16, 5/64, 3/32, 7/64,
1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Bit holder stainless
steel, magnetic



38049 Hex Inch & Metric Pop-Up Bit
Screwdriver Set Cushion Grip handle, multi-
component. Compact storage holds 12 bits.
Includes The Following 1/4" Bits:

Hex Inch: 5/64, 3/32, 1/8,
 5/32, 3/16, 1/4"
lbs. **Hex Metric:** 2.0, 2.5, 3.0,
.42 4.0, 5.0, 6.0mm



74986 Power Bit Belt Pack With
Inch & Metric Hex Bits Set Includes The
Following 10 Bits: lbs. .34

Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
Metric: 3.0, 4.0, 5.0, 6.0mm

Wiha Security Hex Inch & Metric Bit Sets



79266 Bit-Selector With Security Hex Inch
Bits Set Includes Magnetic 1/4" ClicFix Bit
Holder & The Following 9 Bits:

Security Hex Inch:
lbs. 5/64, 3/32, 7/64, 1/8, 9/64,
.32 5/32, 3/16, 7/32, 1/4"



71998 PokitPak - Security Hex Inch Insert
Bits In Molded Case - Set Includes
6 - 1/4" Insert Bits lbs. .12

Inch Security Hex:
3/32, 7/64, 1/8, 9/64, 5/32, 3/16"



71995 PokitPak - Security Hex Metric Insert
Bits In Molded Case - Set Includes
6 - 1/4" Insert Bits lbs. .21

Metric Security Hex:
2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

Wiha Insert Bit Blister Pack



72596 10 Pack Hex Inch Insert Bit Pack
CVM S2 modified tool steel.

Hex Inch: lbs.
1/16, 5/64, 3/32, 7/64, 1/8, .16
9/64, 5/32, 3/16, 7/32, 1/4"

Wiha Hex Inch & Metric Power Blades



760 Hex Inch Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	Inch	lbs.	pkg.
76045	1/16	.01	1
76005	5/64	.01	1
76006	3/32	.02	1
76007	7/64	.02	1
76014	1/8	.03	1
76016	9/64	.03	1
76017	5/32	.04	1
76018	3/16	.04	1
76019	7/32	.05	1
76021	1/4	.06	1

Wiha Ball End Hex Inch & Metric Bit Sets



79276 Bit-Selector With Ball End Hex Inch Bits Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:

lbs. .30
Ball End Hex Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



38056 Ball End Hex SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set Includes The Following 1/4" Bits:
 lbs. **Ball End Hex Inch:** 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Wiha MagicRing Hex Inch & Metric Bit Sets



74999 Power Bit Belt Pack With Ball End Screw Holding Hex Bits

lbs. .37
Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
Metric: 3.0, 4.0, 5.0, 6.0mm

Wiha Security Hex Inch & Metric Power Blades



760 Security Hex Metric Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	mm	lbs.	pkg.
76001	2.5	.02	1
76002	3.0	.02	1
76003	4.0	.03	1
76004	5.0	.04	1



760 Security Hex Inch Power Blades

Item No.	Inch	lbs.	pkg.
76046	5/64	.01	1
76047	3/32	.02	1
76048	7/64	.02	1
76049	1/8	.03	1
76050	9/64	.03	1
76051	5/32	.04	1
76052	3/16	.04	1
76053	7/32	.05	1
76054	1/4	.06	1



76090 4 Piece Security Hex Blade Set

Item No.	lbs.	Set includes:
76090	.12	Metric: 2.5, 3.0, 4.0, 5.0 x 90mm



76096 10 Piece Security Hex Blade Set

Item No.	lbs.	Set includes:
76096	.32	Inch: 1/16*, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 90mm

*1/16" Standard Inch Hex Only

Wiha Power Blade Holder



76000 CentroFix Cushion Grip Blade Holder

Wiha-SoftFinish® impact resistant, with roll off protection. Quick release bit holder with magnet.

Item No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26

Wiha Square Power Blades



760 Square Power Blades

Item No.	Size	lbs.	pkg.
76056	1	.02	1
76057	2	.03	1
76058	3	.04	1



76095 3 Piece Square Blade Set

Item No.	lbs.	Set includes:
76095	.11	Square: #1, 2, 3 x 90mm

Square Insert & Power Bits

Square Bits



CVM,
tool steel,
hardened

□ Square

Suitable for all applications for both manual & machine hardness HRC 59-61



10 bit
pack

718 Square Insert Bits, 1/4"

Item	□	—	—	—
No.	Size	mm	pkg.	lbs.
71801	1	25	10	.11
71802	2	25	10	.11
71803	3	25	10	.11

30 Piece Contractor Grade Bits

725 Square Insert Contractor Grade, 1/4"

Item	□	—	—	—
No.	mm	mm	pkg.	lbs.
72537	1	25	30 pc	.85
72538	2	25	30 pc	.85
72539	3	25	30 pc	.85



2 bit
pack

718 Square Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	□	—	—	—
No.	Size	mm	lbs.	
71851	1	25	.03	
71852	2	25	.03	
71853	3	25	.03	



71854 Square Insert Bit Packs, 1"

CVM S2 modified tool steel. 3 pc. bit pack

71854 Set includes the following bits:

□ Square:
wt. .04 1, 2, 3 x 1" (25mm)



2 bit
pack

777 Square Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item	□	—
No.	Size	mm
77712	#1 + #2	30
77713	#0 + #3	30



10 bit
pack

748 Square Power Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item	□	—	—	—
No.	Size	mm	pkg.	lbs.
74813	1	50	10	.20
74816	2	50	10	.20
74819	3	50	10	.20



2 bit
pack

748 Square Power Bit Packs, 2"

CVM S2 modified tool steel.

Item	□	—	—	—
No.	Size	mm	lbs.	
74860	1	50	.05	
74861	2	50	.05	
74862	3	50	.05	



74890 Square Power Bit Packs, 2" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74890 Set includes the following bits:

□ Square:
wt. .08 1, 2, 3 x 2.0" (50mm)



74895 Square Power Bit Packs, 2.0" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

74895 Set includes the following bits:

□ Square: 2 of each sizes
wt. 1.2 1, 2, 3 x 2.0" (50mm)



748 Square Power Bit, 1/4" Hex Drive, Length 3.5"/90mm CVM S2 modified tool steel.

Item	□	—	—
No.	Size	mm	lbs.
74811	1	90	.08
74812	2	90	.08
74814	3	90	.08

Slotted Bits

The ideal multi-purpose bits for all around quality & performance

Made by Wiha -
Production
Quality

Highly resistant to
wear and tear for a
long tool life

Impact resistant modified CVM,
tool steel, hardened



● Slotted



10 bit
pack

710 Slotted Insert Bits, 1/4" Hex Drive, Length 25mm/.984"

Item	↑	↓	↑	↓	—
No.	mm	Inch	mm	Inch	pkg.
71001	4.5	.177	0.6	.024	10
71004	5.5	.216	0.8	.030	10
71002	6.5	.255	1.2	.039	10
71003	8.0	.315	1.6	.063	10

30 Piece Contractor Grade Bits

725 Slotted Insert Contractor Grade, 1/4"

Item	↑	↓	—	—	—
No.	mm	mm	pkg.	lbs.	
72534	4.5	25	30 pc	.85	
72535	5.5	25	30 pc	.85	
72536	6.0	25	30 pc	.85	



2 pc.
bit
pack!

710 Slotted Insert Bits, 1/4" Hex Drive, Length 1.54"/39mm 2 pc. Bit pack.

Item	↑	↓	—	—	—
No.	mm	Inch	mm	Inch	pkg.
71031	3.5	.139	0.6	.024	2
71032	4.0	.157	0.8	.031	2
71035	6.5	.255	1.2	.047	2



2 bit
pack

777 Slotted Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item	—	—
No.	Size	mm
77715	3.0 + 4.5mm	30
77716	4.0 + 6.0mm	30
77717	5.5 + 6.5mm	30

Wiha Slotted Insert & Power Bits



720 Slotted Insert Bits. 5/16" Hex Drive, Length 41mm

Item No.	mm	Inch	mm	pkg.	lbs.
72049	8.0	.315	1.6	10	.31
72050	10.0	.393	1.6	10	.46
72051	12.0	.472	2.0	10	.56



720 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel. 5/16" Hex Drive.

Item No.	mm	mm	Inch	mm	lbs.
72031	1.6	8.0	.315	41	.08
72039	1.6	10.0	.393	41	.10
72047	2.0	12.0	.472	41	.12



740 Slotted Power Bits, 1/4" Hex Drive, Length 2.75"/70mm

Item No.	mm	Inch	mm	Inch	pkg.
74033	2.5	.098	0.4	.015	10
74034	3.0	.118	0.5	.020	10
74035	3.5	.139	0.6	.024	10
74036	4.0	.157	0.8	.020	10
74039	5.5	.216	1.0	.032	10
74041	6.5	.255	1.2	.039	10



739 Slotted Power Bits, 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack

Item No.	mm	Inch	mm	Inch	pkg.
73905	2.5	.098	0.4	.015	1
73906	3.0	.118	0.5	.020	1
73907	3.5	.139	0.6	.024	1
73908	4.0	.157	0.8	.020	1
73909	5.5	.216	1.0	.032	1
73910	6.5	.255	1.2	.039	1




710 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel.

Item No.	mm	mm	Inch	mm	lbs.
71051	0.6	4.5	.177	25	.03
71052	0.8	5.5	.216	25	.03
71053	1.2	6.0	.255	25	.03
71054	1.6	8.0	.315	25	.03



740 Slotted Power Bits. 1/4" Hex Drive, Length 2.0"/50mm 10pk. weight .20 lbs.

Item No.	mm	Inch	mm	Inch	pkg.
74003	3.0	.118	0.5	.020	10
74006	3.5	.139	0.6	.024	10
74009	4.0	.157	0.5	.020	10
74010	4.0	.157	0.8	.030	10
74012	4.5	.177	0.6	.024	10
74015	5.5	.216	0.8	.032	10
74018	6.5	.255	1.2	.039	10
74021	8.0	.315	1.2	.039	10
74023	8.0	.315	1.6	.063	10



740 Slotted Power Bit Packs, 2" CVM S2 modified tool steel.

Item No.	mm	mm	lbs.
74061	3.0	50	.05
74062	3.5	50	.05
74063	4.0	50	.05
74064	4.0	50	.05
74065	4.5	50	.05
74066	5.5	50	.05
74067	6.5	50	.06
74068	8.0	50	.08
74069	8.0	50	.08



74050 Slotted Power Bit Packs, 2" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74050 Set includes the following bits:

Slotted:	wt. .08	4.5, 5.5, 6.5 x 2" (50mm)
----------	---------	---------------------------

Wiha Slotted Power Blades



760 Slotted Power Blades
S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	mm	lbs.	pkg.
76035	2.5	.02	1
76036	3.0	.02	1
76037	4.5	.03	1
76038	5.5	.03	1
76039	6.0	.04	1




76093 5 Piece Slotted Blade Set

Item No.	lbs.	Set includes:
76093	.16	Slotted: 2.5, 3.0, 4.5, 5.5, 6.0mm x 90mm

Pozidriv® Bits

The ideal multi-purpose tools to meet production requirements for both quality and performance

Impact resistant
modified CVM, tool
steel, hardened



Pozidriv®

Suitable for all
applications for both
manual and machine
Hardness HRC 59-61

PoziDriv® Insert & Power Bits



10 bit
pack

712 Pozidriv® Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71200	0	25	10	.10
71201	1	25	10	.10
71202	2	25	10	.10
71203	3	25	10	.10



2 bit
pack

712 Pozidriv® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
71250	0	25	.03
71251	1	25	.03
71252	2	25	.03
71253	3	25	.04



71254 Pozidriv® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71254 Set includes the following bits:

wt. .04 1, 2, 3 x 1" (25mm)



2 bit
pack

777 Pozidriv® Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77710	#1 + #2	30



10 bit
pack

742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74203	1	50	10	.24
74212	2	50	10	.25
74221	3	50	10	.26




2 bit
pack

742 Pozidriv® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74262	2	50	.06



10 bit
pack

742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item			
No.	Size	mm	pkg.
74201	0	70	10
74205	1	70	10
74214	2	70	10



2 bit
pack

739 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack

Item			
No.	Size	mm	pkg.
73901	0	70	1
73902	1	70	1
73903	2	70	1



742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 3.5"/90mm Single Pack

Item				
No.	Size	mm	pkg.	lbs.
74231	1	90	1	.03
74232	2	90	1	.04
74233	3	90	1	.05



10 bit
pack

742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 3.5"/90mm 10 Bit Pack

Item				
No.	Size	mm	pkg.	lbs.
74236	1	90	10	.34
74237	2	90	10	.46
74238	3	90	10	.53

Wiha Pozidriv® Power Blades



760 Pozidriv® Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76011	1	.03	1
76012	2	.04	1
76013	3	.04	1



76091 3 Piece Pozidriv® Blade Set

Item		
No.	lbs.	Pozidriv®: #1, 2,
76091	.12	3 x 90mm

Specialty

Highly resistant to wear and tear for a long tool life



 Tri-Wing

Tri-Wing Bits



10 bit pack

719 Triwing Insert Bits, 1/4"/25mm

Item No.			Size mm	pkg.	lbs.
71900	0		25	10	.10
71901	1		25	10	.10
71902	2		25	10	.10
71903	3		25	10	.10
71904	4		25	10	.13



2 bit pack

719 Tri-Wing Insert Bit Packs, 1"

Item No.			Size mm	lbs.
71949	0		25	.03
71950	1		25	.03
71951	2		25	.03
71952	3		25	.03
71953	4		25	.03
71913	5		25	.04




71954 Tri-Wing Insert Bit Packs, 1"

6 pc. bit pack.

71954 Set includes the following bits:

 Triwing: 0, 1, 2,
wt. .07 3, 4, 5 x 1" (25mm)

Bits



 Torq Set

Suitable for all applications for both manual & machine Hardness HRC 59-61



2 bit pack

749 Tri-Wing Power Bit Packs, 2"

Item No.			Size mm	lbs.
74961	4		50	.06

Wiha Tri-Wing Power Blades



760 Tri-Wing Power Blades

S2 modified tool steel. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.			Size lbs.	pkg.
76031	1		.02	1
76032	2		.02	1
76033	3		.03	1
76034	4		.04	1



76088 4 Piece Tri-Wing Blade Set

Item No.		Set includes:
76088	.16	3, 4 x 90mm

Torq Set Bits



10 bit pack

719 Torq Set Insert Bits, 1/4"

Item No.			Size mm	pkg.	lbs.
71921	0		25	10	.10
71922	1		25	10	.10
71923	2		25	10	.10
71924	3		25	10	.10
71907	4		25	10	.10
71909	5		25	10	.10
71906	6		25	10	.10
71908	8		25	10	.13
71910	10		25	10	.13



10 bit pack

749 Torq Set Power Bits, 1/4"/50mm

Item No.			Size mm	pkg.	lbs.
74911	4		50	10	.03
74912	5		50	10	.03
74913	6		50	10	.03
74914	8		50	10	.04
74915	10		50	10	.04



2 bit pack

719 Torq Set Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.			Size mm	lbs.
71911	4		25	.03
71912	5		25	.03
71957	6		25	.03
71958	8		25	.04
71959	10		25	.04



2 bit pack

749 Torq Set Power Bit Packs, 2"

CVM S2 modified tool steel.


Item No.			Size mm	lbs.
74964	4		50	.06
74965	5		50	.06
74966	6		50	.06
74967	8		50	.07
74968	10		50	.07

Specialty Bits

Highly resistant to wear & tear for a long tool life

 Spanner

Suitable for all applications for both manual and machine
Hardness HRC 59-61



Spanner Bits



10 bit pack

719 Spanner Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71914	4	25	10	.11
71916	6	25	10	.12
71918	8	25	10	.12
71920	10	25	10	.12



2 bit pack

719 Spanner Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
71963	4	25	.03
71964	6	25	.03
71965	8	25	.04
71966	10	25	.04

Wiha Spanner Power Blades



760 Spanner Power Blades

S2 modified tool steel. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76022	6	.03	1
76023	8	.04	1
76024	10	.04	1



76089 3 Piece Spanner Blade Set

Item		Set includes:
No.	lbs.	Spanner: #6, 8,
76089	.12	10 x 90mm

Terminal Block Xeno Bits



10 bit pack



714 Xeno Combination Terminal Block Power Bits, 1/4" Hex Drive, OAL 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
71452	1	50	10	.24
71453	2	50	10	.25



2 bit pack

714 Xeno Combination Terminal Block Power Bit Packs, 2" CVM S2 modified tool steel

Item			
No.	Size	mm	lbs.
71455	1	50	.06
71456	2	50	.06

XZN Insert Bits

Suitable for all applications for both manual and machine Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life



Triple Square

Impact resistant modified CVM, tool steel, hardened



2 bit pack

701 XZN Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
70143	M3	25	2	.04
70144	M4	25	2	.04
70145	M5	25	2	.04
70146	M6	25	2	.04
70147	M8	35	2	.04

Countersink & Drill Bits

High quality HSS steel, ground with radial relief. Universal application in metal, plastic and wood. Guarantees outstanding chip removal, chatter free operation & smooth surface finish.

90° Countersink Bit - 1/4" Shank



786 HSS 1/4" Drive Countersinks

High quality HSS steel, ground with radial relief. 1/4" Hex shank according to DIN 3126 C 6.3.

Item	  screw 					
No.	Size	Inch	mm	Inch	size	pkg
78615	6.3	.26	35	1.38	M3	1
78617	8.3	.33	35	1.38	M4	1
78619	10.4	.41	35	1.38	M5	1
78621	12.4	.49	35	1.38	M6	1
78622	16.5	.65	35	1.38	M8	1
78624	20.5	.81	35	1.38	M10	1

1/4" Shank High Speed Drill Bits



780 1/4" Shank Stubby High Speed Drill Bits DIN 3126 C 6.3.





Item				
No.	Size	Inch	pkg	lbs.
78002	1/16	1.26	1	.02
78005	3/32	1.41	1	.02
78008	1/8	1.57	1	.02
78011	5/32	1.73	1	.03
78015	3/16	1.97	1	.03
78018	1/4	1.97	1	.03

High Precision Tool Holder For Countersinks & Drill Bits



Quick release tool holder for Drills, Countersinks & Power bits

71480 CentroFix Bit Holder

Item					
No.	Size	Size	mm	Inch	lbs.
71480	1/4"	1/4"	60	2.3	.09

Wiha Power Blade Sets

Blade Holder For
Power Blades



76000 CentroFix Cushion Grip Blade Holder
Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26



76079 Canvas Folding Wallet

Holds 38 90mm power blades.

Item		
No.	Size	lbs. pkg.
76079	7-1/8" x 6" x 2"	.42 1



76099 37 Pc. Power Blade Set, In Durable Belt Pack Set includes cushion grip CentroFix Blade Holder & 36 interchangeable blades.

Item No. 76099  lbs. 2.06

Slotted: 2.5, 3.0, 4.5, 5.5, 6.0mm

Phillips: #0, 1, 2, 3

Security TORX®: T8s, T9s, T10s, T15s,

T20s, T25s, T27s, T30s

Security Hex Inch: 1/16", 5/64, 3/32, 7/64,

1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Pozidriv®: #1, 2, 3 & **Square:** #1, 2, 3

4" Nut Setters: 1/4, 5/16, 3/8"

Cushion Grip CentroFix Blade Holder

* 1/16" Standard Inch Hex Only



76085 9 Pc. Power Blade Nut Driver Set
30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No. 76085  lbs. .96

Inch: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"



76086 12 Pc. Power Blade Nut Driver Set
30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No. 76086  lbs. 1.22

Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm



76087 61 Pc. Power Blade Service Kit, In Durable Zipper Case Set includes Bit Holding Handle, MicroBit Storage Handle, 4mm to 1/4" Magnetic Adapter, 9 power blades, 46 bits & 3 nut setters.

Item No. 76087  lbs. 1.34

90mm Power Blades: Slotted: 4.5, 5.5, 6.0mm

Phillips: #1, 2, 3 & **Square:** #1, 2, 3

75mm Security TORX® Bits: T10s, T15s, T20s, T25s, T27s, T30s

MicroBits: Phillips: #000, 00, 0, 1, 2,

Slotted: .8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

Hex Inch: .028, .035, .050, 1/16, 5/64, 3/32,

7/64, 1/8, 9/64, 5/32"

Hex Metric: 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

Magnetic Nut Setters: 1/4, 5/16, 3/8"



76098 36 Pc. Power Blade Set, In Durable Belt Pack Set includes cushion grip CentroFix Blade Holder & 35 interchangeable blades.

Item No. 76098  lbs. 1.86

Slotted: 2.5, 3.0, 4.5, 5.5, 6.0mm

Phillips: #0, 1, 2, 3

Security TORX®: T8s, T9s, T10s, T15s,

T20s, T25s, T27s, T30s, T40s

Security Hex Metric: 2.5, 3.0, 4.0, 5.0mm

Pozidriv®: #1, 2, 3 & **Square:** #1, 2, 3

Spanner: #6, 8, 10 & **Tri-Wing:** #1, 2, 3, 4

Cushion Grip CentroFix Blade Holder



76084 12 Pc. Power Blade Inch & Metric Nut Driver Set 30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

Item No. 76084  lbs. 2.97


Inch: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"

Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm

Cushion Grip CentroFix Blade Holder

26inOne!

Includes:
13 double end bits
Locking bit holder
Pop-up bit access
Rugged Industrial Design
Cushion grip handle
Professional quality



“Grab & Go Tool Box”



Tradesman



Technician's



Industrial

77790 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 3.0+4.5, 5.5+6.5mm
- ⊕ **Phillips:** #1+2, #0+3 lbs.
- ⊕ **Pozidriv®:** #1+2 .45
- **Square:** #1+2, #0+3
- ⚙ **TORX®:** T10+T15, T20+T25
- ⬡ **Hex Inch:** 1/8+9/64, 5/32+3/16"
- ⬡ **Hex Metric:** 3.0+4.0, 5.0+6.0mm

Tradesman Bit Reload



77780 13 Pc. Double End Insert Bit Reload For the 26inOne (For #77790)

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 3.0+4.5, 5.5+6.5mm
- ⊕ **Phillips:** #1+2, #0+3 lbs.
- ⊕ **Pozidriv®:** #1+2 .14
- **Square:** #1+2, #0+3
- ⚙ **TORX®:** T10+T15, T20+T25
- ⬡ **Hex Inch:** 1/8+9/64, 5/32+3/16"
- ⬡ **Hex Metric:** 3.0+4.0, 5.0+6.0mm

77791 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ **Phillips:** #1+2, #0+3 lbs.
- ⊕ **Pozidriv®:** #1+2 .45
- **Square:** #1+2, #0+3
- ⚙ **TORX®:** T6+T7, T8+T9, T10+T15, T20+T25, T27+T30

Technician's Bit Reload



77781 13 Pc. Double End Insert Bit Reload For the 26inOne (For #77791)

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ **Phillips:** #1+2, #0+3 lbs.
- ⊕ **Pozidriv®:** #1+2 .14
- **Square:** #1+2, #0+3
- ⚙ **TORX®:** T6+T7, T8+T9, T10+T15, T20+T25, T27+T30



Twenty-Six
Screwdrivers
in One

Ultra Lite!
Ultra Compact!
Ultra Fast Access!
Ultra Quality!

77792 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 4.0+6.0mm
- ⊕ **Phillips:** #1+2 lbs.
- ⊕ **Pozidriv®:** #1+2 .45
- ⚙ **TORX®:** T8+T9, T10+T15, T20+T25, T27+T30
- ⬡ **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ⬡ **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm

Industrial Bit Reload



77782 13 Pc. Double End Insert Bit Reload For the 26inOne (For #77792)

Includes the following 1/4" double end bits:

- ⌚ **Slotted:** 4.0+6.0mm
- ⊕ **Phillips:** #1+2 lbs.
- ⊕ **Pozidriv®:** #1+2 .14
- ⚙ **TORX®:** T8+T9, T10+T15, T20+T25, T27+T30
- ⬡ **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ⬡ **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm

Ultra Driver Accessories



Fits 26inOne
Ultra Driver



Fits 26inOne
Ultra Driver

77740 Valve Stem Double End Tool, 2 Pack CVM steel, hardened.

Item			
No.	mm	Inch	lbs.
77740	30	1.18	.02

77741 1/4" Socket Adapter 1/4" Hex to 1/4" Square Drive. CVM steel, hardened.

Item			
No.	mm	Inch	lbs.
77741	30	1.18	.01

Ultra Driver Bonus Pack



77795 24 Piece Cushion Grip Ultra Driver 26inOne Bonus Pack

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes:

- ➊ **Slotted:** 3.0+4.5, 4.0+6.0, 5.5+6.5mm lbs.
- ➋ **Phillips:** #1+2, #0+3 .60
- ➌ **Pozidriv®:** #1+2
- ➍ **Square:** #1+2, #0+3
- ➎ **TORX®:** T6+T7, T8+T9, T10+T15, T20+T25, T27+T30
- ➏ **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ➐ **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm

1/4" Hex to 1/4" Square

Socket Adapter

Double End Valve Stem Tool

Combo Pliers & Bit Set

BiCut SuperCut & Ultra Driver

26inOne!



77786 15 Pc. Ultra Driver & Pliers Set With BiCut SuperCut & Ultra Driver Bit Set

Item No. 77786 lbs. 1.17

8.0" Soft Grip Vinyl BiCut SuperCut

For cutting various materials from soft to extremely hard. Double the power at the press of a button.

Ultra Driver Double End Bits:

Slotted: 3.0+4.5, 5.5+6.5mm

Phillips: #1+2, #0+3

Pozidriv®: #1+2

Square: #1+2, #0+3

TORX®: T10+T15, T20+T25

Hex Inch: 1/8+9/64, 5/32+3/16"

Hex MM: 3.0+4.0, 5.0+6.0mm

Security Ultra Driver



77789 Security Cushion Grip Ultra Driver

26inOne Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes 1/4" double end Security bits:

- ➊ **Slotted/Phillips:** 5.5mm+#2 lbs.
- ➋ **Square:** #1+#2 lbs.
- ➌ **TORX®:** T8s+T9s, T10s+T15s, T20s+T25s, T27s+T30s .45
- ➍ **Hex Inch:** 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ➎ **Hex Metric:** 3.0+4.0, 5.0+6.0mm
- ➏ **Spanner:** #4+#6, #8+#10

Security Bit Reload

77783 13 Pc. Double End Insert Bit Reload For the 26inOne (For #77789)

Includes the following 1/4" double end bits:

- ➊ **Slotted/Phillips:** 5.5mm+#2 lbs.
- ➋ **Square:** #1+#2 lbs.
- ➌ **TORX®:** T8s+T9s, T10s+T15s, T20s+T25s, T27s+T30s .14
- ➍ **Hex Inch:** 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ➎ **Hex Metric:** 3.0+4.0, 5.0+6.0mm
- ➏ **Spanner:** #4+#6, #8+#10



77785 13-Piece Cushion Grip Ultra Driver HVAC Series

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.


Includes the following 1/4" double end bits:

- ➊ **Slotted:** 3.0+4.5, 5.5+6.5mm lbs.
- ➋ **Phillips:** #1+2, #0+3 lbs.
- ➌ **Square:** #1+2
- ➍ **TORX®:** T10+T15, T20+T25
- ➎ **Hex Inch:** 5/32+3/16, 7/32+1/4, 3/8"

1/4" Hex to 1/4" Square Adapter

Double End Core Stem Valve

1/4" Valve Socket Adapter



HVAC Bit Reload

77784 13 Pc. Double End Insert Bit Reload For the HVAC Ultra Driver (For #77784)

Includes the following 1/4" double end bits:

- ➊ **Slotted:** 3.0+4.5, 5.5+6.5mm lbs.
- ➋ **Phillips:** #1+2, #0+3 lbs.
- ➌ **Square:** #1+2
- ➍ **TORX®:** T10+T15, T20+T25
- ➎ **Hex Inch:** 5/32+3/16, 7/32+1/4, 3/8"

1/4" Hex to 1/4" Square Adapter

Double End Core Stem Valve

1/4" Valve Socket Adapter

1/4" Sockets & Bit Set

Tradesman Ultra Driver & 1/4" To 1/4" Sq. Drive Sockets

26inOne!



77793 29 Pc. Ultra Driver & Socket Set

1/4" Sockets, Adapter & Ultra Driver Bit Set

Item No. 77793 lbs. .92

1/4" Square Drive Sockets

Inch: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"

Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm

1/4" x 1/4" Socket Adapter

Ultra Driver Double End Bits:

Slotted: 3.0+4.5, 5.5+6.5mm

Phillips: #1+2, #0+3


Pozidriv®: #1+2

Square: #1+2, #0+3

TORX®: T10+T15, T20+T25

Hex Inch: 1/8+9/64, 5/32+3/16"

Hex MM: 3.0+4.0, 5.0+6.0mm



Cushion Grip



26 Tips on 13 Bits



Standard 1/4" Drive

Locking Bit Holder

26inOne! Ultra Driver Displays



30 Piece Display "Tradesman"

97790 30 Ultra Drivers Display

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97790

Tradesman 1/4" Double End Bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⚙️ TORX®: T10+T15, T20+T25
- ⬡ Hex Inch: 1/8+9/64, 5/32+3/16"
- ⬡ Hex Metric: 3.0+4.0, 5.0+6.0mm



30 Piece Display "Technician's"

97791 30 Ultra Drivers Display

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97791

Technician's 1/4" Double End Bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⚙️ TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30



30 Piece Display "Industrial"

97792 30 Ultra Drivers Display

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97792

Industrial 1/4" Double End Bits:

- Slotted: 4.0+6.0mm
- ⊕ Phillips: #1+2
- ⚙️ TORX®: T8+T9, T10+T15, T20+T25, T27+T30
- ⬡ Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ⬡ Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm



6 Pack "Tradesman"

97780 6 Pack Ultra Drivers Display Reorder

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97780

Tradesman 1/4" Double End Bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⚙️ TORX®: T10+T15, T20+T25
- ⬡ Hex Inch: 1/8+9/64, 5/32+3/16"
- ⬡ Hex Metric: 3.0+4.0, 5.0+6.0mm



6 Pack "Technician's"

97781 6 Pack Ultra Drivers Display Reorder

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97781

Technician's 1/4" Double End Bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⚙️ TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30



6 Pack "Industrial"

97782 6 Pack Ultra Drivers Display Reorder

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97782

Industrial 1/4" Double End Bits:

- Slotted: 4.0+6.0mm
- ⊕ Phillips: #1+2
- ⚙️ TORX®: T8+T9, T10+T15, T20+T25, T27+T30
- ⬡ Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- ⬡ Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm

CushionGrip Stubby Bit Sets



38043 SoftFinish® Cushion Grip Stubby Bit Holder with Wiha cushion grip handle & CVM tool steel shaft.

Set includes the following 1/4" bits:

- ➊ **Slotted:** 4.5, 6.0mm lbs.
- ➋ **Phillips:** #1, #2 .20
- ➌ **Pozidriv®:** #1, #2 .20



38048 SoftFinish® Cushion Grip Stubby Bit Holder with Wiha cushion grip handle & CVM tool steel shaft.

Set includes the following 1/4" bits:

- ➊ **Slotted:** 4.5, 6.0mm lbs.
- ➋ **Phillips:** #1, #2 .20
- ➌ **Square:** #1, #2 .20

Computer Tech Bit Set

12 Piece 1/4" Bit Set



38490 1/4" Computer Tech 12 Pc. Set with Wiha Cushion Grip Bit Holders. CVM steel, hardened shaft.

➊ **Slotted:** 4.5, 5.5, 6.5mm

➋ **Phillips:** #1, 2

➌ **TORX®:** T6, T15, T20

➍ **Security TORX®:** T8s, T10s

➎ **Magnetic Bit holder** 1/4" x 125mm

➏ **Stubby Bit Holder** 1/4" x 57mm

➐ lbs. .60

Wiha Insert Bit Blister Pack



72593 10 Pack Slotted, Phillips & Square Insert Bit Pack CVM S2 modified tool steel.

➊ **Slotted:** 4.5, 5.5, 6.0mm lbs.


➋ **Phillips:** #1, 2, 3 .16

➌ **Square:** #1, 2, 3

Wiha Cushion Grip Pop-Up Screwdriver Bit Sets



Handle
Diameter
1.45"



38032 Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

➊ **Slotted:** 4.5, 5.5, 6.0mm lbs.

➋ **Phillips:** 1, 2, 3 .42

➌ **TORX®:** T10, T15, T20, T25, T27, T30



38041 Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

➊ **Slotted:** 4.5, 6.0mm lbs.

➋ **Square:** 1, 2 .42

➌ **Phillips:** 1, 2 .42

➍ **Hex:** 4.0, 5.0, 6.0mm

➎ **TORX®:** T20, T25, T30



38035 Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

➊ **Slotted:** 4.5, 5.5, 6.5mm lbs.

➋ **Phillips:** 0, 1, 2 .42

➌ **TORX®:** T6, T15, T20, T25

➍ **Security TORX®:** T8s, T10s

Wiha Insulated Pop-Up Insert Bit Sets

Blades High
quality CV
steel, through
hardened

Bit holder
securely holds
bits in place

1000Volt Rated
10,000 Volt Tested

Convenient
rotating cap



38050 Insulated Pop-Up Bit Holder Set With 1/4" Insert Bits

Insulated cushion grip multi-component handle. Bit holder holds 1/4" Insert bits. Convenient rotating cap.

Item **Set includes the following bits:**

No. ➊ **Slotted:** 4.5, 5.5, 6.0mm

38050 ➋ **Phillips:** #0, 1, 2, 3

➌ **Square:** #1, 2, 3

➍ **Pozidriv®:** #1, 2, 3

➎ lbs. .46



38051 Insulated Pop-Up Bit Holder Set With 1/4" Insert Bits

Insulated cushion grip multi-component handle. Bit holder holds 1/4" Insert bits. Convenient rotating cap.

Item **Set includes the following bits:**

No. ➊ **Slotted:** 4.5, 5.5, 6.0mm

38051 ➋ **Phillips:** #0, 1, 2, 3

➌ **Square:** #1, 2, 3

➍ **TORX®:** T15, T20, T25

➎ lbs. .46

Wiha Bit Selectors

Compact size and easy bit selection make the Bit Selector an ideal maintenance tool



Slide out drawer
allows quick bit access
and secure storage



Plastic storage box
is compact, durable
and light weight

1/4" Magnetic Adapter
fits all standard
1/4" bits

Molded hex cavity in box end

Magnetic adapter fits into opening so tool case can be used as a handle on quick fastening jobs

792 Sets Bit-Selector Sets

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" magnetic bit holder can be used in power tools. Plastic storage box is compact, durable and light weight. Molded hex cavity turns box into handle for quick fastening jobs. Quick bit access with slide out drawer. Packaged in clear blister pack.



79243 Bit-Selector With Slotted, Phillips & TORX® Bits, Includes 1/4" Bit Holder & The Following 10 Bits:

- ↓ Slotted: 4.5, 5.5, 6.0mm
- ⊕ Phillips: #0, 1, 2, 3
- ⚙ TORX®: T10, T15, T20



79248 Bit-Selector With Slotted, Phillips & Square Bits, Includes 1/4" Bit Holder & The Following 10 Bits:

- ↓ Slotted: 4.5, 5.5, 6.0mm
- ⊕ Phillips: #0, 1, 2, 3
- ◻ Square: #1, 2, 3



71090 Bit-Selector With Slotted, Phillips & Hex 1/4" Bits, Includes Universal Magnetic 1/4" Bit Holder & The Following 9 Bits:

- ↓ Slotted: 4.5, 5.5, 6.5mm
- ⊕ Phillips: #1, 2, 3
- ⬮ Hex Inch: 1/8, 5/32, 3/16"

Wiha 1/4" Ratchet & Impact Bit Sets




76889 32 Piece Impact Rated Bit Set

Set includes 72 tooth mini ratchet, 1/4" SlimFix locking magnetic bit holder with quick release, 1/4" hex to 1/4" square adapter and Includes 3 Phillips hi-vis yellow impact bits.

Item No.	⊕ Phillips: #1, #2, #3 Blue
	⊕ Phillips: #1, #2, #3 Yellow
76889	◻ Square: #1, #2, #3
	⊕ Pozidriv®: #1, #2, #3
	⚙ TORX®: T10, T15, T20, T25, T27, T30, T40
	⬮ Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	⬮ Hex Metric: 3.0, 4.0, 5.0, 6.0mm

In metal storage box




74996 Ratchet Bit Set, 35 Pcs. Includes: Wiha 1/4" ratchet bit handle, bit holder, Hex/Sqr. Adapter & 33 Insert bits.

Item No. 74996 1/4" Ratchet Bit Set

- ⬮ Slotted: 5.5, 6.0mm
- ⊕ Phillips: #0, 1, 2, 3
- ◻ Square: #1, 2
- ⚙ TORX®: T8, T10, T15, T20, T25, T27, T30
- ⬮ Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
- ⬮ Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
- ⬮ 1/4" Magnetic Bit Holder
- 1/4" Hex to 1/4" Square Adapter
- ⬮ lbs. .80

Wiha 1/4" Ratchet & Bit Sets



74992 Ratchet Bit Set, 29 Pcs. In Canvas Pouch. Includes Wiha 1/4" ratchet bit handle, bit holder & 27 Insert bits.

Item No. 1/4" Ratchet Bit Set

74992 Set includes the following bits:

- ⬮ Slotted: 5.5, 6.0mm/Phillips: #0, 1, 2
- ◻ Square: #1, 2 / Pozidriv®: #1, 2
- ⚙ TORX®: T8, T9, T10, T15, T20, T25
- ⬮ Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0mm
- ⬮ Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"
- ⬮ 1/4" Bit Holder
- ⬮ lbs. .90

Wiha Security Bits Collector Sets



71990 Bits Collector with Security TORX®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 39 Pc. Set includes: Handle, 1/4" bit holder, 1/4" Bit holding socket adapter, storage box & the following 1/4" bits:

-  **Security TORX:** T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
-  **Security Hex:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
-  **Tri-Wing:** 1, 2, 3, 4
-  **Torq Set:** 6, 8, 10
-  **Spanner:** 4, 6, 8, 10
-  **Slotted:** 6.0, 8.0mm
-  **Phillips:** 1, 2
-  **Pozidriv®:** 0, 1, 2, 3
-  **Square:** 1, 2, 3

Wiha Security Bits Collector With Extra Fine 72 Tooth Ratchet



71988 Bits Collector with Security TORX®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 38 Pc. Set includes: 1/4" Bit Holding Ratchet, 1/4" magnetic bit holder, storage box and 1/4" Insert bits:

- | | |
|---|---|
|  | Security TORX®: T8s, T10s, T15s,
T20s, T25s, T27s, T30s, T40s |
|  | Security Hex: 5/64, 3/32,
7/64, 1/8, 9/64, 5/32" |
|  | Tri-Wing: 1, 2, 3, 4 |
|  | Torq Set: 6, 8, 10 |
|  | Spanner: 4, 6, 8, 10 |
|  | Slotted: 6.5, 8.0mm |
|  | Phillips: 1, 2 |
|  | Pozidriv®: 0, 1, 2, 3 |
|  | Square: 1, 2, 3 |



71991 Bits Collector with Security TORX®, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 39 Pc. Set includes: Handle, 1/4" SlimFix bit holder & 1/4" Bit holding socket adapter, storage box & the following 1/4" bits:

- | | |
|---|--|
|  | Security TORX®: T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s |
|  | Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32" |
|  | Tri-Wing: 1, 2, 3, 4 |
|  | Torq Set: 6, 8, 10 |
|  | Spanner: 4, 6, 8, 10 |
|  | Slotted: 6.5, 8.0mm |
|  | Phillips: 1, 2 |
|  | Pozidriv®: 0, 1, 2, 3 |
|  | Square: 1, 2, 3 |



71095 Bits Collector with Phillips & Hex Inch bits. 51 Piece Set Includes: 1/4" SlimFix Bit Holder, storage box and the following 1/4" bits:

- | | | |
|---|---|---|
| |  | 10 Each Phillips: 1, 2 & |
|  | | 5 Phillips: 3 |
| lbs. |  | 10 Each Hex Inch: 1/8, 3/16" & |
| 1.24 | | 5 Hex Inch: 5/32" |



71994 Bits Collector with TORX®, Slotted, Phillips, Pozidriv®, Square & Hex Bits.
38 Pc. Set Includes: Handle, 1/4" bit holder, storage box & the following 1/4" bits:

- | | |
|---|---|
|  | TORX® T7, T8, T9, T10, T15, T20,
T25, T27, T30, T40 |
|  | Square: 1, 2, 3 & Pozidriv®: 1, 2, 3 |
|  | Slotted: 4.5, 5.5, 6.0mm |
|  | Phillips: 0, 1, 2, 3 |
|  | Hex Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm |
|  | Hex Inch: 1/16, 5/64, 3/32,
1/8, 5/32, 3/16, 7/32, 1/4" |

NOTES:

Wiha XSelector & XLSelector Bit Sets

Compact size and easy bit selection make the Wiha XSelector an ideal maintenance tool

XLSelector Pocket Sized
5.3" x 3.1" x .7"

XSelector Pocket Sized
3 1/8" x 2 1/8" x 1/2"

These handy sets include 10 hardened bits of CVM steel. 1/4" Quick Release holder can be used in power tools. Quick bit access through integrated bit-clamp.

Easy bit access hinged cover




79443 XSelector Bit Set With Slotted, Phillips, and TORX® Bits Set Includes 1/4" Magnetic Holder & the following 10 bits:

- Slotted: 5.5, 6.5, 8.0mm
- Phillips: #0, 1, 2, 3
- TORX®: T10, T15, T20



79495 XLSelector Bit Set With Slotted, Phillips, TORX®, Hex Bits, 31 Pc. Set Includes: 1/4" Magnetic Bit Holder & 30 Insert Bits:

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2, 3
- TORX®: T6, T7, T8, T9, T10, T15, T20, T25
- Metric Hex: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
- Inch Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



79490 XLSelector Security Bit Set, 31 Pc. Set Includes Universal Bit Holder-magnetic and the following 30 bits:

- Slotted: 6.0mm
- Phillips: #1, 2
- Torq Set: #6, 8, 10
- Square: #1, 2
- Triwing: #2, 3, 4, 5
- Pozidriv: #1, 2
- Spanner: #4, 6, 8, 10
- Security TORX®: T8s, T10s, T15s, T20s, T25s
- Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"



79499 XLSelector 1/4" Ratchet & Bit Set
Wiha 1/4" ratchet bit handle, bit holder & 15 Insert bits Includes:

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2
- TORX®: T7, T8, T9, T10, T15, T20, T25
- Square: #1, 2
- lbs. .56

Wiha Accessory Bag



91473 General Purpose Zipper Bag

Heavy duty nylon. Keeps Wiha tools & accessories organized.

Item	No.	Size
91473		9.75" x 7.25"



79493 XLSelector Security Bit Set, 31 Pc. Set Includes Universal Bit Holder-magnetic and the following 30 bits:

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #1, 2, 3
- Square: #1, 2
- TORX®: T7, T8, T9, T10, T15, T20, T25
- Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
- Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
- lbs. .64



79491 XLSelector 1/4" Ratchet & Bit Set
Wiha 1/4" ratchet bit handle, bit holder & 15 Insert bits Includes:

- Slotted: 4.5, 6.0mm
- Phillips: #1, 2, 3
- Square: #1, 2
- Pozidriv: #1, 2
- Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

Easy bit access with hinged cover



CentroFix Security Bit Set



71987 29pc Security Bit Set With CentroFix Bit Holder Handle

1/4" CRV steel, hardened shaft.

Security TORX®: T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Tri-Wing: #4, 5

Torq Set: #5, 8

Spanner: #6, 8, 10

Pozidriv: #2

Square: #1, 2

CentroFix Cushion Grip Handle

Magnetic Bit holder 1/4"

Socket Adapter 1/4"

lbs. 1.18

Wiha Power Bit Belt Packs



74983 Power Bit Belt Pack With Slotted, Phillips & TORX® Bits Includes the following 10 bits:

Slotted: 4.5, 5.5, 6.5mm **lbs.**

Phillips: #1, 2, 3

TORX®: T10, T15, T20, T25 .30



74988 Power Bit Belt Pack With Slotted, Phillips & Square Bits Includes the following 10 bits:

Slot: 3.0, 4.5, 5.5, 6.5mm **lbs.**

Phillips: #1, 2, 3

Square: #1, 2, 3

Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box



With
Certificate
of Calibration

28590 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.

Item No. **Slotted:** 1.5, 2.0, 3.0, 4.0mm

28590 Phillips: #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15

Hex Inch: .050, 1/16, 5/64, 3/32,

lbs. 7/64, 1/8, 9/64, 5/32

1.35 28504 - Handle Range 7.5-20 In/lbs.



With
Certificate
of Calibration

28593 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

Item No. **Slotted:** 1.5, 2.0, 3.0, 4.0mm

28593 Phillips: #00, #0, #1

TORX®: T6, T7, T8, T9, T10, T15

lbs. **Hex Inch:** .050, 1/16, 5/64, 3/32,

1.35 7/64, 1/8, 9/64, 5/32

28501 - TorqueVario-S handle

Range 15 - 80 Inch/oz (+/- 10%)



53 Pc. Set

With Certificate
of Calibration

28595 53 Pc. TorqueVario-S Bit Set, In Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

Item No. **28595**

Slotted: 4.5, 5.5, 6.5, 8.0mm

lbs. **Phillips:** #0, #1, #2, #3

2.85 TORX®: T6, T7, T8, T9, T10, T15,

T20, T25, T27, T30

Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8,

9/64, 5/32, 3/16"

Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0,

5.0, 6.0, 8.0mm

Pozidriv: #0, #1, #2, #3

Torq Set: #4, #5, #6, #8

Square: #1, #2, #3

Triwing: #0, #1, #2, #3, #4

28506-Handle Range 10 - 50 In/lbs.

28581 - 1/4" Bit Holder



59 Pc. Set

With
Certificate
of Calibration

28589 59 Piece TorqueVario-S Bit Set, In Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item No. **Slotted:** 4.5, 5.5, 6.5mm

28589 Phillips: #0, 1, 2

TORX®: T5, T6, T7, T8, T9, T10,

lbs. T15, T20, T25, T30

2.73 Hex Inch: .050, 1/16, 5/64, 3/32,

7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Hex Metric: 1.5, 2.0, 2.5, 3.0,

4.0, 5.0, 6.0mm

Pozidriv: #1, 2 & **Square:** #1, 2, 3

Inch Sockets: 5/32, 3/16, 7/32, 1/4,

9/32, 5/16, 3/8"

Metric Sockets: 4.0, 4.5, 5.0, 5.5,

6.0, 7.0, 8.0mm

3 Handles: 15-80 Inch/oz., 5-10 &

10-50 In/lbs.


Wiha Bit Holders

For working in confined spaces




28103 Magnetic 1/4" Bit Holder With Wiha SoftFinish® Stubby Handle Stainless steel with strong magnet. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	mm	Inch	lbs.	pkg.
28103	1/4"	57	2.2	.11	1




38800 Bit Holder With Wiha T-handle Retainer out of stainless steel. Wiha-T-handle high quality plastic, impact resistant.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38800	1/4"	150	6.0	80	3.0	.18	1




38801 Bit Holders With Wiha Soft Grip T-handle Chrome-V-Moly, hardened, hard chrome finish. Wiha soft grips are molded on with through the handle side torque drive.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38801	1/4"	178	7.0	102	4.0	.18	1




52650 1/4" Bit holding Screwdriver, With Wiha MicroFinish Handle Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil & grease resistant.

Item	
No.	Size mm Inch mm Inch lbs. pkg.
52650	1/4" 125 5.0 244 9.6 .24 1



38600 Bit Holder 1/4" with Retaining Ring With Flexible Shaft Wiha-SoftFinish® handle multi-component, cushion grips.

Item								
No.	Inch	mm	Inch	mm	Inch	mm	lbs.	pkg.
38600	1/4"	150	5.9	268	10.6	.30	1	



28489 Drive-Loc VI Bit Holder High alloy CVM steel, through hardened, hard chrome finish. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	Extends		lbs.	pkg.
28489	1/4"	1-3/4" to 4-7/8"	.36	1	



384 1/4" Magnetic Bit Holding Drivers, With Wiha SoftFinish® Handle Ergonomic cushion grip, magnetic, holds bit and screw. Shaft CVM steel, nickel-plated.


Item						
No.	Size	mm	Inch	mm	Inch	lbs.
38450	1/4"	125	5.0	240	9.46	.23
38460	1/4"	300	11.8	400	15.69	.37

"SlimFix"
Impact Rated



71496 "SlimFix" Impact Rated Locking 1/4" Bit Holder For 1/4" Insert Bits Faster, sleeker, more productive "SlimFix" for instant bit changes. Just 10.9mm / 0.42 Diameter. Bit Locks securely in place. CV hardened sleeve.

Item					
No.	Size	Size	mm	Inch	lbs.
71496	1/4"	1/4"	66.5	2.62	.06



Item					
No.	Size	mm	Inch	lbs.	
71475	2.4"	60	2.4	.06	
71476	3.9"	100	3.9	.09	
71477	5.9"	150	5.9	.11	
71478	7.9"	200	7.8	.14	
71479	9.9"	250	9.8	.17	

71474 5 Pc. Protorn 1/4" Quick Release Bit Holder Set With magnets
Includes: 60mm, 100mm, 150mm, 200mm, 250mm .58



Item					
No.	Size	Size	mm	Inch	lbs.
71492	1/4"	1/4"	62	2.4	.10 Non Magnetic
71493	1/4"	1/4"	76	3.0	.10 Magnetic

Wiha Bit Holders



711 Universal Magnetic Bit Holder, 1/4" For Insert Bits

Item No.	Size	Size	mm	Inch	lbs.
71130	1/4"	1/4"	74	2.9	.06
71131	1/4"	1/4"	59	2.3	.05



71139 Magnetic Bit Holder, 1/4" For Insert Bits

Item No.	Size	Size	mm	Inch	lbs.
71139	1/4"	1/4"	100	4.0	.08



Retaining Ring Bit Holders

Magnetic



714 Bit Holder, Retaining Ring & Magnetic

Item No.	Size	Size	mm	Inch	lbs.
71431	1/4"	1/4"	60	2.4	.05
71433	1/4"	1/4"	67	2.6	.05
71435	1/4"	1/4"	100	3.9	.07
71437	1/4"	1/4"	150	5.9	.11
71439	1/4"	1/4"	200	7.8	.13
71441	1/4"	1/4"	253	10.0	.16

71499 5 Pc. Bit Holder Set In Vinyl Pouch
Includes: 60mm, 100mm, 150mm, 200mm, 253mm lbs. .60



71494 Stainless Steel Bit Holder, 1/4" For Insert Bits

Internal C-ring for bit holding & magnet.

Item No.	Size	Size	mm	Inch	lbs.
71494	1/4"	1/4"	54	2.1"	.05



38060 Mini Bit Ratchet & SlimFix Set

Extra fine 72 tooth ratchet, rugged drop forged steel. SlimFix impact rated locking 1/4" bit holder. Accepts 1/4" Bits.

Item No. Includes Phillips: #2

38060 lbs. .28

High Precision Tool Holder



Quick release tool holder for Drills, Countersinks & Power bits

71480 CentroFix Bit Holder

Item No.	Size	Size	mm	Inch	lbs.	pkg.
71480	1/4"	1/4"	60	2.4	.09	1



- Narrow Profile
- One handed bit changes
- Internal bit lock mechanism



71491 ClickFix Bit Holder, Magnetic For Insert Bits

Item No.	Size	Size	mm	Inch	lbs.	pkg.
71491	1/4"	1/4"	75	2.9	.07	1



28180 ESD Safe Stubby 1/4" Bit Holder

With Ring Retainer, Wiha-SoftFinish® Cushion Grip Handle, IEC 61340-5-1, DIN 3126, ISO 1173 Dissipative SoftFinish® cushion grip handle, multi-component, ESD Safe surface resistance 10⁶ - 10⁹ Ohm.

Item No.	Inch	mm	Inch	lbs.	pkg.
28180	1/4"	57	2.2	.11	1



38701 ESD Safe Quick Release 1/4" Bit Holder, With Wiha-SoftFinish® Cushion Grip Handle, IEC 61340-5-1, DIN 3126, ISO 1173 Stainless steel with retaining ring bit holder. Dissipative SoftFinish® cushion grip handle, multi-component, ESD Safe surface resistance 10⁶ - 10⁹ Ohm.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
38701	1/4"	148	5.8	38	1.5	.24	1



38790 ESD Safe 1/4" Quick Release Blade Holder Set 20 Pc. Set With Interchangeable Blades & Quick Release Blade Holder Extension Blades are CVM tool steel, hardened.

Item No. 38790 lbs. .67

Slotted: 2.5, 3.0, 3.5, 4.0, 5.5, 6.5mm

Phillips: #0, 1, 2

TORX®: T6, T7, T8, T9, T10, T15

Pozidriv®: 0, 1, 2

Wiha SYSTEM 4 Micro Bits - On 4mm Hex Stock



75800 SYSTEM 4 Standard Precision Bit

Handle Accepts all SYSTEM 4 Series bits.
110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle 110mm/4.3" OAL

Advantages:

- For working in ESD sensitive applications
Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item					
No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06



758 SYSTEM 4 Inch Nut Setters

CVM steel, hardened, on 4 mm hex stock.

Item No.				
Inch	mm	mm	Inch	lbs.
75810	5/64	30	1.2	.01
75811	3/32	30	1.2	.01
75812	7/64	30	1.2	.01
75813	1/8	30	1.2	.01
75814	9/64	30	1.2	.01
75815	5/32	30	1.2	.01
75816	3/16	30	1.2	.01
75817	7/32	30	1.2	.01



758 SYSTEM 4 Metric Nut Setters

CVM steel, hardened, on 4 mm hex stock.

Item No.				
Metric	mm	mm	Inch	lbs.
75820	2.0	30	1.2	.01
75821	2.5	30	1.2	.01
75822	3.0	30	1.2	.01
75823	3.5	30	1.2	.01
75824	4.0	30	1.2	.01
75825	4.5	30	1.2	.01
75826	5.0	30	1.2	.01
75827	5.5	30	1.2	.01



750 SYSTEM 4 Slotted Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75008	0.8	28	1.1	.01
75012	1.2	28	1.1	.01
75015	1.5	28	1.1	.01
75018	1.8	28	1.1	.01
75020	2.0	28	1.1	.01
75025	2.5	28	1.1	.01
75030	3.0	28	1.1	.01
75035	3.5	28	1.1	.01
75040	4.0	28	1.1	.01



753 SYSTEM 4 Hex Metric Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75307	.7	28	1.1	.01
75309	.9	28	1.1	.01
75313	1.3	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01

753 SYSTEM 4 Hex Inch Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



751 SYSTEM 4 Phillips Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Size	mm	Inch	lbs.
75105	000	28	1.1	.01
75110	00	28	1.1	.01
75115	0	28	1.1	.01
75120	1	28	1.1	.01
75125	2	28	1.1	.01



757 SYSTEM 4 TORX® Micro Bits

CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75701	T1	28	1.1	.01
75702	T2	28	1.1	.01
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01




757 SYSTEM 4 Pentalobe Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Size	mm	Inch	lbs.
75743	PL1	28	1.1	.01
75744	PL2	28	1.1	.01
75745	PL3	28	1.1	.01
75746	PL4	28	1.1	.01
75747	PL5	28	1.1	.01
75748	PL6	28	1.1	.01

Wiha SYSTEM 4 Micro Bits - 10 Bit Packs

CVM steel, hardened,
on 4 mm hex stock.



Tips Exact fit,
precision machined


Bits High alloy
CVM steel,
hardened

**Use bits directly in handle or
with 4" bit extension**




756 SYSTEM 4 Slotted Micro Bits

Item No.	mm	mm	Inch	lbs.
75602	0.8	28	1.1	.06
75603	1.2	28	1.1	.06
75604	1.5	28	1.1	.06
75605	1.8	28	1.1	.06
75606	2.0	28	1.1	.07
75607	2.5	28	1.1	.07
75608	3.0	28	1.1	.07
75609	3.5	28	1.1	.07
75610	4.0	28	1.1	.08




756 SYSTEM 4 Phillips Micro Bits

Item No.	Size	mm	Inch	lbs.
75611	000	28	1.1	.06
75612	00	28	1.1	.06
75613	0	28	1.1	.06
75614	1	28	1.1	.07
75615	2	28	1.1	.07




756 SYSTEM 4 Pentalobe Micro Bits

Item No.	Size	mm	Inch	lbs.
75672	PL1	28	1.1	.06
75673	PL2	28	1.1	.06
75674	PL3	28	1.1	.07
75675	PL4	28	1.1	.07
75676	PL5	28	1.1	.07



756 SYSTEM 4 TORX® Micro Bits

Item No.	Size	mm	Inch	lbs.
75660	T1	28	1.1	.06
75661	T2	28	1.1	.06
75662	T3	28	1.1	.06
75663	T4	28	1.1	.06
75664	T5	28	1.1	.06
75665	T6	28	1.1	.06
75666	T7	28	1.1	.06
75667	T8	28	1.1	.07
75668	T9	28	1.1	.07
75669	T10	28	1.1	.07
75670	T15	28	1.1	.08
75671	T20	28	1.1	.08



756 SYSTEM 4 Inch Nut Setters

Item No.				
Inch	mm	mm	Inch	lbs.
75644	5/64	30	1.2	.07
75645	3/32	30	1.2	.07
75646	7/64	30	1.2	.07
75647	1/8	30	1.2	.07
75648	9/64	30	1.2	.08
75649	5/32	30	1.2	.08
75650	3/16	30	1.2	.08
75651	7/32	30	1.2	.09



756 SYSTEM 4 Metric Nut Setters

Item No.				
Metric	mm	mm	Inch	lbs.
75652	2.0	30	1.2	.07
75653	2.5	30	1.2	.07
75654	3.0	30	1.2	.07
75655	3.5	30	1.2	.07
75656	4.0	30	1.2	.08
75657	4.5	30	1.2	.08
75658	5.0	30	1.2	.08
75659	5.5	30	1.2	.09



756 SYSTEM 4 Hex Metric Micro Bits

Item No.	mm	mm	Inch	lbs.
75616	.7	28	1.1	.06
75617	.9	28	1.1	.06
75618	1.3	28	1.1	.06
75619	1.5	28	1.1	.07
75620	2.0	28	1.1	.07
75621	2.5	28	1.1	.07
75622	3.0	28	1.1	.08
75623	4.0	28	1.1	.08



756 SYSTEM 4 Hex Inch Micro Bits

Item No.	Inch	mm	Inch	lbs.
75628	.028	28	1.1	.06
75629	.035	28	1.1	.06
75630	.050	28	1.1	.06
75631	1/16	28	1.1	.06
75632	5/64	28	1.1	.06
75633	3/32	28	1.1	.07
75634	7/64	28	1.1	.07
75635	1/8	28	1.1	.07
75636	9/64	28	1.1	.08
75637	5/32	28	1.1	.08



75978 SYSTEM 4 Hex Metric Micro Bit Replacement Pack, 8-Piece

CVM steel, hardened, on 4 mm hex stock.

Item No.

75978 SYSTEM 4 Micro Bit Set

Hex Metric: 0.7, 0.9, 1.3, 1.5, 2.0,
2.5, 3.0, 4.0mm

lbs. .05

SYSTEM 4 Micro Bit Extension Blades



75900 Extension Blade For SYS 4 Micro Bits
Shaft CVM steel, hardened, corrosion protected.
Ball retainer bit extension for 4mm bits.

Item No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07



75901 Magnetic Bit Extension Blade For SYS 4 Micro Bits Shaft CVM steel, hardened, corrosion protected. Magnetic bit holder.

Item No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04

Micro Bit 4mm To 1/4" Socket Adapter



75806 Micro Bit 4mm to 1/4" Socket Adapter
CVM steel, hardened.

Item No.	mm	Inch	lbs.
75806	28	1.125	.02

1/4" Drive Micro Bit Tool Adapters



75802 Micro Bit To 1/4" Drive Insert Bit Adapter magnets to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75802	4.0	25	4.0	.01



75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter Uses spring clip non-magnetic to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75803	4.0	38	4.0	.02


Micro Bit 1/4" Drive Power Tool Adapter



75902 Micro Bit 1/4" Drive Power Tool Adapter Shaft CVM steel, hardened, corrosion protected. For 4mm bits. 2.3" OAL


Item No.	Size	mm	mm	lbs.
75902	4.0	60	4.0	.07

Wiha SYSTEM 4 Micro Bit Replacement Packs On 4mm Hex Stock



75982 SYSTEM 4 Hex Inch Micro Bit Replacement Pack, 10 Pcs.
CVM steel, hardened, on 4 mm hex stock.

Item No.	Hex Inch:	lbs.
75982	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	.06



75984 SYSTEM 4 Slotted Micro Bit Replacement Pack, 10 Pcs.
CVM steel, hardened, on 4 mm hex stock.


Item No.	Slotted:	lbs.
75984	0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm	.06

Wiha SYSTEM 4 Micro Bit Replacement Packs On 4mm Hex Stock




75986 SYSTEM 4 Phillips & Pentalobe Micro Bit Replacement Pack, 10 Pcs.
CVM steel, hardened, on 4 mm hex stock.

Item No.	Phillips:	Pentalobe:	lbs.
75986	#000, 00, 0, 1	PL1, PL2, PL3, PL4, PL5, PL6	.06



75987 SYSTEM 4 Slotted & Phillips Micro Bit Replacement Pack, 10 Pcs.
CVM steel, hardened, on 4 mm hex stock.


Item No.	Slotted:	Phillips:	lbs.
75987	1.5, 2.0, 2.5, 3.0, 3.5mm	#000, 00, 0, 1	.06



75988 SYSTEM 4 TORX Micro Bit Replacement Pack, 10 Pcs.
CVM steel, hardened, on 4 mm hex stock.


Item No.	TORX:	lbs.
75988	T1, T2, T3, T4, T5, T6, T7, T8, T9, T10	.06

Wiha SYSTEM 4 Micro Bits & Compact Bit Sets



75996 SYSTEM 4 Interchangeable Bit Set, 40 Pcs. Includes Wiha precision handle, bit extension & 38 interchangeable bits.

Item	SYSTEM 4
No.	Combination Bit Set
75996	Set with ESD Safe Precision Handle
Set includes the following bits:	
↓	Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
+	Phillips: 000, 00, 0, 1
✱	TORX®: T3, T4, T5, T6, T7, T8, T9, T10, T15
⬡	Hex Metric: 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬡	Hex Inch: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	100mm Bit Extension
↔	lbs. 1.04



75994 SYSTEM 4 Slotted/Phillips/Hex Metric/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.

Set includes Wiha precision handle, bit extension & 25 Wiha interchangeable bits.

Item	SYSTEM 4
No.	Combination Bit Set
75994	Set with ESD Safe Precision Handle
Set includes the following bits:	
↓	Slotted: 1.5, 2.0, 3.0, 4.0mm
+	Phillips: 000, 00, 0, 1
✱	TORX®: T3, T4, T5, T6, T7, T8, T9, T10, T15
⬡	Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
○	100mm Bit Extension
↔	lbs. .64



75995 SYS 4 Precision Interchangeable Bit Set, 26 Pcs. In Compact Fold Out Box

Sets includes Wiha precision handle, bit extension & 24 Wiha interchangeable bits.

Item	SYSTEM 4 Micro Bit Set
No.	Set with ESD Safe Precision Handle
75995	and the following bits:
✱	TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
⬡	Pentalobe: PL1, PL2, PL3, PL4, PL5, PL6
↓	Slotted: 1.5, 2.0, 2.5, 3.0mm
+	Phillips: #000, 00, 0, 1
○	100mm Bit Extension
↔	lbs. .54




75999 SYSTEM 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set, 26Pcs. Wiha precision handle, bit extension & 24 interchangeable bits.

Item No.	Combination Bit Set
75999	Set with Standard Precision Handle
Set includes the following bits:	
↓	Slotted: 1.5, 2.0, 3.0, 4.0mm
+	Phillips: 000, 00, 0, 1
⬡	Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬡	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	100mm Bit Extension
↔	lbs. .64



75395 SYS 4 Hex Inch & Metric Precision Interchangeable Bit Set, 18 Pcs. In Compact Fold Out Box. Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

Item No.	Combination Bit Set
75395	Set with Standard Precision Handle
Includes the following bits:	
⬡	Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬡	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	100mm Bit Extension
↔	lbs. .58



759 sets SYS 4 Slotted / Phillips / Hex In / TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box. Sets include your choice of Wiha precision handle, bit extension & 25 Wiha interchangeable bits.

Item	Handle Options for SYSTEM 4
No.	Combination Bit Sets
75991	Set with Standard Precision Handle
75992	Set with ESD Safe Precision Handle
Sets include the following bits:	
↓	Slotted: 1.5, 2.0, 3.0, 4.0mm
+	Phillips: 000, 00, 0, 1
✱	TORX®: T3, T4, T5, T6, T7, T8, T9, T10, T15
⬡	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	100mm Bit Extension
↔	lbs. .64

Wiha SYSTEM 4 Micro Bit Sets



75980 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs. Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 36 Micro Bits.

Item No. SYSTEM 4 Micro Bit Set

75980 Includes The Following Bits:

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1, 2
- ✱ **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
- ⬡ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬠ **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- ⚖ **lbs.** .38



75968 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs. Includes Wiha ESD Safe Precision Handle, Micro Bit Storage Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

Item No. SYSTEM 4 Micro Bit Set

75968 Includes The Following Bits:

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1, 2
- ✱ **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- ⬡ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬡ **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬠ **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- ⊖ **Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- ⊖ **Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- ⚖ **lbs.** .70

In Zipper Storage Case



75993 SYSTEM 4 Premium ESD Safe Micro Bit Set, 28 Pcs. Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension, ESD Safe Tweezers & 21 Micro Bits.

Item No. SYSTEM 4 Micro Bit Set

75993 Micro Bits:

- † **Slotted:** 0.8, 1.5, 2.0, 2.5, 3.0, 3.5mm
- ⊕ **Phillips:** 000, 00, 0, 1, 2
- ✱ **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
- ESD Safe Tweezers:**
- 5SA ESD, 7aSA ESD, 2ASA ESD, AASA ESD, OOSA ESD**
- ⚖ **lbs.** .95

75971 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs. Includes Wiha ESD Safe Precision Handle, Micro Bit Storage Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

Item No. SYSTEM 4 Micro Bit Set

75971 Includes The Following Bits:

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- ⊕ **Phillips:** 000, 00, 0, 1, 2
- ✱ **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- ⬡ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- ⬡ **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⬠ **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- ⊖ **Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- ⊖ **Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- ⚖ **lbs.** .96



75965 SYSTEM 4 Master Tech ESD & Ratchet With Micro Bits, 65 Pieces In Storage Box. Includes Wiha precision ESD Safe handle, micro bit extension, 72 tooth 1/4" ratchet & 62 interchangeable micro bits.

Item Includes the following micro bits:

- No. 1** **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- No. 2** **Phillips:** 000, 00, 0, 1
- No. 3** **TORX®:** T3, T4, T5, T6, T7, T8, 1.16 T9, T10, T15, T20
- No. 4** **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- No. 5** **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- No. 6** **Nut Drivers Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- No. 7** **Nut Drivers Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- No. 8** **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- No. 9** **Magnetic 1/4" to 4mm Adapter**



75977 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs. Includes Wiha ESD Safe Precision Handle, ESD Safe Tweezers, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

Item No. SYSTEM 4 Micro Bit Set



75977 Includes The Following Bits:

- No. 1** **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- No. 2** **Phillips:** 000, 00, 0, 1, 2
- No. 3** **TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- No. 4** **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- No. 5** **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- No. 6** **Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- No. 7** **Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- No. 8** **Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- No. 9** **ESD Fine Round Point Tweezers 3cSA**

Technician's Micro Bit Sets

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension

Surface resistance of handles is $10^6 - 10^9$ Ohms



75093 SYSTEM 4 Slotted, Phillips, **TORX**® Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set


75093 Set with ESD Safe Precision Handle

● **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⚙ **TORX:** T6, T7, T8, T9, T10, T15, T20

lbs. .17 ○ **100mm Bit Extension**



75094 SYS 4 Slotted, Phillips, Hex Inch Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75094 Set with ESD Safe Precision Handle

● **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⚙ **Hex Inch:** .035, .050, 1/16, 5/64,

lbs. 3/32, 7/64, 1/8"

.17 ○ **100mm Bit Extension**



75096 SYSTEM 4 Hex Inch & Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set


75096 Set with ESD Safe Precision Handle

⚙ **Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

⚙ **Hex Metric:** .9, 1.3, 1.5, 2.0,

lbs. 2.5, 3.0, 4.0mm

.17 ○ **100mm Bit Extension**



75097 SYS 4 Slotted, Phillips & 5Point Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set


75097 Set with ESD Safe Precision Handle

● **Slotted:** 1.2, 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 000, 00, 0, 1, 2

⚙ **Pentalobe:** PL1, PL2, PL3, PL4

.17 ○ **100mm Bit Extension**



75095 SYS 4 Slotted, Phillips, Hex Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75095 Set with ESD Safe Precision Handle

● **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⚙ **Hex Metric:** .9, 1.3, 1.5, 2.0,

lbs. 2.5, 3.0, 4.0mm

.17 ○ **100mm Bit Extension**



91109 Black Cartridge Holder

Holds 14 Micro bits 4mm. 1" OAL

Item No.	mm	mm	lbs.
91109	4.0	25.4	.01



Micro Bit Handle Storage Sets

Micro precision bits on 4mm hex drive



Storage handle

Bits hardened for extreme durability

Bits of exclusive CRM-72 tool steel



75981 Micro Bit Handle Storage Slotted & Phillips Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75981 ● **Slotted:** 1.2, 1.5, 2.0mm

lbs. .12 ⊕ **Phillips:** 000, 00, 0



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75983 ⚙ **Hex Inch:** .050, 1/16, 5/64,

lbs. .12 3/32, 7/64, 1/8"



75985 Micro Bit Handle Storage **TORX**® Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75985 ⚙ **TORX:** T3, T4, T5, T6, T7, T8

lbs. .12




75805 SYS 4 Micro Bit Storage Handle

Accepts SYS 4 Series bits. 108mm/4.25" OAL

Item No.	mm	Inch	lbs.
75805	4.0	.1574	.05


Item No.		Set includes
70486	lbs.	1/4" R, 5/16" Y, 3/8" Bl
	1.21	7/16" Br, 1/2" O, 9/16" Bk

Wiha Inch & Metric Nut Setters




704 Metric Nut Setters Standard With Permanent Industrial Magnet, 1/4" Hex

Item No.	Size	mm	lbs.
70437	5.0	55	.04
70438	5.5	55	.05
70440	6.0	55	.05
70442	7.0	55	.05
70445	8.0	55	.05
70448	10.0	55	.06
70450	13.0	55	.07




704 Nut Setters Standard. 1/4" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70462	2.5"	65	.06
70463	4.0"	102	.10
70464	6.0"	152	.15
70466	12.0"	305	.27




704 Nut Setters Standard. 5/16" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70468	2.5"	65	.07
70469	4.0"	102	.12
70470	6.0"	152	.17
70472	12.0"	305	.28



704 Nut Setters Standard. 3/8" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70474	2.5"	65	.08
70476	4.0"	102	.14
70477	6.0"	152	.18
70479	12.0"	305	.41




704 Nut Setters Standard. 1/4" Hex Inch

Item No.	Size	mm	lbs.
70424	1/4	55	.05
70427	5/16	55	.05
70430	3/8	55	.06



70494 3 pc. Hex Metric Nut Setter Set Permanent industrial magnet. 55mm OAL Hex Metric Nut Setters.

Item No.	lbs.	Set includes the following:
70494	.21	7, 8, 10 x 55mm



70490 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 65mm OAL Hex Inch Nut Setters.

Item No.	lbs.	Set includes the following:
70490	.25	1/4, 5/16, 3/8 x 2.5"




70491 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 102mm OAL

Item No.	lbs.	Set includes the following:
70491	.39	1/4, 5/16, 3/8 x 4.0"




70492 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 152mm OAL

Item No.	lbs.	Set includes the following:
70492	.54	1/4, 5/16, 3/8 x 6.0"



70493 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 305mm OAL

Item No.	lbs.	Set includes the following:
70493	1.03	1/4, 5/16, 3/8 x 12.0"



74990 19 Pc. Quick Change Bit Belt Pack Set, Includes: 1/4" SlimFix bit holder and the following 1/4" bits and Nut Setters:

- ⓘ Slotted - Power: 4.5, 5.5, 6.5mm x 50mm
- ⊕ Phillips - Power: #1, #2, #3 x 50mm
- ⊖ Square - Power: #1, #2, #3 x 50mm
- ⊗ Torx® - Insert: T10, T15, T20, T25, T27, T30 x 25mm
- ⊙ Nut Setters-Power: 1/4, 5/16, 3/8" Magnetic

lbs. .93

Wiha TORX®, TORXPlus® & Security TORX® Bit Sockets



Set Screw
Replaceable
Bits

761 TORX® Sockets 1/4" Square Drive

Item	No.	Size	mm	lbs.
	76106	T6	38	.04
	76107	T7	38	.04
	76109	T8	38	.04
	76111	T9	38	.04
	76113	T10	38	.04
	76117	T15	38	.04
	76119	T20	38	.04
	76121	T25	38	.04
	76123	T27	38	.04
	76129	T30	38	.05
	76131	T40	38	.05



763 TORX® Sockets 3/8" Square drive, Set screw replaceable bit. 1/4" bits.

Item	No.	Size	mm	lbs.
	76312	T9	42	.09
	76314	T10	42	.09
	76316	T15	42	.09
	76318	T20	42	.09
	76322	T25	42	.09
	76324	T27	42	.09
	76326	T30	42	.09
	76328	T40	42	.09



763 TORX® Sockets 3/8" Square drive, Set screw replaceable bit. 5/16" bits. 2" OAL

Item	No.	Size	mm	lbs.
	76346	T40	51	.11
	76348	T45	51	.11
	76352	T50	51	.11
	76354	T55	51	.13



Set Screw
Replaceable
Bits

763 Security TORX® Sockets

3/8" Square drive, 5/16" bits.

Item	No.	Size	mm
	76339	T40s	51
	76340	T45s	51
	76341	T50s	51



Set Screw
Replaceable
Bits

763 Security TORX® Sockets

1/4" Square drive, 1/4" bits.

Item	No.	Size	mm
	76330	T8s	38
	76331	T9s	38
	76332	T10s	38
	76333	T15s	38
	76334	T20s	38
	76335	T25s	38
	76336	T27s	38
	76337	T30s	38
	76338	T40s	38



Set Screw
Replaceable
Bits

701 Security TORX® Sockets

3/8" Square drive, 1/4" bits. 2" OAL

Item	No.	Size	mm	lbs.
	70107	T7s	42	.09
	70108	T8s	42	.09
	70109	T9s	42	.09
	70110	T10s	42	.09
	70113	T15s	42	.09
	70115	T20s	42	.09
	70117	T25s	42	.09
	70119	T27s	42	.09
	70121	T30s	42	.09
	70123	T40s	42	.09



716 TORXPlus® Sockets 1/4" Square Drive, Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71661	IP6	38	.04
	71662	IP7	38	.04
	71663	IP8	38	.04
	71664	IP9	38	.04
	71665	IP10	38	.04
	71666	IP15	38	.04
	71667	IP20	38	.04
	71668	IP25	38	.04
	71669	IP27	38	.04
	71670	IP30	38	.04
	71671	IP40	38	.04



716 TORXPlus® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71673	IP9	42	.09
	71674	IP10	42	.09
	71675	IP15	42	.09
	71676	IP20	42	.09
	71677	IP25	42	.09
	71678	IP27	42	.09
	71680	IP30	42	.09
	71681	IP40	42	.09

1/2" Square Drive Sockets



Set Screw
Replaceable
Bits

764 Slotted Bit Sockets 1/2" Square Drive

Item	No.	mm	mm	lbs.	pkg.
	76417	8	59	.12	1
	76418	10	59	.12	1
	76419	12	59	.12	1

1/2" Square Drive Sockets



Set Screw
Replaceable
Bits

764 TORX® Sockets 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76403	T30	59	.10	1
	76404	T40	59	.10	1
	76405	T45	59	.10	1
	76406	T50	59	.10	1
	76407	T55	59	.11	1



Set Screw
Replaceable
Bits

764 Security TORX® Sockets

1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76411	T40s	59	.11	1
	76412	T45s	59	.11	1
	76413	T50s	59	.11	1
	76414	T55s	59	.12	1



Set Screw
Replaceable
Bits

764 Phillips Bit Sockets 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76422	2	59	.15	1
	76423	3	59	.15	1
	76424	4	59	.15	1

Hex Inch/Metric Bit Sockets



713 Hex Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	Inch	mm	lbs.
71371	1/16	38	.05
71370	5/64	38	.05
71372	3/32	38	.05
71374	7/64	38	.05
71376	1/8	38	.05
71378	9/64	38	.05
71380	5/32	38	.05
71382	3/16	38	.05
71384	7/32	38	.05
71386	1/4	38	.05



713 Hex Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM tool steel.

Item			
No.	Inch	mm	lbs.
71375	1/8	42	.09
71377	9/64	42	.09
71379	5/32	42	.09
71381	3/16	42	.09
71383	7/32	42	.09
71385	1/4	42	.09
71388	5/16	42	.10
71390	3/8	42	.10



713 Hex Metric Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	mm	mm	lbs.
71301	1.5	38	.04
71302	2.0	38	.04
71305	2.5	38	.04
71313	3.0	38	.04
71314	4.0	38	.04
71317	5.0	38	.05
71319	6.0	38	.05
71327	8.0	38	.05
71340	10.0	38	.05



713 Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	mm	mm	lbs.
71300	2.0	42	.09
71316	2.5	42	.09
71341	3.0	42	.09
71331	4.0	42	.09
71323	5.0	42	.09
71325	6.0	42	.09
71320	8.0	42	.10
71322	10.0	42	.11



713 Hex Metric Sockets 5/16" Square drive socket. Replaceable bit. 5/16" bits CVM steel.

Item			
No.	mm	mm	lbs.
71332	12.0	75	.22



761 Security Hex Inch Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	Inch	mm	lbs.
76164	5/64	42	.09
76165	3/32	42	.09
76166	7/64	42	.09
76167	1/8	42	.09
76168	9/64	42	.09
76169	5/32	42	.09
76170	3/16	42	.09
76171	7/32	42	.09
76172	1/4	42	.09



761 Security Hex Metric Sockets 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	mm	mm	lbs.
76132	2.0	42	.09
76133	2.5	42	.09
76134	3.0	42	.09
76135	4.0	42	.09
76136	5.0	42	.09
76137	6.0	42	.09
76138	8.0	42	.09

Wiha Ball End Hex Inch & Metric Bit Sockets



717 Ball End Hex Inch Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	Inch	mm	lbs.
71761	3/32	38	.05
71762	7/64	38	.05
71763	1/8	38	.05
71764	9/64	38	.05
71765	5/32	38	.05
71766	3/16	38	.05
71767	7/32	38	.05
71768	1/4	38	.05



717 Ball End Hex Metric Sockets 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item			
No.	mm	mm	lbs.
71771	1.5	51	.11
71772	2.0	51	.11
71773	2.5	51	.11
71774	3.0	51	.11
71775	4.0	51	.11
71776	5.0	51	.12
71777	6.0	51	.12

Socket Adapters



721 Hex To Square 1/4" socket bit adapter.

Item				
No.	Size	mm	Drive	lbs.
72110	1/4"	25	1/4"	.03
72115	1/4"	30	3/8"	.05



724 Tool Shaft 1/4" drive socket power adapter.

Item				
No.	Drive	mm	Drive	lbs.
72401	1/4"	100	1/4"	.09
72405	1/4"	50	1/4"	.03
72410	1/4"	100	3/8"	.17
72415	1/4"	50	3/8"	.06

Wiha Bit Holding Socket Replacements



72014 1/4" Drive Bit Holding Socket With Retaining Ring For 1/4" drive bits.

Item	Bit	mm	Drive	lbs.
72014	1/4"	25	1/4"	.04



72038 3/8" Drive Bit Holding Socket With Retaining Ring For 1/4" drive bits.

Item	Bit	mm	Drive	lbs.
72038	1/4"	25	3/8"	.08



72040 3/8" Drive Bit Holding Socket With Retaining Ring For 5/16" drive bits.

Item	Bit	mm	Drive	lbs.
72040	5/16"	25	3/8"	.08

Wiha Long Blade Sockets & Sets



771 Hex Inch Sockets

1/4" Drive 6" Long Bit Socket

Item	Bit	mm	Drive	lbs.
77128	3/32	6	.12	
77130	7/64	6	.12	
77132	1/8	6	.12	
77134	9/64	6	.12	
77136	5/32	6	.12	
77138	3/16	6	.12	
77139	7/32	6	.12	
77141	1/4	6	.12	

77191 8 Pc. Hex Inch Socket Blade Set

Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" wt. .97



771 Hex Inch Sockets

3/8" Drive 6" Long Bit Socket

Item	Bit	mm	Drive	lbs.
77165	3/32	6	.12	
77167	7/64	6	.12	
77169	1/8	6	.12	
77171	9/64	6	.12	
77173	5/32	6	.12	
77175	3/16	6	.12	
77177	7/32	6	.12	
77179	1/4	6	.12	



771 Hex Metric Sockets

3/8" Drive 6" Long Bit Socket

Item	Bit	mm	Drive	lbs.
77180	2.5	6	.12	
77182	3.0	6	.12	
77184	4.0	6	.12	
77186	5.0	6	.12	
77188	6.0	6	.12	

Impact Bit Holding Sockets



720 Impact Bit Holding Socket With Retaining Ring For 5/16" drive bits.

Item	Bit	mm	Drive	lbs.
72004	5/16"	25	1/4"	.04
72005	5/16"	30	3/8"	.04
72006	5/16"	35	1/2"	.04



Wiha Long Blade Sockets & Sets



771 Hex Metric Sockets

1/4" Drive 6" Long Bit Socket

Item	Bit	mm	Inch	lbs.
77140	2.5	6	.12	
77142	3.0	6	.12	
77144	4.0	6	.12	
77146	5.0	6	.12	
77148	6.0	6	.12	

77192 5 Pc. Hex Metric Socket Blade Set

Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm wt. .51



771 TORX Sockets

1/4" Drive 6" Long Bit Socket

Item	Bit	mm	Inch	lbs.
77151	T8	6	.12	
77153	T9	6	.12	
77152	T10	6	.12	
77154	T15	6	.12	
77156	T20	6	.12	
77158	T25	6	.12	
77160	T27	6	.12	
77162	T30	6	.12	
77164	T40	6	.12	

77193 7 Pc. TORX Socket Blade Set

TORX: T10, T15, T20, T25, T27, T30, T40 wt. .69



720 Impact Bit Holding Socket With Retaining Ring For 1/4" drive insert bits.

Item	Bit	mm	Drive	lbs.
72001	1/4"	25	1/4"	.05
72002	1/4"	30	3/8"	.10
72003	1/4"	35	1/2"	.21

72090 3 Piece Bit Holding Socket Set

for use with 1/4" insert bits

Drive: 1/4", 3/8", 1/2" lbs. .40



771 TORX Sockets

3/8" Drive 6" Long Bit Socket

Item	Bit	mm	Inch	lbs.
77101	T8	6	.12	
77103	T9	6	.12	
77105	T10	6	.12	
77107	T15	6	.12	
77109	T20	6	.12	
77111	T25	6	.12	
77113	T27	6	.12	
77115	T30	6	.12	
77117	T40	6	.12	

77195 9 Pc. TORX Socket Blade Set

TORX: T8, T9, T10, T15, T20, T25, T27, T30, T40 wt. 1.08



77198 22 Pc. Hex & TORX Long Blade Socket Set, 1/4" Drive

Inch Hex: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Metric Hex: 2.5, 3.0, 4.0, 5.0, 6.0mm

TORX: T8, T9, T10, T15, T20, T25, T27, T30, T40

lbs. 2.82

Wiha Universal Socket Rail System



91132 Universal Rail For 1/4, 3/8 and 1/2" Sockets Select any combination of socket drive sizes. Socket snaps firmly into place for a secure hold. Clips required.

Item			
No.	OAL	pkg.	lbs.
91132	8.0"	1	.06



91134 Universal Rail For 1/4, 3/8 and 1/2" Sockets Select any combination of socket drive sizes. Socket snaps firmly into place for a secure hold. Clips required.

Item			
No.	OAL	pkg.	lbs.
91134	14.0"	1	.08



91117 Replacement 1/4" Clips For The Universal Socket Rail Package of 10 pieces.

Item No.	lbs.
91117	.03



91121 Replacement 3/8" Clips For The Universal Socket Rail Package of 10 pieces.

Item No.	lbs.
91121	.03



91124 Replacement 1/2" Clips For The Universal Socket Rail Package of 10 pieces.

Item No.	lbs.
91124	.05


Wiha Socket Sets On Molded Rails



76194 6 pc. TORX® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
76194	.20	T10, T15, T20, T25, T27, T30



76490 6 pc. TORX® Socket Set

1/2" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
76490	1.06	T30, T40, T45, T50, T55, T60



76395 8 pc. TORX® Socket Set

3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel. OAL 1.5"

Item	lbs.	Set includes the following:
76395	.75	T9, T10, T15, T20, T25, T27, T30, T40



76396 8 pc. TORX® Socket Set

3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item	lbs.	Set includes the following:
76396	.84	1/4": T20, T25, T27, T30, T40, 5/16": T45, T50, T55



71698 8 pc. TORXPlus® Socket Set On Rail, In Vinyl Pouch 1/4" & 3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item	lbs.	Set includes the following:
71698	.60	1/4": IP9, IP10, IP15, IP20 3/8": IP25, IP27, IP30, IP40



76397 9 pc. Security TORX® Socket Set 1/4" & 3/8" Sq. Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item	lbs.	Set includes the following:
76397	.85	1/4": T10s, T15s, T20s, T25s, T27s, T30s 3/8": T40s (1/4" bit) 3/8": T45s, T50s (5/16" bit)



76198 9 pc. TORX® Socket Set

1/4" & 3/8" Sq. Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item	lbs.	Set includes the following:
76198	.81	1/4": T10, T15, T20, T25, T27, T30, T40, 5/16": T45, T50

- **Slotted**
- **Phillips**
- **Torx®**
- **Security Torx®**
- **Hex/Ball End/MagicRing**
- **Security Hex**
- **Nut Driver**
- **Pozidriv®**
- **Square**
- **Tri-Wing**
- **Spanner**
- **Torq Set**
- **TorxPlus®**
- **Security TorxPlus®**
- **Xeno Phillips**
- **Security Pentalobe 5Point**

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
28103	40	70430	49	71052	27	71348	21	71508	11	71658	17
28180	41	70437	49	71053	27	71349	23	71509	11	71660	17
28489	40	70438	49	71054	27	71351	21	71510	11	71661	50
28589	39	70440	49	71056	19	71352	23	71515	11	71662	50
28590	39	70442	49	71090	36	71353	21	71520	11	71663	50
28593	39	70445	49	71095	37	71354	23	71523	11	71664	50
28595	39	70448	49	71100	19	71356	21	71524	11	71665	50
38032	35	70450	49	71101	19	71359	21	71525	11	71666	50
38035	35	70462	49	71102	19	71360	21	71527	11	71667	50
38041	35	70463	49	71103	19	71361	21	71530	11	71668	50
38042	15	70464	49	71130	41	71362	21	71536	18	71669	50
38043	35	70466	49	71131	41	71363	21	71537	18	71670	50
38044	13	70468	49	71132	19	71364	21	71538	18	71671	50
38045	13	70469	49	71139	41	71365	21	71540	11	71673	50
38046	15	70470	49	71149	19	71366	21	71541	18	71674	50
38047	15	70472	49	71151	19	71367	21	71542	18	71675	50
38048	35	70474	49	71152	19	71368	21	71543	18	71676	50
38049	24	70476	49	71153	19	71369	21	71544	18	71677	50
38050	35	70477	49	71195	13	71370	51	71545	18	71678	50
38051	35	70479	49	71198	20	71371	51	71546	18	71680	50
38056	25	70480	48	71200	28	71372	51	71547	18	71681	50
38057	24	70481	48	71201	28	71373	21	71548	11	71690	16
38058	24	70482	48	71202	28	71374	51	71549	11	71692	16
38060	41	70483	48	71203	28	71375	51	71550	11	71698	53
38450	40	70484	48	71250	28	71376	51	71551	11	71701	22
38460	40	70485	48	71251	28	71377	51	71552	11	71702	22
38490	35	70486	48	71252	28	71378	51	71553	11	71703	22
38600	40	70490	49	71253	28	71379	51	71554	11	71704	22
38701	41	70491	49	71254	28	71380	51	71555	11	71705	22
38790	41	70492	49	71300	51	71381	51	71556	11	71706	22
38800	40	70493	49	71301	51	71382	51	71557	11	71707	22
38801	40	70494	49	71302	51	71383	51	71558	11	71708	22
52650	40	70507	14	71303	21	71384	51	71559	11	71711	22
70107	50	70508	14	71304	23	71385	51	71560	11	71712	22
70108	50	70509	14	71305	51	71386	51	71561	11	71713	22
70109	50	70510	14	71306	21	71387	21	71570	11	71714	22
70110	50	70515	14	71307	23	71388	51	71571	11	71715	22
70113	50	70520	14	71308	21	71389	54	71603	16	71716	22
70115	50	70525	14	71309	21	71390	51	71604	16	71717	22
70117	50	70527	14	71310	23	71392	54	71605	16	71718	22
70119	50	70530	14	71311	23	71393	54	71606	16	71719	22
70121	50	70533	14	71312	21	71394	54	71607	16	71720	22
70123	50	70534	14	71313	51	71396	21	71608	16	71721	22
70127	14	70535	14	71314	51	71397	21	71609	16	71722	22
70128	14	70536	14	71315	21	71398	54	71610	16	71723	22
70129	14	70537	14	71316	51	71431	41	71615	16	71724	22
70135	14	70538	14	71317	51	71433	41	71620	16	71725	22
70139	14	70539	14	71318	21	71435	41	71625	16	71726	23
70142	14	70540	14	71319	51	71437	41	71627	16	71728	23
70143	30	70545	14	71320	51	71439	41	71630	16	71730	23
70144	30	70550	14	71321	21	71441	41	71631	16	71732	23
70145	30	70556	14	71322	51	71452	30	71632	16	71734	23
70146	30	70557	14	71323	51	71453	30	71633	16	71736	23
70147	30	70558	14	71324	21	71455	30	71634	16	71738	23
70148	14	70559	14	71325	51	71456	30	71635	16	71740	23
70150	14	70560	14	71326	21	71474	40	71636	16	71750	23
70151	14	70561	14	71327	51	71475	40	71637	16	71760	23
70152	14	70562	14	71328	21	71476	40	71638	16	71761	51
70153	14	70563	14	71329	21	71477	40	71639	16	71762	51
70154	14	70564	14	71330	21	71478	40	71640	16	71763	51
70155	14	70565	14	71331	51	71479	40	71641	16	71764	51
70156	14	70566	14	71332	51	71480	30,41	71642	16	71765	51
70157	14	70567	14	71333	21	71491	41	71643	16	71766	51
70158	14	71001	26	71336	21	71492	40	71644	16	71767	51
70159	14	71002	26	71339	21	71493	40	71645	16	71768	51
70160	14	71003	26	71340	51	71494	41	71648	17	71771	51
70163	14	71004	26	71341	51	71496	40	71650	17	71772	51
70168	14	71031	26	71342	21	71499	41	71652	17	71773	51
70190	15	71032	26	71343	23	71505	11	71654	17	71774	51
70424	49	71035	26	71345	21	71506	11	71656	17	71775	51
70427	49	71051	27	71346	23	71507	11	71657	17	71776	51

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
71777	51	71981	23	72536	26	73512	8	73943	12	74301	23
71797	54	71982	23	72537	26	73513	8	73944	12	74305	23
71798	54	71983	23	72538	26	73514	8	73945	12	74307	23
71801	26	71984	23	72539	26	73515	8	73946	12	74311	22
71802	26	71985	23	72540	11	73516	8	74003	27	74312	22
71803	26	71987	39	72542	14	73517	8	74006	27	74313	22
71851	26	71988	37	72545	11	73518	8	74009	27	74314	22
71852	26	71989	54	72547	14	73519	8	74010	27	74315	22
71853	26	71990	37	72550	11	73520	8	74012	27	74316	22
71854	26	71991	37	72551	11	73521	8	74015	27	74317	22
71900	29	71994	37	72555	11	73522	8	74018	27	74318	22
71901	29	71995	24	72558	14	73523	8	74021	27	74319	23
71902	29	71996	54	72559	14	73524	8	74023	27	74325	22
71903	29	71998	24	72560	14	73525	8	74033	27	74330	22
71904	29	71999	54	72561	14	73526	8	74034	27	74332	22
71906	29	72001	52	72562	14	73527	8	74035	27	74333	22
71907	29	72002	52	72563	14	73528	8	74036	27	74334	22
71908	29	72003	52	72564	14	73529	8	74039	27	74335	22
71909	29	72004	52	72567	14	73530	8	74041	27	74336	22
71910	29	72005	52	72568	14	73531	8	74050	27	74337	22
71911	29	72006	52	72569	11	73532	8	74061	27	74340	22
71912	29	72014	52	72570	11	73533	8	74062	27	74343	22
71913	29	72031	27	72572	11	73534	8	74063	27	74344	22
71914	30	72038	52	72573	11	73535	8	74064	27	74345	22
71916	30	72039	27	72574	11	73536	8	74065	27	74346	22
71918	30	72040	52	72575	11	73537	8	74066	27	74348	22
71920	30	72047	27	72576	11	73538	8	74067	27	74349	22
71921	29	72049	27	72577	11	73539	8	74068	27	74350	22
71922	29	72050	27	72578	11	73540	8	74069	27	74351	22
71923	29	72051	27	72579	11	73541	8	74102	20	74352	22
71924	29	72090	52	72580	11	73542	8	74103	20	74353	22
71930	23	72102	19	72581	11	73543	8	74104	20	74354	22
71932	23	72103	19	72582	21	73544	8	74106	20	74355	22
71934	23	72104	19	72583	21	73545	8	74107	20	74356	22
71936	23	72110	51	72584	21	73546	8	74109	20	74357	22
71938	23	72115	51	72585	21	73547	8	74111	20	74360	22
71939	23	72304	10	72586	21	73548	8	74112	20	74361	22
71940	23	72328	10	72587	21	73901	28	74113	20	74362	22
71941	23	72343	10	72590	13	73902	28	74115	20	74363	22
71942	23	72347	10	72593	35	73903	28	74116	20	74364	22
71943	23	72351	10	72595	13	73905	27	74118	20	74365	22
71944	23	72354	10	72596	24	73906	27	74121	20	74366	22
71945	23	72378	10	73302	21	73907	27	74123	20	74369	23
71946	23	72388	21	73303	21	73908	27	74124	20	74371	23
71949	29	72391	10	73304	21	73909	27	74126	20	74373	23
71950	29	72401	51	73305	21	73910	27	74127	20	74375	23
71951	29	72405	51	73306	21	73912	20	74130	20	74379	23
71952	29	72410	51	73307	21	73913	20	74131	20	74380	22
71953	29	72415	51	73308	21	73914	20	74133	20	74381	22
71954	29	72502	21	73309	21	73915	20	74136	20	74382	22
71955	23	72503	21	73310	18	73916	20	74150	20	74383	22
71956	23	72504	21	73311	18	73920	22	74157	20	74384	22
71957	29	72506	21	73312	18	73921	22	74158	20	74385	22
71958	29	72507	21	73313	18	73922	22	74164	20	74386	22
71959	29	72508	21	73314	18	73923	22	74165	20	74387	22
71960	23	72509	21	73315	18	73925	22	74166	20	74388	22
71963	30	72511	21	73316	18	73926	22	74167	20	74413	12
71964	30	72512	21	73317	18	73928	22	74168	20	74415	12
71965	30	72513	21	73318	18	73929	22	74201	28	74461	12
71966	30	72514	14	73319	18	73930	22	74203	28	74462	12
71970	23	72515	14	73501	8	73931	22	74205	28	74501	12
71971	23	72516	14	73502	8	73932	22	74212	28	74502	12
71972	23	72519	19	73503	8	73933	22	74214	28	74503	12
71973	23	72521	19	73504	8	73934	22	74221	28	74504	12
71974	23	72522	19	73505	8	73936	12	74231	28	74506	12
71975	23	72523	19	73506	8	73937	12	74232	28	74508	12
71976	23	72525	11	73507	8	73938	12	74233	28	74510	12
71977	23	72527	11	73508	8	73939	12	74236	28	74511	12
71978	23	72530	11	73509	8	73940	12	74237	28	74512	12
71979	23	72534	26	73510	8	73941	12	74238	28	74513	12
71980	23	72535	26	73511	8	73942	12	74262	28	74514	12

58 Tools that work for you

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
74515 12	74590 12	74982 16	75634 43	75823 42	76046 25
74516 12	74591 12	74983 39	75635 43	75824 42	76047 25
74517 12	74601 16	74985 13	75636 43	75825 42	76048 25
74518 12	74602 16	74986 24	75637 43	75826 42	76049 25
74519 12	74603 16	74987 15	75644 43	75827 42	76050 25
74520 17	74604 16	74988 39	75645 43	75900 44	76051 25
74521 12	74608 16	74990 49	75646 43	75901 44	76052 25
74522 17	74611 16	74992 36	75647 43	75902 44	76053 25
74523 12	74612 16	74996 36	75648 43	75965 46	76054 25
74524 17	74613 16	74999 25	75649 43	75968 46	76056 25
74525 12	74614 16	75008 42	75650 43	75971 46	76057 25
74526 17	74616 16	75012 42	75651 43	75977 46	76058 25
74527 12	74617 16	75015 42	75652 43	75978 43	76059 48
74528 17	74620 16	75018 42	75653 43	75980 46	76060 48
74529 12	74624 16	75020 42	75654 43	75981 47	76061 48
74530 12	74628 16	75025 42	75655 43	75982 44	76062 48
74531 12	74632 16	75030 42	75656 43	75983 47	76063 48
74532 17	74636 16	75035 42	75657 43	75984 44	76064 48
74533 12	74659 16	75040 42	75658 43	75985 47	76065 48
74534 17	74660 16	75093 46	75659 43	75986 44	76066 48
74535 12	74661 16	75094 47	75660 43	75987 44	76067 48
74536 12	74662 16	75095 47	75661 43	75988 44	76068 48
74537 17	74663 16	75096 47	75662 43	75991 45	76069 48
74538 12	74664 16	75097 47	75663 43	75992 45	76070 48
74539 17	74665 16	75105 42	75664 43	75993 46	76071 48
74540 12	74666 16	75110 42	75665 43	75994 45	76072 48
74541 17	74667 16	75115 42	75666 43	75995 45	76073 48
74542 12	74668 16	75120 42	75667 43	75996 45	76074 48
74543 17	74669 16	75125 42	75668 43	75999 45	76075 48
74544 12	74670 16	75307 42	75669 43	76000 15,20,25,31,48	76076 48
74545 17	74711 18	75309 42	75670 43	76001 25	76077 48
74546 12	74714 18	75313 42	75671 43	76002 25	76078 48
74547 17	74717 18	75315 42	75672 43	76003 25	76079 31
74548 12	74721 18	75320 42	75673 43	76004 25	76080 48
74549 17	74724 18	75325 42	75674 43	76005 25	76084 31,48
74550 17	74728 18	75330 42	75675 43	76006 25	76085 31,48
74551 12	74732 18	75340 42	75676 43	76007 25	76086 31,48
74552 17	74736 18	75350 42	75701 42	76008 15	76087 31
74553 12	74739 18	75352 42	75702 42	76009 15	76088 29
74554 17	74742 18	75354 42	75703 42	76010 15	76089 30
74555 17	74760 18	75356 42	75704 42	76011 28	76090 25
74556 12	74761 18	75358 42	75705 42	76012 28	76091 28
74557 17	74762 18	75360 42	75706 42	76013 28	76092 15
74558 12	74763 18	75395 45	75707 42	76014 25	76093 27
74559 12	74764 18	75602 43	75708 42	76015 15	76094 20
74561 12	74765 18	75603 43	75709 42	76016 25	76095 25
74563 12	74766 18	75604 43	75710 42	76017 25	76096 25
74564 17	74767 18	75605 43	75715 42	76018 25	76098 31
74565 12	74768 18	75606 43	75720 42	76019 25	76099 31
74566 14	74811 26	75607 43	75743 42	76020 15	76106 50
74567 12	74812 26	75608 43	75744 42	76021 25	76107 50
74568 14	74813 26	75609 43	75745 42	76022 30	76109 50
74569 12	74814 26	75610 43	75746 42	76023 30	76111 50
74570 14	74816 26	75611 43	75747 42	76024 30	76113 50
74571 12	74819 26	75612 43	75748 42	76025 15	76117 50
74572 14	74860 26	75613 43	75800 42	76027 15	76119 50
74573 12	74861 26	75614 43	75801 42	76030 15	76121 50
74574 14	74862 26	75615 43	75802 44	76031 29	76123 50
74575 12	74890 26	75616 43	75803 44	76032 29	76129 50
74576 14	74895 26	75617 43	75805 47	76033 29	76131 50
74577 12	74911 29	75618 43	75806 44	76034 29	76132 51
74579 12	74912 29	75619 43	75810 42	76035 27	76133 51
74580 12	74913 29	75620 43	75811 42	76036 27	76134 51
74581 12	74914 29	75621 43	75812 42	76037 27	76135 51
74582 12	74915 29	75622 43	75813 42	76038 27	76136 51
74583 12	74961 29	75623 43	75814 42	76039 27	76137 51
74584 12	74964 29	75628 43	75815 42	76040 15	76138 51
74585 12	74965 29	75629 43	75816 42	76041 20	76164 51
74586 12	74966 29	75630 43	75817 42	76042 20	76165 51
74587 12	74967 29	75631 43	75820 42	76043 20	76166 51
74588 12	74968 29	75632 43	75821 42	76044 20	76167 51
74589 12	74981 18	75633 43	75822 42	76045 25	76168 51

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
76169	51	76523	5	76595	9	76825	5	77136	52	77791	32
76170	51	76524	5	76596	9	76826	5	77138	52	77792	32
76171	51	76525	5	76597	9	76830	5	77139	52	77793	33
76172	51	76526	5	76598	9	76831	5	77140	52	77795	33
76194	53	76527	9	76599	9	76832	5	77141	52	78002	30
76198	53	76528	9	76601	7	76833	5	77142	52	78005	30
76312	50	76529	9	76602	7	76834	5	77144	52	78008	30
76314	50	76530	5	76603	7	76835	5	77146	52	78011	30
76316	50	76531	5	76606	7	76838	4	77148	52	78015	30
76318	50	76532	5	76607	7	76839	4	77151	52	78018	30
76322	50	76533	5	76608	7	76840	4	77152	52	78615	30
76324	50	76534	5	76610	7	76841	10	77153	52	78617	30
76326	50	76535	5	76611	7	76842	10	77154	52	78619	30
76328	50	76536	9	76612	7	76843	6	77156	52	78621	30
76330	50	76537	9	76613	7	76844	6	77158	52	78622	30
76331	50	76538	4	76614	7	76845	6	77160	52	78624	30
76332	50	76539	4	76616	7	76846	10	77162	52	79242	13
76333	50	76540	4	76617	7	76847	10	77164	52	79243	36
76334	50	76541	9	76623	7	76848	6	77165	52	79245	13
76335	50	76542	9	76624	7	76849	6	77167	52	79246	24
76336	50	76543	6	76625	7	76850	6	77169	52	79247	15
76337	50	76544	6	76626	7	76851	10	77171	52	79248	36
76338	50	76545	6	76630	7	76852	10	77173	52	79256	24
76339	50	76546	9	76631	7	76853	6	77175	52	79266	24
76340	50	76547	9	76632	7	76854	6	77177	52	79276	25
76341	50	76548	6	76633	7	76855	6	77179	52	79283	18
76346	50	76549	6	76634	7	76856	6	77180	52	79443	38
76348	50	76550	6	76635	7	76857	6	77182	52	79445	13
76352	50	76551	9	76638	7	76858	6	77184	52	79446	24
76354	50	76552	9	76639	7	76859	6	77186	52	79447	15
76395	53	76553	6	76640	7	76860	10	77188	52	79450	17
76396	53	76554	6	76641	7	76861	10	77191	52	79490	38
76397	53	76555	6	76642	7	76863	6	77192	52	79491	38
76403	50	76556	6	76643	7	76864	6	77193	52	79493	38
76404	50	76557	6	76644	7	76865	6	77195	52	79495	38
76405	50	76558	6	76645	7	76866	6	77198	52	79499	38
76406	50	76559	6	76646	7	76870	6	77701	11	91109	46
76407	50	76560	9	76647	7	76871	6	77702	11	91117	53
76411	50	76561	9	76648	7	76872	6	77703	11	91121	53
76412	50	76562	9	76649	7	76873	6	77704	11	91124	53
76413	50	76563	6	76650	7	76874	6	77705	11	91132	53
76414	50	76564	6	76651	7	76875	6	77707	19	91134	53
76417	50	76565	6	76652	7	76876	5	77708	19	91473	4,38
76418	50	76566	6	76653	7	76877	5	77710	28	97780	34
76419	50	76567	9	76654	7	76878	6	77712	26	97781	34
76422	50	76568	9	76655	7	76879	6	77713	26	97782	34
76423	50	76569	9	76656	7	76880	6	77715	26	97790	34
76424	50	76570	6	76663	7	76881	5	77716	26	97791	34
76490	53	76571	6	76664	7	76886	4	77717	26	97792	34
76500	9	76572	6	76665	7	76889	36	77719	21		
76501	4	76573	6	76666	7	76890	5	77720	21		
76502	4	76574	6	76670	7	76891	5	77721	21		
76503	4	76575	6	76671	7	76892	6	77723	21		
76504	9	76576	9	76672	7	76893	5	77724	21		
76505	9	76577	9	76673	7	76894	6	77725	21		
76506	4	76578	6	76674	7	76895	5	77726	21		
76507	4	76579	6	76675	7	76896	6	77740	32		
76508	4	76580	6	76801	4	76897	5	77741	32		
76509	9	76581	9	76802	4	76899	5	77780	32		
76510	4	76582	9	76803	4	77101	52	77781	32		
76511	4	76583	9	76806	4	77103	52	77782	32		
76512	4	76584	9	76807	4	77105	52	77783	33		
76513	4	76585	9	76808	4	77107	52	77784	33		
76514	4	76586	9	76810	4	77109	52	77785	33		
76515	9	76587	9	76811	4	77111	52	77786	33		
76516	4	76588	9	76812	4	77113	52	77789	33		
76517	4	76589	9	76813	4	77115	52	77790	32		
76518	9	76590	9	76814	4	77117	52				
76519	9	76591	9	76816	4	77128	52				
76520	9	76592	9	76817	4	77130	52				
76521	9	76593	9	76823	5	77132	52				
76522	9	76594	9	76824	5	77134	52				



Prop65 WARNING: This product can expose you to chemicals including Diisononyl Phthalate, Vinyl Chloride, Ethylene Glycol, Nickel or Hexavalent Chromium Six, which is known to the State of California to cause cancer or reproductive harm. For more information, go to www.P65Warnings.ca.gov.

MANUFACTURING
EXCELLENCE
AWARD
BESTES KMU
2014

WIHA – WINNER OF THE
MX AWARD 2014.
GERMANY'S BEST SME.

wiha 
Tools that work for you

PROFESSIONAL QUALITY BITS



(800) 494-6104
fax: (800) 494-7456
cservice@wihatools.com
www.wihatools.com

Catalog Item No. 99951
version - 7/1/20

**Subject to change
without notice**

©2020 Willi Hahn Corporation

®Torx is a registered trademark of
Acument Intellectual Properties LLC.



Wiha Quality Tools

1348 Dundas Circle
Monticello, MN 55362
tel: 763.295.6591
fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
Brampton, ONT L6T 4X4
tel: 866.494.0096 or 763.295.6591
fax: 763.295.6598

Like Us On
facebook 

To:




99007 Merchandise Catalog




99977 Pliers/Crimpers Catalog




99004 Automotive Catalog




99919 Insulated Catalog



99945 ESD Catalog



99001 TorqueControl Catalog



99002 Screwdrivers Catalog



99014 TORX Catalog



99934 Hex Tools Catalog