

FEATURES

- Designed for push/pull applications rather than clamping
- Shatterproof thermoplastic
- High tensile strength
- Brass female inserts or zinc-plated steel male studs
- Space between head and shank for operation even when wearing gloves

RS PRO Black Knurled Clamping Knob, M5

RS Stock No.: 448-8836



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Knobs are used in a wide variety of applications in our day-to-day lives and perform many functions, from being used as fixed handles to being used to tighten, loosen, adjust, clamp and push other components or pieces of equipment. They are used in various applications, from industrial and construction machinery to audio and visual equipment.

Female knobs: M4 (RS [4488820](#)), M5 (RS [4488836](#)), M6 (RS [4488858](#)), M8 (RS [4488864](#)), M10 (RS [4488870](#)).

Male knobs: M5 (RS [4488886](#)), M6 (RS [4488892](#)), M8 (RS [4488915](#)), M10 (RS [4488921](#)).

General Specifications

Thread	M5
Knob Shape	Knurled
Mounting Type	Threaded Hole
Body Material	Polymer
Insert Material	Brass
Colour	Black
Application	Fabrication/industrial machinery, Storage and general furniture, Drawers and other moving part

Mechanical Specifications

Thread Diameter	5mm
Thread Length	10mm
Knob Diameter	21mm
Hole Diameter	12.5mm
Hole Length	10.5mm

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------



Dimensions (mm):

L	l	l ₂	D	d	h	d ₁
18	n/a	10.5	21	M5	10	12.5

