


БАТАРЕЙНЫЕ ОТСЕКИ



BH142B For four «D» Cells (with «TS» contact)



HOUSING : BLACK POLYPROPYLENE
FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959
TEMPERATURE RANGE: -10°C to +100°C
RIVETS: BRASS, NICKEL PLATED.
SPRING: SPRING STEEL, NICKEL PLATED.
CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER
EIA-540J000
ROHS 2 COMPLIANT