HellermannTyton

Specification Sheet

Part Number: 151-03123



One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

Stainless-steel mounting plate tolerates high torque and provides superior corrosion resistance against chemicals, salt spray and contact with dissimilar metals.

Ratchet P-Clamp, 2.48 - 3.15" Bundle Dia, 180° Short, 0.41" Hole Dia, PA66HIRHSUV/SS304, Black, 90/ctn

Article Number	151-03123
Туре	RCF180SM10SS
Color	Black (BK)
Quantity Per	carton
Product Description	The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws.

Short Description	Ratchet P-Clamp, 2.48 - 3.15" Bundle Dia, 180° Short, 0.41" Hole Dia, PA66HIRHSUV/SS304, Black,90/ctn
Global Part Name	RCF180SM10SS-PA66HIRHSUV/SS304-BK
Minimum Tensile Strength (Imperial)	100.0
Minimum Tensile Strength (Metric)	445.0
Length L (Imperial)	9.57
Length L (Metric)	243.0
Fixation Method	Screw Mounting
Variant	Short
Width W (Imperial)	1.37
Width W (Metric)	34.9
Bundle Diameter Min (Imperial)	2.48
Bundle Diameter Min (Metric)	63.0
Bundle Diameter Max (Imperial)	3.15
Bundle Diameter Max (Metric)	80.0
Cable Tie Width Max (Imperial)	0.52

Cable Tie Width Max (Metric)	13.2
Mounting Hole Diameter D (Imperial)	0.405
Mounting Hole Diameter D (Metric)	10.29 mm
Stud Diameter (Metric)	M10
Mounting Hole Centers (Imperial)	3.46
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Stainless Steel (SS304)
Material Shortcut	SS304 PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

90

Package Quantity (Imperial)

90

© 2021 HellermannTyton. All Rights Reserved. Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions