


## Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
20	47	14	13,5	6,55	0,28	32000	17000	0,11	6204-2Z *



### Calculation factors

$k_r$  0,025

$f_0$  13