



SPECIFICATIONS

Technical Functions/ Features	UT15B
Voltage LED Steps (AC/D)	12V: between 0 to 12V LED will illuminate 24V: between 19V \pm 2V LED will illuminate 50V: between 48V \pm 6V LED will illuminate 120V: between 110V \pm 20V LED will illuminate 230V: between 200V \pm 20V LED will illuminate 400V: between 340V \pm 30V LED will illuminate 690V: between 520V \pm 30V LED will illuminate
Continuity Test	Range 0 to 100k Ω . The continuity LED will illuminate and buzzer will sound.
Phase Rotation Test	50Hz to 60Hz
Range Selection	Automatic
Polarity Detection	Positive & Negative
Low Battery Display	Short circuit two leads, LED and beeper do not on that means the battery is low
Torch	✓
Single Lead (L2) Voltage Detection	It is intended only as a quick check. 100V to 690V; 50Hz to 400Hz
Short Circuit Detection	✓

GENERAL CHARACTERISTICS

Power	1.5V Battery (AAA) x 2
Product Color	Red and Grey
Product Net Weight	210g
Product Size	275 x 51 x 30mm
Standard Accessories	Batteries, English Manual
Standard Individual Packing	Blister
Standard Quantity Per Carton	30pcs
Standard Carton Measurement	440 x 395 x 455mm (0.079CBM Per Standard Carton)
Standard Carton Gross Weight	17kg