



## SPECIFICATIONS

| Technical Functions/ Features      | UT15C   |
|------------------------------------|---|
| Voltage LED Steps (AC/D)           | 12V: between 0 to 12V LED will illuminate<br>24V: between 19V ± 2V LED will illuminate<br>50V: between 48V ± 6V LED will illuminate<br>120V: between 110V ± 20V LED will illuminate<br>230V: between 200V ± 20V LED will illuminate<br>400V: between 340V ± 30V LED will illuminate<br>690V: between 520V ± 30V LED will illuminate |
| Continuity Test                    | Range 0 to 100kΩ. The continuity LED will illuminate and buzzer will sound.   |
| Phase Rotation Test                | 50Hz to 60Hz  |
| Range Selection                    | Automatic   |
| Polarity Detection                 | Positive & Negative   |
| Low Battery Display                | Short circuit two leads, LED and beeper do not on that means the battery is low   |
| Torch                              | ✓   |
| Single Lead (L2) Voltage Detection | It is intended only as a quick check. 100V to 690V;<br>50Hz to 400Hz  |
| Short Circuit Detection            | ✓   |
| LCD display (AC/DC)                | 24V to 690V: ±(3%+5)  |

## GENERAL CHARACTERISTICS

|                              |  |
|------------------------------|--|
| Power                        | 1.5V Battery (AAA) x 2                           |
| LCD Size                     | UT15C - 23 x 12mm                                |
| Product Color                | Red and Grey                                     |
| Product Net Weight           | 210g   |
| Product Size                 | 275 x 51 x 30mm                                  |
| Standard Accessories         | Batteries, English Manual                        |
| Standard Individual Packing  | Blister  |
| Standard Quantity Per Carton | 30pcs  |
| Standard Carton Measurement  | 440 x 395 x 455mm (0.079CBM Per Standard Carton) |
| Standard Carton Gross Weight | 17kg   |

