



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/400V/1000V	± (0.8%+1)
AC Voltage	4V/40V/400V/750V 400μA/4000μA/40mA/400mA/4A/10A	± (1%+5)
DC Current	400μA/4000μA/40mA/400mA/4A/10A	± (1%+2)
AC Current	400μA/4000μA/40mA/400mA/4A/10A	± (1.2%+2)
Resistance	400Ω/4kΩ/40kΩ/400kΩ/4MΩ/40MΩ□	± (1%+2)
Capacitance	40nF/400nF/4uF/40uF/100uF	± (3%+5)
Frequency	10Hz-10MHz	± (0.1%+3)
Special Functions		
Low Impedance Selection		✓
Fused 10A Range		✓
mA Fuse		Resettable
Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
Relative Mode		✓
Data Hold		
Full Icon Display		✓
Sleep Mode		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	Around 10MΩ	✓
Max. Display	3999	✓

GENERAL CHARACTERISTICS

Power	9V Battery (6F22)
LCD Size	60 x 54mm
Product Colour	Red And Grey
Product Net Weight	340g

Product Size	179x88x39mm
Standard Accessories	Test lead, Batteries, English Manual, Holster
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40pcs
Standard Carton Measurement	598 x 418 x 340mm (0.085 CBM Per Standard Carton)
Standard Carton Gross Weight	23 kg