



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/400V/600V	± (0.8%+1)
AC Voltage	4V/40V/400V/600V	± (1%+5)
DC Current	40A/400A	± (2%+3)
AC Current	40A/400A	± (2.5%+5)
Resistance	400Ω/4kΩ/40kΩ/400kΩ/4MΩ/40MΩ	± (1%+2)
Frequency	10Hz~1MHz	± (0.1%+3)
Duty Cycle	0.1%~99.9%	✓
Special Functions		
Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
Data Hold		✓
Full Icon Display		✓
Sleep Mode		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	Around 10MΩ	✓
Max. Display	3999	✓

GENERAL CHARACTERISTICS

Power	9V Battery (6F22)
LCD Size	35.6 x 18 mm
Product Colour	Red and Grey
Product Net Weight	200g
Product Size	210 x 75.6 x 30mm
Standard Accessories	Test Lead, English Manual, Carrying Bag
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40 pcs
Standard Carton Measurement	510 x 490 x 330mm (0.082 CBM Per Standard Carton)
Standard Carton Gross Weight	15kg