



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	6.6V/66V/600V	± (0.8%+1)
AC Voltage	6.6V/66V/600V	± (1.2%+5)
DC Current	66A/1000A	± (1.5%+8)
AC Current	66A/1000A	± (2%+8)
Resistance	660Ω/6.6kΩ/66kΩ/660kΩ/ 6.6MΩ/66MΩ	± (1%+2)
Temperature	-40°C~1000°C -40°F~1832°F	
Frequency	660Hz/6.6kHz/66kHz/660kHz/ 6.6MHz/66MHz	± (0.1%+3)
Special Functions		
Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
True RMS	AC Voltage	✓
Surge Current	AC Current	✓
Max/Min Mode		✓
Data Hold		✓
Sleep Mode		✓
Display Backlight		✓
Full Icon Display		✓
Low Battery Display		✓
Input Impedance for AC Voltage Measurement	Around 10MΩ	✓
Max. Display	5999	✓

GENERAL CHARACTERISTICS

Power	9V Alkaline Battery (1604A)
LCD Size	47 x 30 mm
Product Color	Red and Grey
Product Net Weight	533g
Product Size	285 x 105 x 45 mm
Standard Accessories	UT207 - Test Lead, Alkaline Battery, English Manual, Carrying Bag
Standard Individual Packing	Gift Box
Standard Carton Gross Weight	24 pcs
Standard Carton Gross Weight	610 x 360 x 305 mm (0.067 CBM Per Standard Carton)
Standard Carton Gross Weight	25kg