



## SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage	400mV/4V/40V/400V/600V	± (0.8%+1)
AC Voltage	400mV/4V/40V/400V/600V	± (1.2%+5)
DC Current	40A/1000A	± (1.5%+8)
AC Current	40A/1000A	± (2%+8)
Resistance	400Ω / 4kΩ / 40kΩ / 400kΩ / 4MΩ / 40MΩ	± (1%+2)
Temperature	-40°C~1000°C -40°F~1832°F	
Frequency	4kHz/40kHz/400kHz/4MHz/40MHz	± (1%+3)
Duty Cycle	0.1%~99.9%	
<b>Special Functions</b>		
Auto Ranging		✓
Diode		✓
Continuity Buzzer		✓
True RMS	<b>AC Voltage</b>	✓
Surge Current	AC Current	✓
Peak Max/Peak Min Mode		✓
Max/Min Mode		✓
Data Hold		✓
Sleep Mode		✓
Display Backlight		✓
Full Icon Display		✓
Low Battery Display		✓
Input Impedance for AC Voltage Measurement	Around 10 MΩ	✓
Max. Display		4000
Analogue Bar Graph		✓

## GENERAL CHARACTERISTICS

<b>Power</b>	9V Alkaline Battery (1604A or 6LF22)
<b>LCD Size</b>	47 x 30 mm
<b>Product Color</b>	Red and Grey
<b>Product Net Weight</b>	533g
<b>Product Size</b>	285 x 105 x 45 mm
<b>Standard Accessories</b>	Test Lead, Alkaline Battery, English Manual, Tool Box
<b>Standard Individual Packing</b>	Gift Box
<b>Standard Quantity Per Carton</b>	5 pcs
<b>Standard Carton Measurement</b>	480 x 372 x 315 (0.056CBM Per Standard Carton)
<b>Standard Carton Gross Weight</b>	11 kg