



## SPECIFICATIONS

Basic Functions	UT321
Temperature (K-Type) -200.0°C to +1372°C -328.0°F to +2501°F	✓
Temperature (J-Type) -210.0°C to +1200°C -346.0°F to +2192°F	✓
Temperature (T-Type) -250.0°C to +400.0°C -418.0°F to +752.0°F	✓
Temperature (E-Type) -150.0°C to +1000°C -238.0°F to +1832°F	✓
Temperature Best Accuracy	K,J,T,E-Type : 0.5% ± 0.8°C
Display Resolution	0.1°C (when > 999.9°C : 1°C)
T1 input	✓
°C/°F/K Selection	✓
Data Logging	100
USB Data Transfer	✓
User Setup	✓
Temperature Data Hold	✓
Electricity Cut Off Memory	✓
MAX / MIN/ AVG temperatures	✓
Sleep Mode	✓
Low Battery Display	✓

## GENERAL CHARACTERISTICS

<b>Power</b>	USB (Auto Double White Display Backlight) or 9V Battery (6F22)
<b>LCD Size</b>	30x32mm
<b>Product Color</b>	Red and Grey
<b>Product Net Weight</b>	270g
<b>Product Size</b>	175x85x30mm
<b>Standard Accessories</b>	Battery, English Manual, USB Cable, CD Software, K Type Temperature Probe
<b>Standard Individual Packing</b>	Gift Box
<b>Standard Quantity Per Carton</b>	40 pcs
<b>Standard Carton Measurement</b>	460x390x270mm (0.048 CBM Per Standard Carton)
<b>Standard Carton Gross Weight</b>	21kg