



SPECIFICATIONS

Basic Functions	UT325
Temperature -200.0°C to +1372°C (K-Type) -328.0°F to +2501°F	✓
Temperature -210.0°C to +1200°C (J-Type) -346.0°F to +2192°F	✓
Temperature -250.0°C to +400.0°C (T-Type) -418.0°F to +752.0°F	✓
Temperature -150.0°C to +1000°C (E-Type) -238.0°F to +1832°F	✓
Temperature 0.0°C to +1767°C (R-Type) +32°F to +3212°F	✓
Temperature 0°C to +1767°C (S-Type) +32°F to +3212°F	✓
Temperature -200°C~+1300°C (N-Type) -328.0°F to +2372°F	✓
Temperature Best Accuracy	K,J,T,E-Type: 0.2% ± 0.6°C R,S Type: 0.2% ± 2°C N-Type: 0.2% ± 1.5°C
Display Resolution	0.1°C(When > 999.9°C : 1°C)
T1, T2 input	✓
°C/°F/K Selection	✓
High/Low Alarm	✓
High/Low Signal Output	✓
User Self-Calibration	✓
Data Logging	100
USB Data Transfer	✓

User Setup	✓
Temperature Data Hold	✓
Electricity Cut Off Memory	✓
MAX / MIN/ AVG temperatures	✓
Sleep Mode	✓
Low Battery Display	✓

GENERAL CHARACTERISTICS

Power	USB (Auto Double White Display Backlight) or 9V Battery (6F22)
LCD Size	30x32mm
Product Color	Red and Grey
Product Net Weight	270g
Product Size	175x85x30mm
Standard Accessories	Battery, English Manual, USB Cable, CD Software, K Type Temperature Probe
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40 pcs
Standard Carton Measurement	460x390x270mm (0.048 CBM Per Standard Carton)
Standard Carton Gross Weight	21kg