



SPECIFICATIONS

Technical Specifications	UT371
Measurement	10 to 99,999 RPM
Range Selection	10 to 99 RPM, 100 to 999 RPM, 1000 to 9999 RPM, 10000 to 99999 RPM
Best Accuracy	0.04% ± 2dgt
Display	99999 counts
Target Distance	50mm to 200mm
Start/Hold	Start and Stop Measurement, Data Hold
MAX/MIN/AVE/ZERO	Maximum Value, Minimum Value, Average Value, Zeroing
Sleep Mode	Around 15 minutes
Low Battery Display	4.8V

GENERAL CHARACTERISTICS

Power	1.5V Battery (AA) x 4
LCD Size	53 x 41mm
Product Color	Red and Grey
Product Net Weight	100g
Product Size	184 x 56 x 34mm
Standard Accessories	Batteries, English Manual, Reflecting Tape
Standard Individual Packing	Blister
Standard Quantity Per Carton	20pcs
Standard Carton Measurement	420 x 305 x 370mm (0.047 CBM Per Standard Carton)
Standard Carton Gross Weight	5 kg