

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| | A | REDRAWN PER ECO-18-009925 | 25JUN2018 | RS | DR |



- △ 1 STAMP AMP 16-14* APPROX AS SHOWN
- △ 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- △ 3 MATERIAL:
COPPER PER ASTM B152
- △ 4 FINISH:
GOLD 0.001270[.000050] MIN THK PER
ASTM B488 TYPE 1, CODE C
OVER NICKEL PLATE 0.000762[.000030] MIN
THK PER SAE AMS QQ-N-290

| | | |
|-----|--------------|-------------|
| 500 | LOOSE PIECE | 134540-1 |
| QTY | PACKAGE TYPE | PART NUMBER |

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN RAVI S 25JUN2018

CHK ROHDE DANIEL F 25JUN2018

APVD ROHDE DANIEL F 25JUN2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



NAME BUTT SPLICE SOLISTRAND
16-14 AWG

| | | | |
|------|-----------|------------|---------------|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
| A3 | 00779 | C-134540 | - |

| | | |
|--|--|---|
| FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS | PRODUCT INFORMATION CENTER 1-800-522-6752 | MAX RECOMMENDED OPERATING TEMPERATURE: 260°C [500°F] VOLTAGE RATING: N/A |
| FOR APPLICATION TOOLING INFORMATION | TOOLING ASSISTANCE CENTER 1-800-722-1111 | |
| FOR ORDER ENTRY | 1-800-526-5142 | WIRE CROSS SECTIONAL AREA RANGE, 1.04-2.62mm²[2,050-5,180] CIR MILS |

| | |
|----------------------------|--|
| DIMENSIONS: mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED: |
| | 0 PLC ± - |
| | 1 PLC ± - |
| | 2 PLC ± - |
| | 3 PLC ± 0.127[.005] |
| | 4 PLC ± - |
| | ANGLES ± 5° |

| | |
|--------------|------------|
| MATERIAL △ 3 | FINISH △ 4 |
|--------------|------------|

| | | |
|-------|--------|-----|
| SCALE | SHEET | REV |
| 8:1 | 1 OF 1 | A |