


# Dual Clamp Terminal Blocks

SAKB 10C



Available Options		Version	Part No.
		Melamine	0259920000
<b>Dimensions</b>			
Width / Length / Height mm (in.)	with TS 32	↔	10/50/60 (.39/1.97/2.36)
Insulation stripping length		mm (in.)	12 (.47)
<b>Technical Data</b>			
Rated voltage / rated current / wire size	UL		–
	CSA		600 V / 45 A / #18...8 AWG
<b>End Plate / End Bracket (thickness mm)</b>			
	Type		Part No.
End plate	AP (3)		0146720000
End bracket	EWK 2 (15)		0199360000
<b>Jumpers</b>			
Note: Final number in model indicates no. of poles (e.g. Q 2 = 2 poles). For additional information, see Accessories section.	Q 2		0457100000
	Q 3		0457200000
	Q 4		0457300000
	Q 10		0457400000
<b>Test Plugs</b>			
Plug	PS		0299600000
Plug bolt	StB 16		0169900000
<b>Marking Tags</b>			
	Print		
	Consecutive horizontal	DEK 5/6.5	0468160001
	Consecutive vertical	DEK 5/6.5	0468260001

See Accessories section for mounting rails, end brackets, additional marking material and accessories.