


# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
	B	ECR # 061123-6 ADD LENGTH	11/23/06'
	C	ECR # 061222-4 ADD CABLE P/N	12/22/06'




**NOTE:**

- CABLE: UL-2919 [30AWG(7/0.102 T.C)\*1C INS:FOAM-PE ID:1.3±0.05 +SPRAL(T.C)]\*3C INS:PVC ID:2.3±0.1+28AWG(7/0.127 T.C)\*7C +INS:SR-PVC ID:ø0.9±0.05mm+AL/MY+DRAIN 30AWG(7/0.102 T.C) +BRAID (16/4/0.1 T.C)+OUTER JACKET:PVC COLOR:BLACK(NK-K01) OD:ø7.5±0.15mm, **(C2919283BA)**
- CONNECTOR:  
P1:HDB 15P MALE GOLD FLASH CONTACT, NICKEL PLATED SHELL (THE 9TH PIN UNLOAD)  
P2:HDB 15P FEMALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL

- FERRITE CORE: 17.5\*28.5\*9.5mm
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)
- ELECTRICAL TEST: <1>.100% OPEN SHORT & MIS WIRE TEST  
<2>. CONTACT RESISTANCE 3 Ohms MAX  
<3>. INSULATION RESISTANCE 10M Ohms MIN
- PACKING: <1>EACH PC / POLYBAG + EAN CODE LABEL & ROHS LABEL  
<2>EACH CARTON / ROHS LABEL(L\*W=35\*22mm)

**PIN OUT**



120-2621-6	CV0022	20000±200mm	4260113563021
120-2621-5	CV0021	15000±150mm	4260113563014
120-2621-4	CV0019	10000±100mm	4260113563007
120-2621-3	CV0006	5000±50mm	4260113560235
120-2621-2	CV0005	3000±30mm	4260113560228
120-2621-1	CV0004	1800±30mm	4260113560211
DWG	P/N	L±T	EAN CODE



Tolerance	Inch	M/M
X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Draw	FANNIE 12/22/06'
Check	
Engr	

App'd	Customer	P/N
Scale	NONE	Units
Dwg No.	120-2621	REV: C

Third Angle Projection	Sheet 1/2
------------------------	-----------

## 2DIREKT GMBH

HDB15/M - HDB15/F CABLE