



SPECIFICATIONS

MANUFACTURER	BON;ECI OR CZT
PART NO.	4P-4C
UL REF:	E159371;UL 498 NO,E129580 OR E134299
CSA REF	LR 90513 OR LR 96654
HOUSING	POLY CARBONATE(PC) UL94V2 NO. E919153
CONTACT BLADE	HIGH STRENGTH COPPER ALLOY
MATERIAL	100 MICRON NICKEL UCNDERPLATED
PLATING TYPE	8% PHOSPHOR BRONZE
PLATING THICKNESS:	(50U")GOLD PLATED
OPERATING TEMP	-40°C TO 125°C
CURRENT RATING	250V AC MAX AT 2A
DIELECTRIC	500V AC
INSULATION RES	500MEGAOHMS
TERMINATION RES	35 MAX AFTER ENVIRONMENTAL TESTS
TENSILE STRENGTH	20 LBS(89N)MIN
DURABILITY	500 MATING CYCLES

COMPLIES WITH FCC68/F

REVISED	VERSION	BASIS	CONTENTS
17-12-15	A/1	T1214A	NEW DRAWING

CnC Tech, LLC Industrial Cable and Connector Technology		
REV.NO:	ISSUE (A/0)	CUSTOMER:L-671
DRAWING NO:	671-437	PART NO: 5010-FU0044-005
ITEM NO:	MP4P4C PLUG 50U" F	
UNIT:MM	DRAWN:	ENGINEER:
DATE: 2017-12-15	QA:	SALES DEPT:
		SALES MANAGER: