


RoHS  
Compliant  
Drawing For  
Reference Only



Technical requirement :

1. This product should meet EU RoHS related requirement.
2. The surface of plastic part should be without any crackle such as burr,lack,and so on phenomenon.
3. The surface of metal part should be without any defect such as scaur,nick,oxidation and plating problem.
4. The electronic performance should be the same as spec.
5. The un-specified tolerance is :  $<6 \pm 0.1$   
 $6 \sim 20 \pm 0.2$   
 $>20 \pm 0.3$


Specification:

Contact Resistance : 30m ohm max.

Insulation Resistance : 100M ohm min. at DC 500V

Dielectric Strength : AC 500V for one minute.

**DCI** DRAGON CITY INDUSTRIES LIMITED

Item Name	3.5mm Mono Phone Plug	Tolerance :	Design	K.W Law	Remark		Scale	
Item No.	NP-106-EN	Unit : mm 	Drawing	W.K Yeung	Remark		Material	
			Check	K.L Wong	Remark		Drawing No.	90429-0954
			Approval	K.W Chan	Remark		Sheet	