

38999  
III  
HD  
Dualok  
II  
I  
SJT  
Accessories  
Aquacon  
Herm/Seal  
PCB

**PART #** Part number reference. To complete, see how to order pages 62-66.

**Commercial**

Connector Type	Shell Style	Service Class	Shell Size & Insert Arrg	Contact Type	Alternate Position	Special Variations
JTG/JTNG	06	RE	22-2	P	A	(XXX)

**Military**

MS Number	Service Class	Shell Size	Finish	Insert Arrg	Contact Style (P or S)	Alternate Position
MS27484	E	14	A	18	P	A

HIGH SPEED  
Fiber Optics  
Contacts  
Connectors  
Cables

EMI Filter  
Transient

26482  
Matrix 2

83723 III  
Matrix | Pyle


26500  
Pyle

5015  
Crimp Rear Release  
Matrix

22992  
Class L

Back-Shells

Options  
Others



\* Plug with grounding fingers  
\*\* Clear iridite finish (gold color), N<sub>2</sub>O<sub>4</sub> resistant

Shell Size	F Dia.	L Max.	L' Max.	Q Dia Max.	V Thread Modified		KK Dia. Max.	KK' Dia. Max.
					Class 2A UNEF	Modified Major Dia.		
8	.444	.891	1.000	.734	.4375-28	.421 - .417	.625	.578
10	.558	.891	1.000	.844	.5625-24	.542 - .538	.750	.703
12	.683	.891	1.000	1.016	.6875-24	.667 - .663	.875	.828
14	.808	.891	1.000	1.141	.8125-20	.791 - .787	1.000	.953
16	.909	.891	1.000	1.265	.9375-20	.916 - .912	1.125	1.078
18	1.034	.891	1.000	1.391	1.0625-18	1.034 - 1.030	1.250	1.203
20	1.159	.891	1.000	1.500	1.1875-18	1.158 - 1.154	1.375	1.328
22	1.284	.891	1.000	1.625	1.3125-18	1.283 - 1.279	1.500	1.453
24	1.409	.891	1.062	1.750	1.4375-18	1.408 - 1.404	1.625	1.578

All dimensions for reference only.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[MS27484T16B55S](#) [MS27484T16B35PC](#) [MS27484T14B18PC](#) [MS27484T16F6BA](#) [MS27484T16B26BA](#)  
[MS27484T10B5SC](#) [MS27484T10A35SC](#) [MS27484T24B35SB-LC](#) [MS27484T20B2BA](#) [MS27473E16F26S](#)  
[MS27473E18F35S](#) [MS27473E20F41PA](#) [MS27473E20F41S](#) [MS27484E12A3S](#) [MS27484E12B35S-LC](#)  
[MS27484E12F35P](#) [MS27484E14B18P](#) [MS27484E16B35S](#) [MS27484E16B6S](#) [MS27484E16F35S-LC](#)  
[MS27484E18F11PC](#) [MS27484E20B41A](#) [MS27484E8F35S](#) [MS27484P16B35P](#) [MS27484T10A35S](#)  
[MS27484T10F35P](#) [MS27484T10F35SB](#) [MS27484T10F5S](#) [MS27484T12A35P](#) [MS27484T12B8S](#)  
[MS27484T12F35PB](#) [MS27484T12F8S](#) [MS27484T14B18P-LC](#) [MS27484T14B18S](#) [MS27484T14B35P](#)  
[MS27484T14B35P-LC](#) [MS27484T14B35S](#) [MS27484T14B5S](#) [MS27484T14F35P](#) [MS27484T14F35PC](#)  
[MS27484T14F35S](#) [MS27484T14F5PA](#) [MS27484T16A35P](#) [MS27484T16A8P](#) [MS27484T16B26P-LC](#)  
[MS27484T16B26S-LC](#) [MS27484T16B35PA-LC](#) [MS27484T16B35P-LC](#) [MS27484T16B35SA-LC](#) [MS27484T16B35S-](#)  
[LC](#) [MS27484T16F26PA](#) [MS27484T16F26S-LC](#) [MS27484T16F35S](#) [MS27484T16F35SA-LC](#) [MS27484T16F8S-LC](#)  
[MS27484T18B32P](#) [MS27484T18B32S-LC](#) [MS27484T18B35S-LC](#) [MS27484T18F32S](#) [MS27484T18F35P-LC](#)  
[MS27484T18F35SA](#) [MS27484T18F35S-LC](#) [MS27484T20B35S-LC](#) [MS27484T20B39S-LC](#) [MS27484T20B41S](#)  
[MS27484T20B41SA-LC](#) [MS27484T20B41S-LC](#) [MS27484T20F16P](#) [MS27484T20F35SA](#) [MS27484T20F41S](#)  
[MS27484T22B21S-LC](#) [MS27484T22B35S](#) [MS27484T22B55S-LC](#) [MS27484T22F21SA-LC](#) [MS27484T22F21S-LC](#)  
[MS27484T22F35B](#) [MS27484T22F35P-LC](#) [MS27484T22F55SC-LC](#) [MS27484T22F55S-LC](#) [MS27484T24B35AB](#)  
[MS27484T24B35P](#) [MS27484T24F2P](#) [MS27484T24F35PA-LC](#) [MS27484T8B35P-LC](#) [MS27484T8B35S-LC](#)  
[MS27484T8B44S](#) [MS27484T8B44S-LC](#) [MS27484T8B98P](#) [MS27484T8B98S-LC](#) [MS27484T8F35S](#)  
[MS27484T8F35S-LC](#) [MS27484T8F98P](#) [MS27484T24B29SC](#) [MS27484T10B35A](#) [MS27484T10B35B](#)  
[MS27484T22B55B](#) [MS27484P16B35PA](#) [MS27484P24B35SA](#) [MS27484P12A35SA](#) [MS27484P24B35SC](#)