

PRODUCT-DETAILS

ASF28/M25/A/BL

STRAIGHT M25 IP66.69/ NC28 COND BLK



General Information

Extended Product Type	ASF28/M25/A/BL
Product ID	7TCA296000R1692
EAN	5020963010842
Catalog Description	STRAIGHT M25 IP66.69/ NC28 COND BLK
Long Description	Adaptaseal Straight Conduit Fitting, Fixed External Male Thread, Fine Profile, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 6.6, Black

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Product Type	Conduit Fitting with Metric Threads

Ordering

EAN	5020963010842
UPC	786210281612

Technical

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6.6
Size	NC 28mm

Environmental

WEEE Category

Product Not in WEEE Scope

Container Information

Package Level 1 Units

10 piece

Certificates and Declarations

Data Sheet, Technical Information	ASF28/M25/A/BL
Instructions and Manuals	ASF28/M25/A/BL
Declaration of Conformity - CE	9AKK107492A9618
RoHS Information	9AKK107992A8994
RoHS Date	9AKK107992A8994
REACH Declaration	9AKK107992A8994

Classifications

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

