

UT 233 токовые клещи (ваттметр)



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
AC Voltage	15V/100V/300V/600V	± (1.2%+5)
AC Current	40A/100A/400A/1000A	± (2%+5)
Active Power	0.01kW-600kW	± (3%+5)
Apparent Power	0.01kVA-600kVA	± (3%+5)
Reactive Power	0.01kVAr-600kVAr	± (4%+5)
Power Factor	0.3~1(Capacitive or Inductive)	± (0.02+2)
Phase Angle	0°C~360°C	± 1°
Frequency	20Hz-500Hz	✓
Active Energy	1~9999 kWh	± (3%+2)
Special Functions		
Auto Ranging		✓
Single-phase 2-wire		✓
3-phase 3-wire		✓
3-phase 4-wire		✓
Phase Rotation Test		✓
True RMS	AC Voltage or Current	✓
Calibration Feature		✓
Data Logging	99	✓
Data Recall		✓
Max/Min Mode		✓
Data Hold		✓
USB		✓
Display Backlight		✓

Full Icon Display		✓
Sleep Mode		✓
Low Battery Display		✓
Input Impedance for AC Voltage Measurement	$\geq 10M\Omega$	✓
Max. Display	9999	✓