









PRODUCT NUMBER
SEE PART NO. TABLE



TOLERANCE: ±0.05
RECOMMENDED P.C.B. Layout
TOP VIEW



Mating Condition (REF.)



PIN	A	B	PIN	A	B
02	0.80	3.80	12	8.80	11.80
03	1.60	4.60	13	9.60	12.60
04	2.40	5.40	14	10.40	13.40
05	3.20	6.20	15	11.20	14.20
06	4.00	7.00	16	12.00	15.00
07	4.80	7.80	17	12.80	15.80
08	5.60	8.60	18	13.60	16.60
09	6.40	9.40	19	14.40	17.40
10	7.20	10.20	20	15.20	18.20
11	8.00	11.00			

NOTES:

- MATERIAL:
INSULATION(HALOGEN FREE): THERMOPLASTIC HIGH TEMP,UL94V-0,GLOW WIRE COMPATIBLE
CONTACT: COPPER ALLOY, t=0.15
- MATE WITH RECEPTACLE: AFCI 10145492
- THE INSULATION CAN WITHSTAND IR REFLOW 260°C FOR 10 SECONDS
- PRODUCT SPEC: GS-12-1444
- PACKAGING SPEC: GS-14-2616
- ORDERING CODE: 10144042-XX X X X LF

NO. OF PINS	XX	X	X	X	LF	PACKAGE
02~20 PIN						1: TAPE & REEL
INSULATION COLOR						CONTACT FINISH
0: CREAM						1: MATTE-TIN PLATED OVER NICKEL
						2: GOLD FLASH OVER NICKEL

mat'l. code	surface	tolerance	projection	product family MINITEK	
ISO 1302	ISO 406	ISO 1101			
ltr	ecn no	dr	date		title 0.8mm Pitch VT Header SMT
tolerances unless otherwise specified					
	angles	.X±.25	mm	dwg no 10144042	
	linear	.XX±.15	scale 1:1		sheet 1 of 1
	0°±x'	.XXX±.08		size A3	
dr	TONY LENG	2017-05-22		type Product Customer Drawing	
engr	TONY LENG	2017-05-22			
chr	ZK HU	2017-05-22			
appd	TIM YAO	2017-05-22			
sheet index	revision sheet	A 1			



Amphenol FCI

© 2016 AFCI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10144042-08011LF](#) [10144042-07011LF](#)