



DESCRIPTION: CAT5E MOLDED & BOOTED PATCH CABLE
 MODEL NUMBER: 73-779X-XXX
 APPLICATION: PATCH CABLE
 CRIMP TOOL: N/A
 IMPEDANCE: N/A
 FREQUENCY RANGE: N/A
 MATERIAL: PLUG RJ-45, GODL PLATED
 HOOD PVC
 CABLE UTP, 24 AWG, 4 TWISTED PAIRS, STRANDED
 BARE COPPER, UL ETL EIA/TIA-568B
 VERIFIED CATEGORY 5E

RoHS COMPLIANCE: YES
 TECHINCAL DETAIL: N/A





TABLE 1

MODEL NUMBER	LENGTH (FEET)	DESCRIPTION
73-779X-1	1	CAT5E MOLDED & BOOTED PATCH CABLE, 1FT
73-779X-1.5	1.5	CAT5E MOLDED & BOOTED PATCH CABLE, 1.5FT
73-779X-3	3	CAT5E MOLDED & BOOTED PATCH CABLE, 3FT
73-779X-5	5	CAT5E MOLDED & BOOTED PATCH CABLE, 5FT
73-779X-7	7	CAT5E MOLDED & BOOTED PATCH CABLE, 7FT
73-779X-10	10	CAT5E MOLDED & BOOTED PATCH CABLE, 10FT
73-779X-14	14	CAT5E MOLDED & BOOTED PATCH CABLE, 14FT
73-779X-25	25	CAT5E MOLDED & BOOTED PATCH CABLE, 25FT
73-779X-35	35	CAT5E MOLDED & BOOTED PATCH CABLE, 35FT
73-779X-50	50	CAT5E MOLDED & BOOTED PATCH CABLE, 50FT
73-779X-100	100	CAT5E MOLDED & BOOTED PATCH CABLE, 100FT

X=COLOR
 0-GRAY
 1-BLACK
 2-BLUE
 3-GREEN
 4-RED
 5-YELLOW
 6-WHITE
 7-ORANGE
 8-PINK
 9-PURPLE



This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traded or copied without permission and is returnable upon demand.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.

3RD ANGLE PROJECTION

 RoHS2
 2011/65/EU
 UNLESS OTHERWISE SPECIFIED
 UNITS: INCH
 -XX ±.02
 -XXX ±.005
 ANGLES ±2°

AIM-Cambridge
 Title: CAT5E MOLDED & BOOTED PATCH CABLE
 Model No. 73-779X-XXX
 Size A DO NOT SCALE DRAWING Date: 2015/5/18 Sheet 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions:

[73-7790-10](#) [73-7790-5](#) [73-7791-10](#) [73-7791-5](#) [73-7792-10](#) [73-7792-5](#) [73-7793-5](#) [73-7797-25](#) [73-7797-50](#)