


CAPACITOR MOUNTS



Material Specifications:

Natural or black Nylon, per ASTM D 4066
PA111, UL Rated 94V-2

Oxygen Rating Index: Over 28%

Standard Drawing Tolerances:


(unless otherwise indicated)

Fractions: $\pm 1/64$ (0.4) .XX = ± 0.01 (0.25)
.X = ± 0.10 (2.5) .XXX = ± 0.005 (0.13)

311 thru 316 Series


Color: Natural

| Part No. | A55485/06 M38527/06 | A | B | Price Code |
|----------|------------------------|-------------|-------------|------------|
| 311-200 | -023N | .300 (7.6) | .200 (5.1) | A |
| 312-250 | -024N | .350 (8.9) | .250 (6.4) | A |
| 313-300 | -025N | .400 (10.2) | .300 (7.6) | A |
| 314-350 | -026N | .450 (11.4) | .350 (8.9) | B |
| 315-400 | -027N | .500 (12.7) | .400 (10.2) | B |
| 316-500 | -028N | .600 (15.2) | .500 (12.7) | B |



330 Series Discrete

| Part No. | A55485/06 M38527/06 | H | F | Price Code |
|----------|------------------------|------------|------------|------------|
| 330-050 | -047N | .050 (1.3) | .000 | A |
| 330-072 | -046N | .072 (1.8) | .022 (.56) | A |
| 330-085 | -048N | .085 (2.2) | .035 (.89) | A |



388 Series

Color: Black

| Part No. | H | F | Price Code |
|----------|------------|------------|------------|
| 388-025 | .025 (.64) | .000 | A |
| 388-050 | .050 (1.3) | .025 (.64) | A |
| 388-075 | .075 (1.9) | .050 (1.3) | A |

