


Search Results

- Evaluate
  - FAQ's
  - Product Bulletins
  - PDFPEEK Cable T.
- Design a Solution
  - Catalog Cut Sheet
  - PDFPLT1MC71 Pr
  - Part Drawings
  - PDFPan-Ty PEEK.
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PLT1.5M-C71'

Your search criteria matched only one product, shown below

**PLT1.5M-C71**



- Designed for harsh environments where a cable tie material is required to hold up to chemical, high radiation, and/or high operating temperature environments
- Non-conductive material that is excellent for high temperature applications up to 500°F (260°C)
- Flammability rating of V-0 with low smoke and toxicity
- PEEK material meets MIL specification MIL -P-46183, and is approved for use by The Department of Defense

|                                   |  |
|-----------------------------------|--|
| Part Number                       | PLT1.5MC71   |
| RoHS Compliancy Status            | Compliant  |
| Part Description                  | Cable Tie, Locking, 5.8", Standard cross section.            |
| Product Type                      | Cable Ties   |
| Material                          | Polyetheretherketone (PEEK)                                  |
| Color                             | Translucent Brown  |
| CSA Certified                     | No   |
| UL Listed (File #E56854)          | No   |
| UL Recognized (File #E56854)      | No   |
| Length (In.)                      | 5.8  |
| Length (mm)                       | 147  |
| Width (In.)                       | 0.098  |
| Width (mm)                        | 2.5  |
| CE Compliant                      | Yes  |
| Cross Section                     | Miniature  |
| Head Height (In.)                 | 0.131  |
| Head Height (mm)                  | 3.3  |
| Head Width (In.)                  | 0.188  |
| Head Width (mm)                   | 4.8  |
| Locking Style                     | Locking  |
| Material Flammability Rating      | V-0  |
| Max. Bundle Diameter (In.)        | 1.38   |
| Max. Bundle Diameter (mm)         | 35   |
| Max. Continuous Use Temperature   | 500°F (260°C)  |
| Min. Bundle Diameter (In.)        | 0.06   |
| Min. Bundle Diameter (mm)         | 1.5  |
| Min. Loop Tensile Strength (Lbs.) | 35   |
| Min. Loop Tensile Strength (N)    | 156  |
| PlenumRated                       | No   |
| Pricing Description               | Cable Tie, 5.8"L (147mm), Miniature, PEEK, Translucent Brown |
| Thickness (In.)                   | 0.048  |
| Thickness (mm)                    | 1.2  |
| Tip Style                         | Curved   |
| Tool                              | GTS, GTSL, PTS   |
| Min. Order UOM                    | PC   |
| Min. Order Qty.                   | 100  |
| BOM Qty. (# of Pkgs.)             | <input type="text" value="0"/>                               |
| Add to Favorite Product List      | <input type="button" value="e"/>                             |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.