



NOTE 1. APPLICABLE WIRE SIZE IS MENTIONED BELOW.

TABLE 1

CRIMP TYPE	APPLICABLE WIRE		V GROOVE	DIMENSIONS	
	WIRE SIZE	INSULATION OUTER DIA.		φ A	φ B
C 1	AWG# 8~10 (8 mm~5.5 mm)	φ 7.25MAX.	WITH V GROOVE	4.3	5.6
C 2	AWG# 10~12 (5.5 mm~3.5 mm)	φ 7.25MAX.	WITHOUT V GROOVE	3.5	4.5

2	RETAINER CLIP	1	SYNTHETIC RESIN	_____	_____
1	PIN CONTACT	1	COPPER ALLOY	SILVER PLATING	_____
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
UNLESS OTHERWISE SPECIFIED: T76-20-M			DATE 21. Apr. '95	TITLE JAE-CONNECTOR.COM CONT-JL05-08P-C* Reference Only	
DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON : (INCHES) FRACTIONS DECIMALS ANGLES			DRAWN M. OOWA	JAE-CONNECTOR.COM JAPAN AVIATION ELECTRONICS INDUSTRY, LTD. MUSASHINO, AKISHIMA-SHI TOKYO, JAPAN DWG. NO. SJ025430-E	
			CHECKED S. NANA O		
			APP'D T. MORITA		
			APP'D M. Takagi	SERIES JL05	SCALE 2/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[CONT-JL05-08P-C1-10](#) [CONT-JL05-08P-C2-10](#)